



HIGH TEMPERATURE

Hermetically Sealed AC-LVDT Position Sensors MACRO HPGS 750

Overview

Macro Sensors' HPGS 750 Series of 3/4 inch (19 mm) diameter AC-operated LVDTs is designed for a wide range of position measurement applications. These are rugged hermetically sealed sensors, constructed entirely of stainless steel, and intended for use at high temperatures (400°F). The coil windings are IP-68 sealed against hostile environments and electrical termination is through a sealed radial screw on style 38999 connector (mating connector included).

The screw on radial connector offers three important benefits. First, it results in a through-bore design, which permits access to either or both ends of the LVDT's core for better mechanical support and core guidance, and easier cleanout in dusty or dirty locations. The second advantage of the radial connector is shorter installed length compared to units of the same range with axial connectors. Third, units withstand higher vibration.

Macro Sensors offers several standard options, including *Teflon® bore liners and metric threaded cores. In addition, Macro Sensors can provide a range of mounting accessories and core extension rods. HPGS LVDT's series can also be supplied to withstand exposure to mild radiation (3x10⁷ Rads). On special order, the HPGS 750 Series can also be constructed for immersion in pressurized fluids.

All HPGS 750 Series LVDTs will operate properly with any conventional differential input LVDT signal conditioner. Macro Sensors offers a full line of LVDT signal conditioners that will deliver optimum performance from any HPGS 750 Series LVDT.

^{*} Teflon® is a registered trademark of DuPont

HPGS 750 Position Sensors

Benefits

- ◆ Ranges of ±0.050 inch to ±10.0 inches
- Long term high vibration survivability
- 400°F (200°C) operating temperature
- Screw on radial connector; through-bore operation
- ◆ IP-68
- ◆ Non-linearity less than ±0.25% of FRO

Applications

- Hydraulic cylinder position
- Steam valve positioning
- Power generation equipment
- ◆ Corrosive environments

Performance

Linearity Error $<\pm0.25\%$ of FRORepeatability Error $<\pm0.01\%$ of FSOHysteresis Error $<\pm0.01\%$ of FSO

Environmental Data

Operating
Temperature
-65°F to +400°F (-55°C to +200°C)


Temperature


-0.01%/°F (nominal) (-0.02%/°C nominal)


Vibration Tolerance 20 g to 2 kHz **Shock Survival** 1000 g, 11 ms

Electrical Data


Input Voltage 3.0 Vrms (nominal)
Input Frequency 2.5 to 3.0 kHz







Dimensions



DENOTES CENTER OF CORE @ ELECTRICAL ZERO

Parameter ▼	Range Code >	050	125	250	500	1000	2000	3000	4000	5000	7500	10000
Nominal Range	inches	± 0.050	± 0.125	± 0.25	± 0.50	± 1.00	± 2.00	± 3.00	± 4.00	± 5.00	± 7.50	± 10.00
	mm	± 1.3	± 3.0	± 6.3	± 12.5	± 25	± 50	± 75	± 100	± 125	± 190	± 250
Sensitivity	mV/V/.001 in	6.1	3.9	2.4	0.63	0.61	0.37	0.25	0.17	0.12	0.11	0.07
	mV/V/mm	240	154	96	25	24	15	9.8	6.7	4.9	4.3	2.8
Primary Impedance (Ω)	ohms	325	735	1400	1200	1250	2150	2150	420	600	775	620
Dimension "A"	inches	2.01	2.64	3.35	5.92	7.38	10.91	13.65	16.17	18.65	23.85	31.66
	mm	51.1	67.1	85.1	150.4	187.5	277.1	346.1	411	473.7	606	804
Dimension "B"	inches	0.8	1.25	1.65	3.45	3.45	5.3	6.2	6.2	6.2	7	9.5
	mm	20.3	31.7	41.9	87.6	87.6	134.6	157.5	157.5	157.5	177.8	241.3
Dimension "N"	inches	0.63	0.94	1.32	2.57	3.32	5.07	6.29	7.65	8.94	11.52	15.42
	mm	16	24	33	65	84	129	160	194	227	293	392
Weight - Body	ounces	1.6	2.1	2.5	3.3	4.3	6.2	8.2	9.2	10	14.2	18.3
	grams	45	59	71	93	122	176	232	260	283	402	519
Weight - Core	ounces	0.08	0.12	0.18	0.4	0.4	0.65	0.8	0.8	0.8	0.9	1.2
	grams	2.4	3.7	4.8	11.6	11.6	18	22	22	22	25.5	34

HIGH TEMPERATURE HPGS 750 Position Sensors

Ordering Information

- Mild radiation resistant -080 option
- For standard HPGS 750, order by model number with range.
- ◆ For metric threaded core option, add -006 after model number with range.
- For Teflon® bore liner option, add -010 after model number with range (not available with -080 option).



Macro Sensors also offers a full line of LVDT signal conditioners, controllers and indicators that deliver optimum performance from any AC operated LVDT.

NORTH AMERICA

AST Macro Sensors, a TE Connectivity company Tel: 800-522-6752

Email: customercare.pens@te.com

TE.com/sensorsolutions

AST Macro Sensors, a TE Connectivity company.

AST Macro Sensors, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

HPGS 750 11/01/15

