



FEATURES

- ◆ 0.25% linearity (100% stroke)
- Large 1/16" core-to-bore clearance
- Shock and vibration tolerant
- Electromagnetic/electrostatic shielding
- High temperature (220°C) version available
- Calibration certificate supplied with each unit

APPLICATIONS

- Process control
- Factory automation
- Materials testing
- Metrology
- Applications with large misalignments
- General industrial

HR SERIES

General Purpose LVDT

SPECIFICATIONS

- High Reliability
- Large core-to-bore clearance
- Stroke ranges from ± 0.05 to ±10 inches
- ◆ AC operation from 400Hz to 5kHz
- Stainless steel housing
- Imperial or metric threaded core
- Many options and accessories

The **HR Series** general purpose LVDTs provide the optimum performance required for a majority of applications. The large 1/16 inch [1.6mm] bore-to-core radial clearance provides for ample installation misalignments and therefore reduces the application costs. Featuring a high output voltage and a broad operating frequency range, these versatile and highly reliable LVDTs deliver worry-free and precise position measurements.

Available in a variety of stroke ranges from ± 0.05 to ± 10 inches, the HR Series can be configured with a number of standard options including guided core, small diameter/low mass core. High temperature (200° C) operation and Mild Radiation Resistance versions are also available *(consult factory)*. The HR Series is compatible with the full line of Measurement Specialties LVDT signal conditioners.

Like in most of our LVDTs, the HR windings are vacuum impregnated with a specially formulated, high temperature, flexible resin, and the coil assembly is potted inside its housing with a two-component epoxy. This provides excellent protection against hostile environments such as high humidity, vibration and shock.

PERFORMANCE SPECIFICATIONS

ELECTRICAL SPECIFICATIONS												
Parameter	HR 050	HR 100	HR 200	HR 300	HR 500	HR 1000	HR 2000	HR 3000	HR 4000	HR 5000	HR 7500	HR 10000
Stroke range	±0.05 [±1.27]	±0.1 [±2.54]	±0.2 [±5.08]	±0.3 [±7.62]	±0.5 [±12.7]	±1 [±25.4]	±2 [±50.8]	±3 [±76.2]	±4 [±101.6]	±5 [±127]	±7.5 [±190.5]	±10 [±254]
Sensitivity V/V/inch [mV/V/mm]	5.8 [228]	4.2 [165]	2.5 [98.4]	1.3 [51.2]	0.7 [27.6]	0.39 [15.4]	0.23 [9.1]	0.25 [9.8]	0.20 [7.9]	0.14 [5.5]	0.13 [5.1]	0.07 [2.8]
Output at stroke ends, mV/V (*)	290	420	500	390	350	390	460	750	800	700	975	700
Phase shift	-1°	-5°	-4°	-11°	-1°	-3°	+5°	+11°	+1°	+3°	+1°	-5°
Input impedance (PRIMARY)	430Ω	1070Ω	1150Ω	1100Ω	460Ω	460Ω	330Ω	315Ω	275Ω	310Ω	260Ω	550Ω
Output impedance (SECONDARY)	4000Ω	5000Ω	4000Ω	2700Ω	375Ω	320Ω	300Ω	830Ω	400Ω	400Ω	905Ω	750Ω
Non-linearity			•	•	•	±%	of FR	•			•	
@ 50% stroke	0.10	0.10	0.10	0.10	0.15	0.15	0.15	0.15	0.15	0.15	/	0.15
@100% stroke (maximum)	0.25	0.25	0.25	0.25	0.25	0.25	0.25	0.25	0.25	0.25	0.25	0.25
@125% stroke	0.25	0.25	0.25	0.35	0.35	1.00	0 .50 (**)	0 .50 (**)	0 .50 (**)	1.00 (**)	/	1.00 (**)
@150% stroke	0.50	0.50	0.50	0.50	0.75	1.30 (**)	1.00 (**)	1.00 (**)	1.00 (**)	1	/	/
Input voltage	3 VRMS sine wave											
Input frequency	400Hz to 5kHz											
Test frequency	2.5kHz											
Null voltage	0.5% of FRO, maximum											

ENVIRONMENTAL SPECIFICATIONS & MATERIALS						
Operating temperature	-65°F to +300°F [-55°C to 150°C]					
Shock survival	1,000 g (11ms half-sine)					
Vibration tolerance	20 g up to 2KHz					
Housing material	AISI 400 Series stainless steel					
Electrical connection	Six lead-wires, 28 AWG stranded Copper, PTFE insulated, 1 foot [30cm] long (longer wires optional)					
IEC 60529 rating	IP61					

Notes:

Dimensions are in inch [mm]

All values are nominal unless otherwise noted

Electrical specifications are for the test frequency indicated in the table

FR: Full Range is the stroke range, end to end; FR=2xS for ±S stroke range


FRO (Full Range Output): Algebraic difference in outputs measured at the ends of the range

(*) Unit for output at stroke ends is millivolt per volt of excitation (input voltage)

(**) Requires special reduced core length


MECHANICAL SPECIFICATIONS

Parameter	HR 050	HR 100	HR 200	HR 300	HR 500	HR 1000	HR 2000	HR 3000	HR 4000	HR 5000	HR 7500	HR 10000
Body length "A"	1.13	1.81	2.50	3.22	5.50	6.63	10.00	12.82	15.64	17.88	24.09	30.85
	[28.7]	[46.0]	[63.5]	[81.8]	[139.7]	[168.4]	[254]	[325.6]	[397.3]	[454.2]	[611.9]	[783.6]
Core length "B"	0.80	1.3	1.65	1.95	3.45	4.00	5.30	5.60	7.00	7.00	7.00	8.50
	[20.3]	[33.0]	[41.9]	[49.5]	[87.6]	[101.6]	[134.6]	[142.2]	[177.8]	[177.8]	[177.8]	[215.9]
Body weight, oz [g]	1.13	1.69	2.12	2.72	3.85	4.45	5.93	7.94	10.41	11.99	16.16	20.46
	[32]	[48]	[60]	[77]	[109]	[126]	[168]	[225]	[295]	[340]	[458]	[580]
Core weight, oz [g]	0.14	0.21	0.28	0.35	0.64	0.74	0.95	0.99	1.27	1.27	1.27	1.52
	[4]	[6]	[8]	[10]	[18]	[21]	[27]	[28]	[36]	[36]	[36]	[43]



Dimensions are in inch [mm]

WIRING INFORMATION



Connect blue (BLU) to green (GRN) for differential output

ORDERING INFORMATION

Description	Model	Part Number	D	Des	cription	Model	Part Number	
±0.05 inch LVDT	HR 050	02560389-000 ±2			nch LVDT	HR 2000	02560396-000	
±0.1 inch LVDT	HR 100	100 02560390-000 ±3			nch LVDT	HR 3000	02560398-000	
±0.2 inch LVDT	0.2 inch LVDT			±4 inch LVDT		HR 4000	02560399-000	
±0.3inch LVDT	HR 300	HR 300 02560392-000 ±5			nch LVDT	HR 5000	02560400-000	
±0.5 inch LVDT	HR 500	02560394-000	±7.5 inch LVDT		inch LVDT	HR 7500	02561011-000	
±1 inch LVDT	HR 1000	02560395-000 ±1		±10	inch LVDT	HR 10000	02560401-000	
OPTIONS								
5.0 kHz calibration				HR 050, 100, 200 and 500 only		XXXXXXXX-002		
Metric threaded core)			All models		XXXXXXXXX-006		
Guided core				All models		XXXXXXXXX-010		
Small-diameter/low-	mass core <i>(con</i>	sult factory for mass a		Consult factory		XXXXXXXX-020		
10 foot long lead-wir	es	_		Consult factory		XXXXXXXXX-040		

Note: Add multiple option dash numbers together to determine proper ordering suffix Example: HR 1000, ±1 inch, with 5 kHz calibration and guided core, P/N 02560395-012

ACCESSORIES							
Core connecting rod, 6 inches long, 6-40 threads	05282947-006						
Core connecting rod, 12 inches long, 6-40 threads	05282947-012						
Core connecting rod, 24 inches long, 6-40 threads	05282947-024						
Core connecting rod, 36 inches long, 6-40 threads	05282947-036						
Core connecting rod, 6 inches long, M4x0.7 metric threads	05282978-006						
Core connecting rod, 12 inches long, M4x0.7 metric threads	05282978-012						
Mounting block	04560952-000						

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity company Tel: 800-522-6752 Email: customercare.frmt@te.com

EUROPE

Measurement Specialties (Europe), Ltd., a TE Connectivity Company Tel: 800-440-5100

Email: customercare.bevx@te.com

ASIA

Measurement Specialties (China) Ltd., a TE Connectivity company Tel: 0400-820-6015

Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

