

# **Power PCB Relay T9V OBC**

- 1 pole 40A, 1 form A (NO) contact
- Contact gap >1.8mm (suffix S)
- 350mW hold power1)
- Ambient temperature up to 85°C at 35A, 105°C at 32A
- The appliance is able to meet VDE V 0126-1-1
- Product in accordance to IEC 60335-1
- EN61095: AC7a at 85°C

Typical applications On board charger Electrical vehicle loading stations Electrical vehicle Photovoltaic inverter

Technical data of approved types on request







Approvals			
VDE 40030974,	UL E58304,	CQC1600214520	3, TUV R50369970

Contact Data	
Contact arrangement	1 form A (NO)
Contact gap	>1.8mm
Rated voltage	277VAC (1.8mm gap)
Rated current	40A <sup>2)</sup>
Breaking capacity max.	10 000 VA
Contact material	AgNi
Initial contact resistance	75mΩ max. at 1A 6VDC or
	$3m\Omega$ max. at $40A$
Fraguency of operation, with/with	thout load 6/200min-1

requericy of operation, with without load	0/30011111
Operate/release time max., incl bounce time	18/15ms

Contact ratings <sup>3)</sup>					
Туре	Contact	Load	Cycles		
IEC 61810					
T9VV1K15-12S	A (NO)	35A, 250VAC, cosφ=1, 85°C	20x10 <sup>3</sup>		
UL 508					
T9VV1K15-12S	A (NO)	35A, 250VAC, resistive, 85°C	20x10 <sup>3</sup>		
T9VV1K15-12S	A (NO)	40A, 30VDC, resistive, 70°C	60x10 <sup>3</sup>		
CQC					
T9VV1K15-12S	A (NO)	40A, 250VAC, resistive, 60°C	20x10 <sup>3</sup>		
TUV					
T9VV1K15-12S	A (NO)	40A, 30VDC, resistive, 70°C	60x10 <sup>3</sup>		
Internal Test					
T9VV1K15-12S	A (NO)	32A, 250VAC, cosφ=1, 105°C	30x10 <sup>3</sup>		

Coil Data		
Rated coil voltage	12VDC	
Coil insulation system according UL	class F	

Coil ver	rsions, DC coil	l			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	W
12	see note 1)	9.6	0.8	64+10%	2.25 /
					min. 0.35
					hold

All figures are given for coil without pre-energization, at ambient temperature +23°C.

Insulation Data	
Initial dielectric strength	
between open contacts	2500V <sub>rms</sub>
between contact and coil	4000V <sub>rms</sub>
Initial surge withstand voltage	
between contact and coil	6kV
Clearance/creepage	
between contact and coil	3/4mm
Initial insulation resistance	
between open contacts	1×10 <sup>9</sup> Ω
between contact and coil	1×10 <sup>9</sup> Ω
Material group of insulation parts	III
Tracking index of relay base	PTI 325

Other	Data	

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature	-40 ~ 85°C/105°C
Cold storage <sup>4)</sup>	240h, -40°C
Dry heat <sup>4)</sup>	240h, +105°C
Temperature cycling (Shock) <sup>4)</sup>	1000cycles, -40/+105°C
Operational Life <sup>4)</sup>	1000hrs, 32A, +105°C
Category of environmental protection	
IEC 61810	RTII – flux proof
	10-40Hz 1.27mm
Vibration resistance (functional) <sup>4)</sup>	40-70Hz 5g
	70-100Hz 0.5mm
	100-500Hz 10g
Shock resistance (functional) <sup>4)</sup>	11ms, up to 30g
Shock resistance (destructive)	
IEC 60068-2-27	100g
Terminal Strength (Leaded)4)	1.13Kg
Terminal type	PCB-THT
Mounting	see note <sup>2)</sup>
Mounting distance	≥10mm
Weight	appr. 30g
Resistance to soldering heat THT <sup>4)</sup>	Tb, method 1A, hot dip 10s,
	260°C with thermal screen
Packaging unit	box/500 pcs.

- Packaging unit box/500 pcs.

  1) Rated voltage: 12VDC. After the energization time of 100ms with 12 VDC the coil requires a reduction of the coil voltage to 4.7...6.0 VDC.
- 2) The relay connections and wiring have to be designed with an adequate cross sections to ensure the current flow and heat dissipation.
- 3) Contact ratings with relay properly vented.
- 4) Refer to AEC-Q200.


Mechanical endurance, DC coil

5x10<sup>5</sup> operations




## Power PCB Relay T9V OBC (Continued)


#### **Dimensions**



#### PCB layout / terminal assignment

Bottom view on solder pins







1 FORM A


#### **Notes**

#### 1) General tolerance

Diagram Dimension	Tolerance		
< 1 mm	±0.1		
1 ~ 3 mm	±0.2		
> 3 mm	±0.3		

### 2) Dimensions of the pins after tin soldering

- a) +0.4 for the width and the thickness
- b) +1.0 for the length



Product code	Version	Contact arrangement	Contact material	Contact gap	Coil	Part Number
T9VV1K15-12S	PCB, flux tight	1 form A (NO) contact	AgNi	>1.8mm	12VDC	2027395-5

Note. This list represents the most common types and does not show all variants covered by this datasheet, other types on request.