


REV. 0  
DCO 143566

COIL: @ 25°C	
RESISTANCE	125 OHMS ±10%
NOMINAL VOLTAGE	6.0 VDC
MUST OPERATE	3.5 VDC
MUST RELEASE	2.0 VDC MAX, 0.28 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE TIME 2.0 MS MAX. RELEASE TIME 4.0 MS MAX. CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING:	LOW LEVEL TO 1A
	28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 22 MAY 02 *EK [Signature]*



CUST. QPL	"J1MAD" RELAY
CUST. NO. M39016/23-014P REV.	

J1MAWD-6XP