




COIL: @ 25°C

RESISTANCE 6500 OHMS $\pm$ 10%

NOMINAL VOLTAGE 32.0 VDC

MUST OPERATE 18.7 VDC

MUST RELEASE 10.6 VDC MAX, 1.59 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX

RELEASE TIME 2.5 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 5/15/97 CK. Jerry C 5/15/97

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M39016/10-045L

TYPE "J1MS" RELAY

J1MSC-32XLS