

SOLISTRAND


TE Internal #: 36865

Rings & Spades, Flag Tongue, 16 – 14AWG Wire Size, 1.04 – 2.62 mm² Wire Size, 2050 – 5180CMA Wire Size, #10, Stud Diameter 5

mm [.197 in]
View on TE.com >



Terminals & Splices > Rings & Spades



Terminal & Splice Type: Flag Tongue

Wire Size: 2050 – 5180 CMA
Ring & Spade Stud Size: #10

Features

Product Type Features

rioduct Type reatures	
Shape Description	RING-091
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support
Configuration Features	
Number of Holes	1
Terminal Angle	Straight
Body Features	
Inspection Slot	No
Weight per Piece	2.064 g
Ring & Spade Plating Material	Copper, Tin
Contact Features	
Terminal & Splice Type	Flag Tongue

Flag

Without

Ring & Spade Terminal Orientation

Mechanical Attachment

Wire Insulation Support



Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	5 mm[.197 in]
Tongue Thickness	1.22 mm[.05 in]
Ring & Spade Overall Length	19.86 mm[.78 in]
Barrel Inside Diameter	2.67 mm[.105 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty No

Industry Standards

Packaging Features

Packaging Quantity	1
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





TE Part #CC2642-000

B-106-4632CS100

TE Part #CC2641-000

B-106-3632CS100



Documents

Product Drawings
SOLIS FLAG RING 16-14 HD 10

English