





REV. 0
DCO 143538


COIL: @ 25°C	
RESISTANCE	255 OHMS ±10%
NOMINAL VOLTAGE	6.0 VDC
MUST OPERATE	3.5 VDC
TURN-ON BASE CURRENT	.20 mADC
MUST RELEASE	2.0 VDC MAX, 0.28 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 3.5 MS MAX.
TURN-OFF TIME 7.5 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 30APR02

[Signature] 5/1/02

CII Technologies
advanced control electronic solutions

CUST. GPL
CUST. NO. M28776/4-018L REV.

"J1MST" RELAY

J1MSW T-6XL