

Power PCB Relay RPII/1

- 1 pole 8/12/16A, 1 form C (CO) or 1 form A (NO) contact
- 4kV/8mm coil-contact
- Pinning 3.5 or 5mm (8/12A) and 5mm (16A)
- RoHS compliant (Directive 2011/65/EC)

Typical applications

Power supplies, domestic appliances, heating control, installation





-0146-B

Approvals
VDE Cert. No. 40025448
UL E214025 (only for AgNi versions

Technical data of approved types on request

Contact Data	8A	12A	16A
Contact arrangement	1 form	C (CO) or 1 form	m A (NO)
Rated voltage		250VAC	
Max. switching voltage		400VAC	
Rated current	8A	12A	16A
Limiting making current,			
max. 4s, df 10%	16A	20A	25A
Breaking capacity max.	2000VA	3000VA	4000VA
Contact material	AgNi0.15	AgNi 90/10	AgNi 90/10
			AgSnO ₂
Frequency of operation, with/witho	ut load	600/36000h ⁻¹	
Operate/release time typ		8/2ms	

Contact	ratings

Bounce time typ., form A/form B

Contact rating	3		
Туре	Contact	Load	Cycles
IEC61810			
RP314/RP714	A (NO)	16A, 250 VAC, resistive, 35°C	100x10 ³
RP314 DC-coil	A (NO)	6A, 250 VAC, $\cos \varphi = 0.4$, 35°C	250x10 ³
RP31L DC-coil	C (CO)	16A, 250 VAC, resistive, 35°C	10x10 ³
RP414 DC-coil	A (NO)	12A, 250 VAC, resistive, 70°C	100x10 ³
RP414 REM	A (NO)	12A, 250 VAC, resistive, 35°C	100x10 ³
RP41N/RP814	C (CO)	12A, 250 VAC, resistive, 35°C	10x10 ³
RP411/RP412	A (NO)	8A, 250 VAC, resistive, 35°C	100x10 ³
RP411/RP412	C (CO)	8A, 250 VAC, resistive, 35°C	10x10 ³
UL61810-1 (for	merly UL50	8)	
RP411/RP412	C(CO)	8A, 250VAC, general purpose, 40°	C 6x10 ³
RP314/RP714	C(CO)	16A, 250VAC, general purpose, 40	°C 6x10 ³
RP314/RP714	C(CO)	250VAC, 1.5HP, 40°C	6x10 ³
RP*14/RP*1N	C(CO)	12A, 250VAC, general purpose, 70	°C 6x10 ³
RP**4/RP**N	A(NO)	10A, 250VAC, resistive, 70°C	100x10 ³

Mechanical endurance

DC-coil version: >20x10⁶ operations REM/bistable version: >1x10⁶ operations

Coil Data	
Coil voltage range	5 to 110VDC
Operative range, IEC 61810	2

Coil vers	sions, DC co	il			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
005	5	3.5	0.5	54	500
006	6	4.2	0.6	68	500
012	12	8.4	1.2	270	500
024	24	16.8	2.4	1100 ¹⁾	500
048	48	33.6	4.8	4400 ¹⁾	500
060	60	42.0	6.0	6540 ¹⁾	500
110	110	77.0	11.0	23100 ¹⁾	500

1) Coil resistance ±15%.

All figures are given for coil without pre-energization, at ambient temperature +20°C. Other coil voltages on request.


Coil versions, REM I (1 coil bistable/remanence)


COII V	Con versions, new r (r con bistable/remailence)								
Coil	Rated	Resistance	e Magnetisation range Demagnetisation rang			isation range			
code	voltage	Ω±15%	MIN./ Vda	MAX./Vdc	MIN./ Vdc	MAX./Vdc			
	VDC								
A12	12	115	9	18	3	4.8			
A24	24	460	18	36	6	9.6			
A48	48	1748	36	72	12	19.2			

Coil versions, REM II (2 coil bistable/remanence)


Coil	Rated	Resistance	Magnetisat	tion range	Demagnetisation range		
code	voltage	Ω±15%	MIN./ Vdc	MAX./Vdc	MIN./ Vdc	MAX./Vdc	
	VDC						
F05	5	20	3.7	7.5	3.7	6	
F12	12	105	9	18	9	14.4	
F24	24	460	18	36	18	28.8	

All figures are given for coil without pre-energization, at ambient temperature +20°C. Other coil voltages on request.





2/4ms






Power PCB Relay RPII/1 (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	1000V _{rms}
between contact and coil	4000V _{rms}
Clearance/creepage	
between contact and coil	≥8/8mm
Material group of insulation parts	Illa

Dimensions Dimensions in mm



Monostable and REM I (REM II version has 3 coil terminals)

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature -40 to +70°C

Category of environmental protection

RTII - flux proof, RTIII - wash tight IEC 61810


Vibration resistance (functional),

10/2g form A/form B, 30 to 300Hz Shock resistance (destructive) 100g Terminal type PCB-THT Weight 18g Resistance to soldering heat THT, IEC 60068-2-20

flux proof version 270°C/10s wash tight version 260°C/5s tube/20 pcs., box/500 pcs. Packaging/unit

PCB layout / terminal assignment

Bottom view on solder pins



Туре RP Power PCB Relay RPII/1 Version 16A, flux proof 16A, wash tight 8/12A, wash tight 8/12A, flux proof 8 Contact arrangement 3 1 form A contact (1 NO) 1 form B contact (1 NC) 1 1 form C contact (1 CO) Contact material and pinning AgNi0.15, 8A, pinning 5mm Discontinued: AgCdO, pinning 5mm²⁾ 0 AgNi 90/10, pinning 5mm AgNi0.15, 8A, pinning 3.5mm 8 Discontinued: AgCdO, 8/12A, pinning 3.5mm²⁾ AgNi 90/10, 12A, pinning 3,5mm AgSnO₂, pinning 5mm Coil Coil code: please refer to coil versions table

2) AgCdO contacts are discontinued and replaced with AgNi contacts (see PCN E-18-003947)

2



Power PCB Relay RPII/1 (Continued)

Product Code	Version	Contacts	Cont. Material	Pinning	Coil Version	Coil	Part Number
RP314005	16A, flux proof	1 form C (CO) contact	AgNi 90/10	5 mm	monostable	5VDC	8-1415546-4
RP314006		, ,	, and the second			6VDC	8-1415546-5
RP314010						10VDC	8-1415546-6
RP314012						12VDC	8-1415546-7
RP314024						24VDC	8-1415546-8
RP314048						48VDC	8-1415546-9
RP314110						110VDC	9-1415546-0
RP314F12					REM II	12VDC	8-1415546-1
RP314F24						24VDC	8-1415546-2
RP31L012			AgSnO ₂		monostable	12VDC	7-1415071-1
RP31L024			0 -			24VDC	8-1415071-1
RP31L048						48VDC	2-1415044-1
RP334012		1 form A (NO) contact	AgNi 90/10			12VDC	9-1415546-1
RP334024						24VDC	9-1415546-2
RP334048						48VDC	9-1415546-4
RP354012		1 form B (NC) contact				12VDC	9-1415546-5
RP411012	8A, flux proof	1 form C (CO) contact	AgNi0.15			12VDC	9-1393230-4
RP411024	, ,	` '	Ü			24VDC	9-1393230-5
RP411048						48VDC	9-1393230-6
RP411060						60VDC	9-1393230-7
RP411110						110VDC	9-1393230-8
RP431012		1 form A (NO) contact				12VDC	4-1393231-5
RP412012		1 form C (CO) contact		3,5 mm		12VDC	1-1393231-1
RP412024						24VDC	1-1393231-2
RP412F12					REM II	24VDC	1393231-6
RP414012	12A, flux proof	1 form C (CO) contact	AgNi 90/10	5 mm	monostable	12VDC	1415547-4
RP414024						24VDC	1415547-5
RP414A24					REM I	24VDC	9-1415546-6
RP414F24					REM II	24VDC	9-1415546-7
RP41N024				3,5 mm	monostable	24VDC	1-1415547-7
RP434024		1 form A (NO) contact		5 mm		24VDC	9-1415546-3
RP43N024				3,5 mm		24VDC	7-1415547-0
RP45N024		1 form B (NC) contact				24VDC	7-1415547-1
RP714006	16A, wash tight	1 form C (CO) contact		5 mm		6VDC	9-1415546-8
RP714012						12VDC	9-1415546-9
RP714024						24VDC	1415547-1
RP714048						48VDC	1415547-2
RP734012		1 form A (NO) contact				12VDC	1415547-6
RP734020						20VDC	1415547-7
RP734024						24VDC	1415547-8
RP734036						36VDC	1415547-9
RP734A12					REM I	12VDC	1415547-3
RP814012	12A, wash tight	1 form C (CO) contact			monostable	12VDC	1-1415547-0
RP814024						24VDC	1-1415547-1
RP814048						48VDC	1-1415547-2

Note. This list represents the most common types and does not show all variants covered by this datasheet. Other types on request.