


COIL: @ 25°C  
 RESISTANCE 50 OHMS ± 10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 2.7 VDC  
 MUST RELEASE 1.4 VDC MAX. 0.22 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX  
RELEASE TIME 4.0 MS MAX  
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
1A 28 VDC RESISTIVE 100,000  
OPERATIONS

DR. R.B. 10/30/96 CK *[Signature]* 10/30/96



CUST. QPL  
 CUST. NO. M39016/15-130L

TYPE JMAD RELAY

**JMACD-5XLS2**