


The RT9420 provides rotational position feedback via 4...20 mA current loop signal. This device combines the superb linearity and resolution of a plastic-hybrid potentiometer and the durability of our 4...20mA circuit to provide an accurate and reliable electrical signal. Additionally the zero and span settings are adjustable through access holes in the housing.

This innovative sensor is designed to meet NEMA-4 and IP67 standards, is available in full stroke ranges of 1/4 to 50 turns.



\*Optional 3-wire, 0...20mA output signal available.

# **RT9420**

Rotation Position Sensor Industrial • 4..20 mA • 0..20mA

**Absolute Rotary Position to 50 turns** 

**Aluminum or Stainless Steel Enclosure Options** 

IP68 / NEMA 6 • Hazardous Area Certification

#### **GENERAL**

Full Stroke Range Options 0-0.25 to 0-50 turns

Output Signal Options 4...20 mA (2-wire) and 0...20 mA (3-wire)

Accuracysee ordering informationRepeatability± 0.05% full strokeResolutionessentially infinite

**Enclosure Material Options** powder-painted aluminum or stainless

steel

Sensor plastic-hybrid precision potentiometer

Potentiometer Cycle Life see ordering information

**Shaft Loading** up to 35 lbs. radial and 5 lbs. axial

Weight, Aluminum Enclosure 5 lbs. max.
Weight, Stainless Steel Encl. 10 lbs. max.

## **ELECTRICAL**

Input Voltage see ordering information

**Input Current** 20 mA max.

Maximum Loop Resitance (Load) (loop supply voltage - 8)/0.020

Circuit Protection 38 mA max.

Impedence 100M ohms@100 VDC, min.

**Output Signal Adjustment** 

**Zero Adjustment** from factory set zero to 50% of full stroke

range

**Span Adjustment** to 50% of factory set span

Thermal Effects, Zero 0.01% f.s./°F, max. Thermal Effects, Span 0.01% f.s./°F, max.

#### **EMC COMPLIENCE PER DIRECTIVE 89/336/EEC**

Emission/Immunity EN50081-2/EN50082-2

## **ENVIRONMENTAL**


Enclosure NEMA 4/4X/6, IP 67/68

Operating Temperature -40° to 200°F (-40° to 90°C)

Vibration up to 10 g to 2000 Hz maximum

SENSOR SOLUTIONS /// RT9420 PAGE 1

#### **Outline Drawing:**



- #8-32 x 0.180 @ 90° apart on a 4.15 in. dia. BC (4 places)
  mounting holes for 6-mm shaft diameter option
- M4 x 4,5 mm @ 90° apart on a 105,4 mm dia. BC (4 places)

  1 reference mark
- g reference mark full counter-clockwise position - align mark on shaft to mark on face for start of measurement range

DIMENSIONS ARE IN INCHES [MM] tolerances are  $\pm 0.02$  in.  $[\pm 0.5 \text{ mm}]$  unless otherwise noted

## **Ordering Information:**

#### **Model Number:**



Sample Model Number:

RT9420 - 0005 - 111 - 1110

R range:

A enclosure: aluminum

shaft diameter:
output signal:
electrical connection:

.25 inches

4...20 mA signal increasing clockwise 6-pin plastic connector

5 turns (clockwise shaft rotations)

**Full Stroke Range:** 

<b>R</b> <u>order code:</u>	R125	0R25	0R50	0001	0002	0003	0005	0010	0020	0030	0050
clockwise shaft rotations, min:	0.125	0.25	0.50	1	2	3	5	10	20	30	50
accuracy (% of f.s.):	0.3%	0.3%	0.3%	0.3%	0.3%	0.3%	0.2%	0.15%	0.15%	0.15%	0.15%
potentiometer cycle life*:	2.5 x 10 <sup>6</sup>	5 x 10 <sup>5</sup>	2.5 x 10 <sup>5</sup>								

<sup>\*–</sup>number of times the sensor shaft can be cycled back and forth from beginning to end and back to the beginning before any measurable signal degradation may occur.


## **Enclosure Material:**

↑ order code:

1 powder-painted aluminum


2 303 stainless steel

## **Shaft Diameter:**




# **Ordering Information (cont.):**

## **Output Signals:**



\*IMPORTANT: intrinsically safe when powered from a CSA certified zener barrier rated 28 VDC max, 110 mA max per installation drawing#677984





Notes: 


\* -Test pressure: 100 feet [30 meters] H<sub>2</sub>O (40 PSID); Test Medium: Air; Duration: 2 hours.

\*\* -NEMA 4X applies to stainless steel enclosure only.

\* –14-32 VDC for hazardous area option.

### **Output Signal Selection:**

The output signal direction can be reversed at any time by simply changing the dip-switch settings found on the internal signal board. After the settings have been changed, adjustment of the Zero and Span trimpots will be required to precisely match signal values to the beginning and end points of the stroke.



#### **NORTH AMERICA**

Measurement Specialties, Inc. a TE Connectivity Company

20630 Plummer Street Chatsworth, CA 91311 Tel +1-800-423-5483 Tel +1-818-701-2772 Fax +1-800-701-2799

customercare.chtw@te.com

#### te.com/sensorsolutions

Measurement Specialties Inc. a TE Connectivity company

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/ or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.