

Relay Package SNR

- Relay package consisting of DIN-rail socket and relay
- 1 CO with 6 A rated load
- Module width only 6.2 mm
- Reduced system width for increased packing density on the DIN rail

A	n	n	ro	va	al	ç
$\overline{}$	~	v			-	×

Relay: VDE Cert. No. 40010063, cULus E214025, cCSAus 2148326

Socket: VDE Cert. No. 40010063, cULus E224918

Technical data of approved types on request

For contact ratings see datasheet Slim interface Relay SNR

Comtact Data				
Contact Data				
Contact configuration	1 CO			
Contact set	single contact			
Type of interruption	micro disconnection			
Rated voltage/max. switching voltage	e AC 240/40	0 VAC		
Rated current	64	4		
Maximum breaking capacity AC	1500	VA		
Limiting breaking capacity,				
max. 4 s, duty factor 10%	10A			
Contact material	AgSnO ₂	AgSnO ₂		
		gold plated		
Minimum contact load	100mA, 12V	50mW		
Rated frequency of operation				
with/without load	6 /1200) min ⁻¹		
Operate/release time	max 12 / 5 ms			
Bounce time NO/NC contact	max 3 / 8 ms			
Contact ratings				
For contact ratings see datasheet	Slim interface	Relay SNR		


Input data							
Rated input voltage DC	12, 24 VDC, 115, 230 VAC/VDC*)						
Operative range to IEC 61810	2						
*) Version 115, 230 VAC/VDC equipped with 60 VDC relay							

Coil versions, DC coil

Coil	Rated	Operate	Release	Coil	Rated coil				
code	voltage	voltage	voltage	resistance	power				
	VDC	VDC	VDC	Ω±10%	mW				
LB2	12	8.4	0.6	848	184				
LC4	24	16.8	1.2	3390	220				
Coil vers	Coil versions, AC coil 50 Hz								
Coil	Rated	Operate	Release	Coil	Rated coil				
code	voltage	tage voltage voltage resistance		power					
	VAC	50 Hz	50 Hz	Ω	50 Hz				
		VAC	VAC		mVA				
SM5	115	82.0	9.0	not applicable	403				
TP0	230	160.0	15.0	not applicable	736				

Other coil voltages on request.






Dielectric strength		
coil-contact circuit	400	OV_{rms}
open contact circuit	100	00V _{rms}
Clearance /creepage coil-contact circuit	≥6/	' 8 mm
Material group of insulation parts		lla
Insulation to IEC 60664-1		
Type of insulation coil-contact circuit	rein	forced
open contact circuit	micro dis	connection
Rated insulation voltage	25	50 V
Pollution degree	3	2
Rated voltage system	240 V	230 / 400 V
Overvoltage category		III




Relay Package SNR (Continued)

Other Data				
Mechanical endurance	10x10 ⁶ cycles			
Material compliance: EU RoHS/ELV, C	China RoHS, REACH, Halogen content			
refer to the P	roduct Compliance Support Center at			
www.te.com	n/customersupport/rohssupportcenter			
Environment				
Ambient temperature range	-40+55°C			
Processing				
Terminals	screw			
Terminal screw torque acc. IEC 619	984 0.5 Nm			
max.	0.6 Nm			
Wire cross section				
single wire	0.142.5 mm ²			
fine wire	0.142.5 mm ²			
with bootlace crimp (DIN 46228)	/1) 0.142.5 mm ²			
Insertion cycles	A (10)			
Max. Insertion Force total	100 N			
Mounting distance	≥ 0 mm, dense packing of sockets			
Weight	32 g			
Packaging unit	10 pcs			

Accessories	
For accessories see datasheet	Accessories Slim Interface Relay SNR





Product code structure	Typical product code	ST	3P	3	TP0
Туре					
ST Relay Package SNR					
Version			_		
3P Relay set, SNR 1-pole CO (1 form C), 6 A,	screw terminals				
Contact material					
2 AgSnO ₂ , gold plated 3	AgSnO ₂				
Coil	-				
LB2 12 VDC L	C4 24 VDC				
SM5 115 VDC/VAC T	P0 230 VDC/VAC				

Product code	Socket	Terminals	Relay	Contacts	Coil	Part Number
ST3P2LC4	ST3FLC4	screw	V23092-S1024-A201	AgSnO ₂ gold pl.	24VDC	3-1416100-0
ST3P3LB2			V23092-S1012-A301	AgSnO ₂	12VDC	3-1416100-1
ST3P3LC4			V23092-S1024-A301		24VDC	3-1416100-2
ST3P3SM5	ST3FSM5		V23092-S1060-A301		115VDC/VAC	3-1416100-3
ST3P3TP0	ST3FTP0				230VDC/VAC	3-1416100-4