





REV. 0
DCO 143286

COIL: @ 25°C
 RESISTANCE 98 OHMS $\pm$ 10%
 NOMINAL VOLTAGE 6.0 VDC
 MUST OPERATE 3.5 VDC
 MUST RELEASE 2.0 VDC MAX, 0.28 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX
 RELEASE TIME 4.0 MS MAX
 CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
 1A 28 VDC RESISTIVE 100,000
 OPERATIONS

DR. B.D. 10/30/01 CK *[Signature]*

CII Technologies
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/15-101P REV.

"JMCD" RELAY

JMCD-6XPS