

REV. 0


DCO 141254

COIL: @ 25°C	
RESISTANCE	1560 OHMS \pm 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	15.2 VDC
MUST RELEASE	9.5 VDC MAX, 1.8 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX
 RELEASE TIME 4 MS MAX
 CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 8/11/99 CK: JEP/C 8/11/99



CUST. QPL
 CUST. NO. M39016/20-054M REV.

'JMADD' RELAY

JMACDD-26XM