


COIL: @ 25°C
 RESISTANCE 98 OHMS ± 10%
 NOMINAL VOLTAGE 6.0 VDC
 MUST OPERATE 3.5 VDC
 MUST RELEASE 2.0 VDC MAX, 0.28 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX
RELEASE TIME 4 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/6/97 CK *[Signature]* 3/6/97

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/15-029L

TYPE JMAD RELAY

JMAWD-6XL