




REV. 0
DCO 140794

COIL: @ 25°C
RESISTANCE 39 OHMS ± 10%
NOMINAL VOLTAGE 5.0 VDC
MUST OPERATE 3.2 VDC
MUST RELEASE 2.3 VDC MAX, 0.6 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX
RELEASE TIME 4 MS MAX
CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 12/11/98 [Signature]

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M39016/20-007P

TYPE 'JMADD' RELAY

JMAWDD-5XP