


REV. 0  
DCO 142851

COIL: @ 25°C	
RESISTANCE	390 OHMS ±10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	7.0 VDC
MUST RELEASE	4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES: OPERATE TIME 2.0 MS MAX	
RELEASE TIME 15 MS MAX	
CONTACT STABILIZATION 2.5 MS MAX	

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 4/3/01 CK. Jerry 4/3/01

**CII Technologies**  
advanced control electronic solutions

CUST. QPL  
CUST. NO. M39016/17-040M REV.

JMGA RELAY

JMGAC-12MW