

REV. 0

DCO 144078

COIL: @ 25°C	1560 OHMS ±10%
RESISTANCE	_____
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.2 VDC
_____	_____
MUST RELEASE	8.0 VDC MAX., 1.37 VDC MIN.


ENVIRONMENT:

VIBRATION	10 Hz	TO	3000 Hz	@	30 g's
SHOCK	75 g's		6 MS. DURATION		
TEMPERATURE	-65 °C	TO	+125 °C		

NOTES:

OPERATE TIME	2.0 MS MAX
RELEASE TIME	1.5 MS MAX
CONTACT BOUNCE	1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 16AUG2005

CK. JERRY C. 8/16/05

CII Technologies™
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/17-042L REV. _____

"JMGA" RELAY

JMGAC-26LW