


REV. 0
DCO 143503

COIL: @ 25°C	
RESISTANCE	39 OHMS ±10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	3.2 VDC
MUST RELEASE	2.3 VDC MAX, 0.6 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE TIME 2.0 MS MAX
	RELEASE TIME 4.0 MS MAX
	CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 8 APR 02

CK. *[Signature]* 4/8/02

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/19-037L REV.

"JMGADD" RELAY

JMGACDD-5LW