



MODEL 45007

High Temp Glass NTC Thermistor

- Superior Long Term Stability
- Glass hermetic Seal
- Use up to 250°C
- 5000 ohm Resistance @ 25°C
- Interchangeable $\pm 0.2^\circ\text{C}$, 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- Thermally conductive epoxy coating
- 32 AWG, 3" (7.6 cm) long Gold plated Dumet leads
- RoHS Compliant

FEATURES

- Glass Hermetic Seal
- 5000 Ohm Resistance @ 25°C
- Interchangeability
- Excellent High Temperature Performance
- Superior Long Term Stability
- High Sensitivity
- Thermally Conductive Epoxy Coating
- RoHS Compliance

APPLICATIONS

- High Moisture Applications
- Low to Mid Range Temperature Applications
- Tight Tolerance Instrumentation
- Applications Requiring Excellent Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments
- Allows use in Applications World-wide


MODEL 45007

High Temp Glass NTC Thermistor

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C	Ohms	5000
Tolerance 0°C to 70°C	°C	± 0.2
Beta Value 25/85	K	3978
Tolerance on Beta Value	%	0.8
Time response in air	Seconds	< 2.5
Dissipation Constant in air	mW/°C	10
Insulation Resistance (Min. of 100 Mohms for 1 sec.)	Volts	500

MECHANICAL DETAILS



RESISTANCE VS. TEMPERATURE TABLE

Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms
-55	482.200	-13	32.630	29	4.204	71	0.8464	113	0.2351
-54	447.900	-12	30.880	30	4.029	72	0.8183	114	0.2287
-53	416.300	-11	29.230	31	3.861	73	0.7912	115	0.2226
-52	387.100	-10	27.670	32	3.702	74	0.7651	116	0.2167
-51	360.200	-9	26.210	33	3.549	75	0.7400	117	0.2109
-50	335.300	-8	24.830	34	3.404	76	0.7159	118	0.2053
-49	312.300	-7	23.540	35	3.266	77	0.6927	119	0.1999
-48	291.000	-6	22.320	36	3.134	78	0.6703	120	0.1947
-47	271.300	-5	21.170	37	3.008	79	0.6488	121	0.1896
-46	253.000	-4	20.080	38	2.888	80	0.6281	122	0.1847
-45	236.200	-3	19.060	39	2.773	81	0.6082	123	0.1799
-44	220.500	-2	18.100	40	2.663	82	0.5889	124	0.1753
-43	205.900	-1	17.190	41	2.559	83	0.5704	125	0.1708
-42	192.500	0	16.330	42	2.459	84	0.5526	126	0.1664
-41	180.000	1	15.520	43	2.363	85	0.5354	127	0.1622
-40	168.300	2	14.750	44	2.272	86	0.5188	128	0.1581
-39	157.500	3	14.030	45	2.184	87	0.5028	129	0.1541
-38	147.500	4	13.340	46	2.101	88	0.4874	130	0.1503
-37	138.200	5	12.700	47	2.021	89	0.4726	131	0.1465
-36	129.500	6	12.090	48	1.944	90	0.4582	132	0.1429
-35	121.400	7	11.510	49	1.871	91	0.4444	133	0.1394
-34	113.900	8	10.960	50	1.801	92	0.4310	134	0.1360
-33	106.900	9	10.440	51	1.734	93	0.4182	135	0.1326
-32	100.300	10	9.951	52	1.670	94	0.4057	136	0.1294
-31	94.220	11	9.486	53	1.608	95	0.3937	137	0.1263
-30	88.530	12	9.046	54	1.549	96	0.3821	138	0.1232
-29	83.220	13	8.628	55	1.493	97	0.3709	139	0.1203
-28	78.260	14	8.232	56	1.439	98	0.3601	140	0.1174
-27	73.620	15	7.857	57	1.387	99	0.3497	141	0.1146
-26	69.290	16	7.500	58	1.337	100	0.3396	142	0.1119
-25	65.240	17	7.162	59	1.290	101	0.3298	143	0.1092
-24	61.450	18	6.841	60	1.244	102	0.3204	144	0.1067
-23	57.900	19	6.536	61	1.200	103	0.3113	145	0.1042
-22	54.580	20	6.247	62	1.158	104	0.3025	146	0.1018
-21	51.470	21	5.972	63	1.117	105	0.2940	147	0.0994
-20	48.560	22	5.710	64	1.079	106	0.2857	148	0.0971
-19	45.830	23	5.462	65	1.0410	107	0.2778	149	0.0949
-18	43.270	24	5.225	66	1.0060	108	0.2701	150	0.0927
-17	40.860	25	5.000	67	0.9711	109	0.2626		
-16	38.610	26	4.787	68	0.9380	110	0.2554		
-15	36.490	27	4.583	69	0.9063	111	0.2484		
-14	34.500	28	4.389	70	0.8757	112	0.2416		

MODEL 45007

High Temp Glass NTC Thermistor

ORDERING INFORMATION

Model Number	Description	Ω @25°C	MOQ
090043	45007 THERMISTOR	5,000	100
091533	45007-BP (100 PCS) THERM	5,000	100

* For quantities less than Minimum Order Quantity – contact distribution

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.tlse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.