


REV. 0  
DCO 142387

COIL: @ 25°C	
RESISTANCE	50 OHMS ±10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	2.7 VDC
MUST RELEASE	1.4 VDC MAX, 0.22 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 2.0 MS MAX
	RELEASE TIME 4.0 MS MAX
	CONTACT STABILIZATION TIME 2.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 10/12/00 CK. TEG 10-12-00

**II CII Technologies**  
advanced control electronic solutions

CUST. QPL  
CUST. NO. M39016/18-049P REV.

JMGAD RELAY

JMGACDG-5PW