



## KISSLING MICRO SWITCH

Series MZX1/MZT1/MZN1

### Quality Switch

Our MZW1 KISSLING micro switches have been specifically designed for mission critical applications with extended environmental requirements in a centrally controlled miniature housing.

These high quality micro switches are precise and display both reliable and consistent switching behavior under the harshest conditions and over product lifespans of 10 million cycles. The switch has a load switching range from 0.1A up to 10A (AC). The housings are made of thermoplastic and are sealed up to IP67 depending on the configuration. This switch is also available in a modified version for special applications of up to 300°C.

This series offers high switching security, since in operation the moving contact is activated in a cross traverse with respect to the fixed contact. This movement provides automatic self cleaning of the main contact surface and inhibits welding or sticking. These switches are intended to be used in extreme environmental conditions.

### Features


- 1- and 2-pole switches available
- Nominal load up to 10A at 250VAC
- Min. switching current 10mA at 12VDC
- Switching frequency up to 200 cycles/min.
- Variety of available actuator geometries and sizes
- High quality silver alloy or gold plated contacts
- Dimensions according to DIN 41635 Form A

### Applications


- Automotive equipment
- General mechanical engineering
- Appliance and industrial engineering
- Medical equipment
- Commercial vehicles

### Switching function


#### Change-over



#### NO



#### NC



# KISSLING MICRO SWITCH

Series MZX1/MZT1/MZN1

## Specification

### Technical Data

Housing Material	Thermoplast GF
Interior protection / Protection terminals	IP 40 IEC 60529 / IP00 IEC 60529
Positive action operation (MZT)	Similar DIN EN IEC 60 947-3


### Mechanical Data (Change-over)

Pre-travel	0.5mm - 1.1mm
Overtravel	> 1mm
Movement differential	0.05mm - 0.3mm
Operating force	Class 2: 1N - 1.5N   Class 3: 1.5N - 3N   Class 4: 3N - 4.5N
Release force	Class 2: > 0.6N   Class 3: > 1N   Class 4: > 1N
Max operating force	< 10N
Current carrying parts	CuZn-alloy
Contact material	Silver alloy or gold plated contacts
Mechanical life	10 Mio.
Frequency	200/min
Operating speed in direction of plunger	max. 0.5m/sec
Temperature range	-40°C to +85°C
Temperature range (special ecition)	-55°C to +300°C

### Electrical data

Nominal voltage	250VAC, 24VDC
Continuous current	10.1A
Min. switching capacity	12VDC, 10mA

## Technical drawings




# KISSLING MICRO SWITCH

Series MZX1/MZT1/MZN1


## Actuators

### Switch actuator




02	MZX1 / MZT1		
Class	2	3	4
OF	1.0-1.5	1.5-3.0	3.0-4.5
P mm		0.5-1.1	
O mm		> 1	
MD mm		0.05-0.3	

### Short lever




04	MZX1 / MZT1	
Class	3	4
OF	1.5-3.0	3.0-4.5
P mm		0.5-1.1
O mm		> 1
MD mm		0.05-0.3

### Long lever




05	MZX1 / MZT1	
Class	3	4
OF	0.5-1.4	1.4-2.5
P mm		1.0-2.5
O mm		> 2
MD mm		0.1-0.7

### Lever with angle cam




07	MZX1 / MZT1	
Class	3	4
OF	1.0-2.2	2.2-4.0
P mm		0.6-1.5
O mm		> 1
MD mm		0.05-0.4

### Long lever




12	MZX1 / MZT1	
Class	3	4
OF	0.25-0.5	0.5-1.0
P mm		2.1-4.0
O mm		> 0.8
MD mm		0.3-1.2

### Short lever with roller Ø 5




30	MZX1 / MZT1	
Class	3	4
OF	0.35-0.8	0.8-1.3
P mm		1.5-2.5
O mm		> 0.8
MD mm		0.3-1

### Short lever with roller Ø 5



36	MZX1 / MZT1	
Class	3	4
OF	1.5-3.0	3.0-4.5
P mm		1.5-1.1
O mm		> 1
MD mm		0.05-0.3

### Lever with roller Ø 5



37	MZX1 / MZT1	
Class	3	4
OF	0.5-1.4	1.4-2.5
P mm		1.0-2.5
O mm		> 0.8
MD mm		0.1-0.7

Roller material plastic, optional material brass or steel

#### Description:

OF = Operating force

O = Overtravel

P = Pretravel


MD = Movement differential

# KISSLING MICRO SWITCH


Series MZX1/MZT1/MZN1

## Connection types


Solder Connection




Solder Connection




Screw terminals M2.6




FASTON terminals 2.8 x 0.8




FASTON terminals 6.3 x 0.8



Screw terminals M3



## Ordering Information



### Series

<b>X</b>	Snap switch
<b>T</b>	Snap switch with positive action
<b>N</b>	Main disconnecting switch

### Actuator

<b>__</b>	Select on page 3
-----------	------------------

### Switching function

<b>1</b>	Change-over
<b>2</b>	NO
<b>3</b>	NC

### Connection types

<b>02</b>	Solder Connection 2.5
<b>04</b>	Solder Connection 6.2
<b>05</b>	Screw terminals M 2.6
<b>06</b>	FASTON terminals 2.8 x 0,8
<b>08</b>	FASTON terminals 6.3 x 0.8
<b>09</b>	Screw terminals M3

### Class

<b>2</b>	select on page 3
<b>3</b>	select on page 3
<b>4</b>	select on page 3

## te.com

TE Connectivity, TE, TE connectivity (logo), FASTON and KISSLING (word) are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity | All Rights Reserved.

K1166737 | Version 08/2020