



Technische Daten

Polzahl	11
Leistung	5 (4+PE)
Signal	6
Temperaturbereich	-20 °C bis 130 °C
Schutzart	gesteckt IP 66/67

Elektrische Daten

*Bemessungsstrom	30A	Signal	max. 1,2 A
Bemessungsspannung	850 V (DC) 630 V (AC)		50 V (DC) 30V(AC)
Bemessungsstoßspannung (L-L)	6000 V		1500 V

Steckzyklen	500
-------------	-----

Werte nach VDE 0110/EN 61984, Abschnitt 6.19.2.2

Verschmutzungsgrad	3
Überspannungskategorie	III
Aufstellhöhe	bis 2000 m

Werkstoffe

Gehäuse	Zinkdruckguß, chromatiert
Isolierkörper	PA 6.6 mod., UL 94/ V0
Dichtungen	FKM



Kontakte (nicht im Lieferumfang enthalten)

Werkzeuge (nicht im Lieferumfang enthalten)

digitale Crimpzange für
1mm Kontakte (für 0,14mm²-1,0mm²)
2mm Kontakte (für 0,34mm²-2,5mm²)
Locator für digitale Crimpzange


Best Nr.: C0.235.00

Best Nr.: C0.265.00




Hauptabmessungen

Einbaudose




Polbild

Buchse, Code 1
Ansicht Steckseite



Hauptabmessungen

Flansch



Montagefenster



Technical Data

number of pins	11
power	5 (4+PE)
signal	6
temperature range	-20 °C bis 130 °C
protection class	IP 66/67 when connected

Electrical Data

*rated current	30A	Power	max. 1,2 A	Signal	max. 1,2 A
rated voltage	850 V (DC) 630V(AC)		50V(DC) 30V(AC)		1500V
rated insulation voltage (L-L)	6000 V				

mating cycles	500
---------------	-----

Data According to VDE 0110/EN 61984, Paragraph 6.19.2.2

pollution degree	3
overvoltage category	III
max. operating altitude	2000 m



Material

housing	zinc diecast, chromated
insulation insert	PA 6.6 mod., UL 94/ V0
sealing	FKM


Contacts (not part of product contents)

Tools (not part of product contents)


digital crimping tool	order code: C0.235.00
1mm contacts (014mm ² -1,0mm ²)	
for 2mm contacts (0,35mm ² -2,5mm ²)	
locator for digital crimping tool	order code: C0.265.00




Main Dimensions
receptacle



Contact Arrangement
mating view, socket Code 1



Main Dimensions
receptacle



Mounting Hole

Copyright by Intercontec Produkt GmbH, Germany.
All rights, including rights created by patent grant or registration
of a utility model or design, are reserved.
Noncompliance will result in seeking damages.
This document is for information only and before utilization
the user must reconfirm actuality.
Subject to technical changes.

INTERCONTEC Produkt GmbH
Bernriederstraße 15, 94559 Niederwinkling
Tel.: 0049 9962/ 2002-0, Fax: 0049 9962/ 2002-70
E-Mail: info@intercontec.biz
Web: www.intercontec.biz

* for max. wire cross-section