



FEP HEAT SHRINK TUBING

APPLICATIONS

- Process aid for reflowing catheter shafts
- Process aid for joint bonding
- Abrasion protection / strain relief

PROFILE

- Shrink ratio $\leq 1.6:1$
- Full recovery at 210°C (410°F) minimum
- Tight longitudinal change control as low as 0 to 4%
- Custom sizing, finishing options available
- Translucent for high optical clarity

ABOUT

- FEP is a fluorinated ethylene propylene (FEP) heat shrink tubing. FEP offers excellent consistency, high dielectric strength and is chemically inert. FEP is lubricious and semi-rigid with shrink ratios up to 2:1*. FEP is the industry gold standard for reflowing catheter shafts and bonding joints
- For our FEP, we can control longitudinal growth as low as 0 to 4% ensuring consistency on lot-to-lot, reducing waste and cost

*Upper limit on select applications. Optimal shrink ratio is 1.6:1

HEAT SHRINK TUBING — FEP

TABLE 1: DIMENSIONS

Standard Sizes	As Supplied		Recovered							
	Inside Diameter (D) Minimum		Inside Diameter (d) Maximum		Wall Thickness (in., mm.) (W)					
					Minimum		Maximum		Nominal	
Size	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
1/32	0.031	0.79	0.02	0.5	0.007	0.18	0.009	0.23	0.008	0.2
3/64	0.047	1.19	0.03	0.762	0.007	0.18	0.009	0.23	0.008	0.2
1/16	0.063	1.59	0.039	0.99	0.0085	0.22	0.0115	0.29	0.01	0.25
3/32	0.094	2.38	0.056	1.42	0.0085	0.22	0.0115	0.29	0.01	0.25
1/8	0.125	3.18	0.075	1.91	0.0085	0.22	0.0115	0.29	0.01	0.25
3/16	0.188	4.76	0.115	2.92	0.0085	0.22	0.0115	0.29	0.01	0.25
1/4	0.25	6.35	0.15	3.81	0.0105	0.27	0.0135	0.34	0.012	0.3
3/8	0.375	9.53	0.225	5.72	0.0135	0.34	0.0165	0.24	0.015	0.38
1/2	0.5	12.7	0.313	7.95	0.0135	0.47	0.0165	0.55	0.015	0.51

*Denotes lot acceptance test

Note 1: Sample preparation and extraction is per USP XXII. Metals analysis may be colorimetric as described in USP XXII or by equivalent quantitative analytical method.

TE.com/medical

TE Connectivity, TE connectivity (logo), Raychem and TE are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2024 TE Connectivity. All Rights Reserved.

11/24 med-mt-feb-hst-ss-en

