


P2 Relay V23079

- Standard telecom relay (ringing and test access)
- Slim line 15x7.5mm (.590x.295")
- Max. Switching current 2A
- 2 form C bifurcated contacts (2 changeover contacts, 2 CO)
- Immersion cleanable
- High sensitivity for low power consumption 140mW/ 70mW

Typical applications

Communications equipment linecard application (ringing and test access), PABX, voice over IP, office equipment, measurement and control equipment, automotive equipment as CAN bus, keyless entry, speaker switch, medical equipment, consumer electronics, set top boxes, HiFi



Approvals

UL61810-1 (former UL508) No. 214025
Technical data of approved types on request

Contact Data


| | |
|--------------------------------------|--|
| Contact arrangement | 2 form C (CO) |
| Max. switching voltage | 220VDC, 250VAC |
| Rated current | 2A |
| Limiting continuous current, 85°C | 2A |
| Switching Power | 60W, 62.5VA |
| Contact material | AgNi, gold-covered |
| Contact style | bifurcated contact |
| Minimum switching voltage | 100µV |
| Thermoelectrical potential | <10µV |
| Initial contact resistance | <50mΩ at 10mA, 20mV |
| Frequency of operation, without load | 50 operations/s |
| Operate time | typ. 2ms, max. 4ms |
| Set/reset time | typ. 2ms, max. 4ms |
| Release time | |
| without diode in parallel | typ. 2ms, max. 4ms |
| with diode in parallel | typ. 4ms, max. 6ms |
| Bounce time | typ. 1ms, max. 3ms |
| Electrical endurance | |
| at 12V / 10mA | typ. 5x10 ⁷ operations |
| at 6V / 100mA | typ. 1x10 ⁷ operations |
| at 60V / 500mA | typ. 5x10 ⁵ operations |
| at 30V / 1000mA | typ. 1x10 ⁶ operations |
| at 30V / 2000mA | typ. 2x10 ⁵ operations |
| at 12V / 5000mA / 25°C | typ. 1x10 ⁵ operations |
| Contact ratings, UL | 110VDC / 0.3A - 33W 30VDC / 2.0A - 60W 120VAC / 0.5A - 60VA 240VAC / 0.25A - 60VA 125VAC / 1A NO Side 125VDC / 0.5A NO Side |
| Mechanical endurance | typ. 10x10 ⁶ operations |

| | |
|-----------------------|------------|
| Magnetic system | polarized |
| Coil voltage range | 2 to 24VDC |
| Max. coil temperature | 105°C |
| Thermal resistance | < 125K/W |


Coil versions, monostable

| Coil code | Rated voltage VDC | Operate voltage VDC | Limiting Voltage VDC | Release voltage VDC | Coil resistance Ω±10% | Rated coil power mW |
|-----------|-------------------|---------------------|----------------------|---------------------|-----------------------|---------------------|
| 008 | 3.00 | 2.25 | 6.50 | 0.30 | 64 | 140 |
| 016 | 4.00 | 3.00 | 8.70 | 0.40 | 114 | 140 |
| 011 | 4.50 | 3.38 | 9.80 | 0.45 | 145 | 140 |
| 001 | 5.00 | 3.75 | 10.90 | 0.50 | 178 | 140 |
| 002 | 6.00 | 4.50 | 13.00 | 0.60 | 257 | 140 |
| 006 | 9.00 | 6.75 | 19.60 | 0.90 | 578 | 140 |
| 003 | 12.00 | 9.00 | 26.15 | 1.20 | 1029 | 140 |
| 005 | 24.00 | 18.00 | 52.30 | 2.40 | 4114 | 140 |

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



Coil Data



P2 Relay V23079 (Continued)

Coil Data (continued)


Coil versions, bistable

| Coil code | Rated voltage VDC | Set voltage VDC | Limiting Voltage VDC | Reset voltage VDC | Coil resistance $\Omega \pm 10\%$ | Rated coil power mW |
|-------------------------|-------------------|-----------------|----------------------|-------------------|-----------------------------------|---------------------|
| Bistable, 1 coil | | | | | | |
| 108 | 3.00 | 2.25 | 9.2 | -2.25 | 128 | 70 |
| 111 | 4.50 | 3.38 | 13.85 | -3.38 | 289 | 70 |
| 101 | 5.00 | 3.75 | 15.33 | -3.75 | 357 | 70 |
| 102 | 6.00 | 4.50 | 18.5 | -4.50 | 514 | 70 |
| 106 | 9.00 | 6.75 | 27.75 | -6.75 | 1157 | 70 |
| 103 | 12.00 | 9.00 | 37 | -9.00 | 2057 | 70 |
| 105 | 24.00 | 18.00 | 74 | -18.00 | 8228 | 70 |

Bistable, 2 coil

| | | | | | | |
|-----|-------|-------|-------|-------|------|-----|
| 219 | 2.00 | 1.50 | 4.33 | 1.50 | 28 | 140 |
| 218 | 2.40 | 1.80 | 5.2 | 1.80 | 41 | 140 |
| 208 | 3.00 | 2.25 | 6.5 | 2.25 | 64 | 140 |
| 211 | 4.50 | 3.38 | 9.8 | 3.38 | 145 | 140 |
| 201 | 5.00 | 3.75 | 10.9 | 3.75 | 178 | 140 |
| 202 | 6.00 | 4.50 | 13 | 4.50 | 257 | 140 |
| 206 | 9.00 | 6.75 | 19.6 | 6.75 | 578 | 140 |
| 203 | 12.00 | 9.00 | 26.15 | 9.00 | 1029 | 140 |
| 205 | 24.00 | 18.00 | 52.3 | 18.00 | 4114 | 140 |


All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



Coil versions, high dielectric version, monostable, overmolded

| Coil code | Rated voltage VDC | Operate voltage VDC | Limiting Voltage VDC | Release Voltage VDC | Coil resistance $\Omega \pm 10\%$ | Rated coil power mW |
|-----------|-------------------|---------------------|----------------------|---------------------|-----------------------------------|---------------------|
| 008 | 3.00 | 2.25 | 6.1 | 0.30 | 45 | 200 |
| 001 | 5.00 | 3.75 | 10.1 | 0.50 | 125 | 200 |
| 002 | 6.00 | 4.50 | 12.1 | 0.60 | 180 | 200 |
| 006 | 9.00 | 6.75 | 18.2 | 0.90 | 405 | 200 |
| 003 | 12.00 | 9.00 | 24.2 | 1.20 | 720 | 200 |

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.



Insulation Data

| | Standard | HDV |
|---|-----------------------|----------------------|
| Initial dielectric strength | | |
| between open contacts | 1000V _{rms} | 1500V _{rms} |
| between contact and coil | 1500V _{rms} | 1500V _{rms} |
| between adjacent contacts | 1000 V _{rms} | 1500V _{rms} |
| Initial surge withstand voltage | | |
| between open contacts | 2000V | 2500V |
| between contact and coil | 2500V | 2500V |
| between adjacent contacts | 2500V | 2500V |
| between open contacts | 2000V | 2500V |
| between contact and coil | 2500V | 2500V |
| between adjacent contacts | 2500V | 2500V |
| Initial insulation resistance at 500 Vdc | | |
| | > 10 ⁹ Ω | |
| Capacitance | | |
| between open contacts | max. 1pF | |
| between contact and coil | max. 2pF | |
| between adjacent contacts | max. 1.5pF | |
| Clearance /creepage | | |
| | 1.3/2.5mm | |

Other Data


| | |
|---|---------------------------------------|
| Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customer-support/rohssupportcenter | |
| Ambient temperature | -40 to +85°C |
| Category of environmental protection IEC 61810 | RT III - wash tight |
| Vibration resistance (functional) | 35g, 10 to 1000Hz |
| Shock resistance (functional) IEC 60068-2-27 (half sine) | 100g |
| Terminal type | PCB-THT, SMT long and short terminals |
| Weight | max. 2.8 g |
| Resistance to soldering heat THT IEC 60068-2-20 | 265°C/10s |
| Moisture sensitive level, JEDEC J-Std-020E | MSL3 |
| Related to SMT relays and THT relays packed in reel | |
| Ultrasonic cleaning | not recommended |
| Packaging/unit | |
| THT | tubes/2000 pcs. |
| THT | reel/1500 pcs. |
| SMT | reel/2000 pcs. or 2500 pcs. |

P2 Relay V23079 (Continued)

Terminal assignment


TOP view on component side of PCB

Monostable version




ECR0912-C

Bistable version, 1-coil



ECR0912-C

Bistable version, 2-coils




ECR0913-K

Contacts are shown in reset condition.
Both coils can be used as either set or reset coils.
Contact position might change during transportation and must be reset before use.

PCB layout


TOP view on component side of PCB

THT version




ECR0856-X

SMT, long terminals




P2 SMT L Layout

SMT, short terminals




Dimensions


Overmolded coil, high dielectric version
THT version



SMT, long terminals





SMT, short terminals




P2 Relay V23079 (Continued)

Processing




Packing

THT-tubes




Reel dimensions




P2 Relay V23079 (Continued)


SMT - LONG TERMINALS



SMT - SHORT TERMINALS



THT - REEL



P2 Relay V23079 (Continued)

| | | | | | | | | | | | | | | | | | | |
|--|--|--|--|---------------|----------|----------|------------|----------|------------|---------------------------|--|---------------------------------------|---------------------------------|--|---|--------------------------------|---|--|
| Product code structure | | Typical product code | | V23079 | A | 2 | 001 | B | 301 | | | | | | | | | |
| Type | | V23079 Signal Relay P2 Series | | | | | | | | | | | | | | | | |
| Version | | <table border="0"> <tr> <td>A THT, monostable</td> <td>D SMT, monostable, long term.</td> <td>G SMT, monostable, short term.</td> </tr> <tr> <td>B THT, latching, 2 coils</td> <td>E SMT, latching, 2 coils long term.</td> <td>H SMT, latching, 2 coils short term.</td> </tr> <tr> <td>C THT, latching, 1 coil</td> <td>F SMT, latching, 1 coil long term.</td> <td>J SMT, latching, 1 coil short term.</td> </tr> </table> | | | | | | | | A THT, monostable | D SMT, monostable, long term. | G SMT, monostable, short term. | B THT, latching, 2 coils | E SMT, latching, 2 coils long term. | H SMT, latching, 2 coils short term. | C THT, latching, 1 coil | F SMT, latching, 1 coil long term. | J SMT, latching, 1 coil short term. |
| A THT, monostable | D SMT, monostable, long term. | G SMT, monostable, short term. | | | | | | | | | | | | | | | | |
| B THT, latching, 2 coils | E SMT, latching, 2 coils long term. | H SMT, latching, 2 coils short term. | | | | | | | | | | | | | | | | |
| C THT, latching, 1 coil | F SMT, latching, 1 coil long term. | J SMT, latching, 1 coil short term. | | | | | | | | | | | | | | | | |
| Coil design | | <table border="0"> <tr> <td>2 Overmolded coil</td> </tr> <tr> <td>1 Overmolded coil (not available for new design)</td> </tr> </table> | | | | | | | | 2 Overmolded coil | 1 Overmolded coil (not available for new design) | | | | | | | |
| 2 Overmolded coil | | | | | | | | | | | | | | | | | | |
| 1 Overmolded coil (not available for new design) | | | | | | | | | | | | | | | | | | |
| Coil | | Coil code: please refer to coil versions table | | | | | | | | | | | | | | | | |
| Version | | <table border="0"> <tr> <td>B Standard version</td> </tr> <tr> <td>X Special version (High dielectric, THT packed in reel)</td> </tr> </table> | | | | | | | | B Standard version | X Special version (High dielectric, THT packed in reel) | | | | | | | |
| B Standard version | | | | | | | | | | | | | | | | | | |
| X Special version (High dielectric, THT packed in reel) | | | | | | | | | | | | | | | | | | |
| Contacts for standard versions | | 301 2 form C contacts (2 CO), AgNi +Au | | | | | | | | | | | | | | | | |
| Contacts for dielectric versions | | 07* 2 form C contacts (2 CO), AgNi +Au | | | | | | | | | | | | | | | | |
| Packing | | X1** THT version packed in reel | | | | | | | | | | | | | | | | |

* any digit

| Product code | Version | Coil design | Coil type | Coil voltage | Part number |
|-------------------|--------------------|-----------------|-------------------|--------------|-------------|
| V23079-A2008-B301 | THT | Overmolded | Monostable | 3VDC | 6-1419120-6 |
| V23079-A2011-B301 | | | | 4.5VDC | 3-1393789-9 |
| V23079-A2001-B301 | | | | 5VDC | 3-1393789-5 |
| V23079-A2002-B301 | | | | 6VDC | 3-1393789-6 |
| V23079-A2006-B301 | | | | 9VDC | 3-1393789-8 |
| V23079-A2003-B301 | | | | 12VDC | 3-1393789-7 |
| V23079-A2005-B301 | | | | 24V | 1-1422025-0 |
| V23079-A2016-B301 | | | | 4V | 1393790-3 |
| V23079-B2219-B301 | | | Bistable, 2 coils | 2VDC | 1-1422002-2 |
| V23079-B2218-B301 | | | | 2.4VDC | 1-1422002-1 |
| V23079-B2208-B301 | | | | 3VDC | 1-1422002-0 |
| V23079-B2201-B301 | | | | 5VDC | 1422002-9 |
| V23079-B2211-B301 | | | | 4.5VDC | 1-1422002-7 |
| V23079-D2008-B301 | SMT, long pins | Overmolded | Monostable | 3VDC | 4-1393789-7 |
| V23079-D2011-B301 | | | | 4.5VDC | 4-1393789-8 |
| V23079-D2001-B301 | | | | 5VDC | 4-1393789-3 |
| V23079-D2002-B301 | | | | 6VDC | 4-1393789-4 |
| V23079-D2006-B301 | | | | 9VDC | 4-1393789-6 |
| V23079-D2003-B301 | | | | 12VDC | 4-1393789-5 |
| V23079-D2016-B301 | | | | 4VDC | 1393790-4 |
| V23079-E2219-B301 | | | Bistable, 2 coils | 2VDC | 1422007-6 |
| V23079-E2201-B301 | | | | 5VDC | 1422007-7 |
| V23079-E2206-B301 | | | | 9VDC | 6-1422008-9 |
| V23079-E2208-B301 | | | | 3VDC | 1422007-8 |
| V23079-E2218-B301 | | | | 2.4VDC | 1422007-9 |
| V23079-E2211-B301 | | | | 4.5V | 1-1422007-6 |
| V23079-G2008-B301 | SMT, short pins | | Monostable | 3VDC | 5-1393789-4 |
| V23079-G2016-B301 | | | | 4VDC | 1393790-5 |
| V23079-G2011-B301 | | | | 4.5VDC | 5-1393789-5 |
| V23079-G2001-B301 | | | | 5VDC | 4-1393789-9 |
| V23079-G2002-B301 | | | | 6VDC | 5-1393789-0 |
| V23079-G2006-B301 | | | | 9VDC | 5-1393789-3 |
| V23079-G2003-B301 | | | | 12VDC | 5-1393789-1 |
| V23079-G2008-X079 | | High dielectric | | 3VDC | 1422006-5 |
| V23079-G2001-X071 | | Overmolded | | 5VDC | 1422006-1 |
| V23079-G2002-X072 | | | | 6VDC | 1422006-2 |
| V23079-G2006-X073 | | | | 9VDC | 1422006-3 |
| V23079-G2003-X074 | | | | 12VDC | 1422006-4 |
| V23079-A2003-X074 | THT | | | 12VDC | 1422025-7 |
| V23079-A2008-X079 | | | | 3VDC | 1-1422025-1 |
| V23079-A2008-X101 | THT packed in reel | Overmolded | | 3VDC | 6-1419170-9 |
| V23079-A2011-X102 | | | | 4.5VDC | 3-1393790-1 |
| V23079-A2001-X103 | | | | 5VDC | 3-1393790-2 |
| V23079-A2002-X104 | | | | 6VDC | 3-1393790-3 |
| V23079-A2006-X105 | | | | 9VDC | 3-1393790-4 |
| V23079-A2003-X106 | | | | 12VDC | 3-1393790-5 |
| V23079-B2219-X107 | | | Bistable, 2 coils | 2VDC | 1-1422003-0 |
| V23079-B2218-X108 | | | | 2.4VDC | 1-1422003-1 |
| V23079-B2208-X109 | | | | 3VDC | 1-1422003-2 |
| V23079-B2201-X110 | | | | 5VDC | 1422003-3 |

Note:

1. Not shown part numbers upon request.
2. All product with coil design 1 produced before 01/2023 contain the old standard coil design.