


REV. 0
DCO 140882

COIL: @ 25°C
 RESISTANCE _____ 50 OHMS ± 10%
 NOMINAL VOLTAGE _____ 5.0 VDC
 MUST OPERATE _____ 2.7 VDC
 MUST RELEASE _____ 1.4 VDC MAX, 0.22 VDC MIN.

ENVIRONMENT:
 VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: OPERATE TIME _____ 2.0 MS MAX
 RELEASE TIME _____ 4.0 MS MAX
 CONTACT STABILIZATION _____ 2.0 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/3/99 *CK* *ERR* 2/3/99



CUST. _____ C. I. I.
 CUST. NO. _____ COTS STD.

TYPE 'PRMGAD' RELAY

PRMGAPD-5Y