


COIL: @ 25°C
 RESISTANCE 400 OHMS ± 10%
 NOMINAL VOLTAGE 9.0 VDC
 MUST OPERATE 4.85 VDC
 MUST RELEASE 3.0 VDC MAX, 0.55 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX
RELEASE TIME 7.5 MS MAX
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. R.B. 7/16/98 *(Signature)* 7/16/98

COMMUNICATIONS INSTRUMENTS, INC.

CUST. TELEDYNE
 CUST. NO. ER134D-9A

TYPE PRMGSD RELAY

PRMGSCD-9X