



intercontec
products

623 Stecker

EMV-Schirmung
Gehäuse Code 1

TE Teile Nr.: A S A 000 N 00 40 0235 000
IC Ref. Nr.: A ST A 000 NN 00 40 0235 000



Technische Daten

Temperaturbereich -20 °C bis 130 °C
Kabelklemmbereich ø9,0 mm - ø13,2 mm
Schutzart gesteckt IP 66/67

Steckzyklen 500

Werkstoffe

Gehäuse Zinkdruckguss, vernickelt
Klemmring Messing, vernickelt
Dichtungen FKM



Hauptabmessungen

Stecker

© 2020 TE Connectivity.

Y6-C740-000-0DE
TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz





intercontec
products

623 Plug

EMC-Shielding
Housing Code 1

TE part number: A S A 000 N 00 40 0235 000
IC reference number: A ST A 000 NN 00 40 0235 000



Technical Data

temperature range -20 °C bis 130 °C
clamping range $\varnothing 9,0$ mm - $\varnothing 13,2$ mm
protection type IP 66/67 when connected

mating cycles 500

Material

housing zinc diecast, nickel plated
clamp ring brass, nickel plated
seals FKM



Main Dimensions

plug

© 2020 TE Connectivity

Y6-C740-000-0EN issued: 30.03.2020/HE; TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz

