



PSD 40-15

Dual Rail DC Power Supply

SPECIFICATIONS

- ✦ **±15 VDC outputs**
- ✦ **1 AMP continuous output current**
- ✦ **DIN rail mount for easy installation**
- ✦ **Rugged design**
- ✦ **UL listed** (including for hazardous environments)
- ✦ **CE certified**
- ✦ **RoHS compliant**

The PSD 40-15 switching power supply is designed for optimum operation of our DC sensors including our DC LVDTs, RVDTs, RVITs and Gage Heads. As the current capability is 1A continuous, it can operate multiple sensors. The compact design features a DIN standard rail mount, for secure installation in most industrial environments.

FEATURES

- ✦ 115/230 VAC input
- ✦ 45 to 65Hz input frequency
- ✦ Low noise output
- ✦ Overload and short circuit protection

The PSD 40-15 has the following UL approvals:

- ✦ UL/C-UL listed UL 508
- ✦ UL/C-UL Recognized UL 60950
- ✦ UL/C-UL Listed UL 1604 Class I, Division 2, Groups A, B, C, D

APPLICATIONS

- ✦ Use with our DC position sensors
- ✦ DIN rail or chassis mount applications
- ✦ Multiple sensor applications


PERFORMANCE SPECIFICATIONS

Input		Output	
Input Voltage	85 to 264 VAC	Output Voltage	±15 VDC ±1%
Input Frequency	45 to 65 Hertz	Output Current	1 Amp continuous
Input current at 120VAC	600mA maximum	Ripple	<30mV peak to peak
Input current at 230VAC	400mA maximum	Overload protection	Internal fuse
		Short circuit protection	Internal fuse
Other			
Operating temperature	-25°C to +70°C	Storage temperature	-40°C to +85°C
Weight	250 grams	Conductor cross-section	2.5 mm ² maximum

PSD 40-15

Dual Rail DC Power Supply

DIMENSIONS



Dimensions are in inch [mm]

ORDERING INFORMATION

Description	Part Number
PSD 40-15, Dual Rail DC Power Supply	02291339-000

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Phone +1-800-522-6752
Email: customercare.pens@te.com

EUROPE

MEAS Deutschland GmbH(Europe)
a TE Connectivity Company
Phone: +49-800-440-5100
Email: customercare.dtmd@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Phone: +86-400-820-6015
Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Accustar, American Sensor Technologies, AST, ATEXIS, DEUTSCH, IdentiCal, TruBlue, KPSI, Krystal Bond, Microfused, UltraStable, Measurement Specialties, MEAS, Schaevitz, TE, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.