




The PT1A is perfect where space and money are limited. The PT1A is part of Celesco's compact line of cable-extension transducers. Using a high cycle plastic-hybrid potentiometer, the PT1A provides a precision voltage divider position feedback signal for fullscale measurement ranges from 2 to 50 inches.

The PT1A has many features to offer including 500 to 10K ohm potentiometer selection, adjustable bridge circuit and multiple measuring cable exit options.



PT1A

Cable Actuated Sensor Instrument Grade • Voltage Divider Output Absolute Linear Position to 50 inches (1270 mm)

Aluminum and Polycarbonate Enclosure

Compact Design

IP65 • NEMA 4 Protection

General

Full Stroke Range Options	0-2 to 0-50 inches
Output Signal Options	voltage divider (potentiometer)
Accuracy	\pm 0.25% to \pm 0.15% full stroke (see ordering information)
Repeatability	± 0.02% full stroke
Resolution	essentially infinite
Measuring Cable	.019-in. dia. nylon-coated stainless steel
Enclosure	glass-filled polycarbonate and black anodized aluminum
Sensor	plastic-hybrid precision potentiometer
Potentiometer Cycle Life	see ordering information
Maximum Retraction Acceleration	see ordering information
Weight	1 lb. max.


Electrical


Input Resistance	see ordering information
Options	
Power Rating, Watt	see ordering information
Recommended	see ordering information
Maximum Input Voltage	
Output Signal Change	94% ±4% of input voltage
Over Full Stroke Range	

Environmental

Enclosure	NEMA 4, IP 65
Operating Temperature	-40° to 200°F (-40° to 90°C)
Vibration	up to 10 g to 2000 Hz maximum

Outline Drawing






DIMENSIONS ARE IN INCHES [MM] tolerances are 0.03 IN. [0.5 MM] unless otherwise noted.

Ordering Information

Model Number:



Full Stroke Range:

4 places \	<	
2.75 [69,9]		
0.38 [9,5]→		0.91 [23]
	0.170 [4,32] –	
	 ← 2.33 [59,1] → ↓ 3.85 [97,8] 	0.09 [2,2]

Ø.20 [5,1]


Α

* tolerance = +.005 -.001 [+.13 -.03] ** tolerance = +.005 -.005 [+.13 -.13]

Sample Model Number: PT1A - 30 - UP - 500 - MC4 - SG 30 inches R range: measuring cable exit:
 up B output signal: 500-ohm pot. electrical connection: 4-pin micro connector Ď cable guide: spring-loaded guide

B _order code:	2	5	10	15	20	25	30	40	50
full stroke range, min:	2 in.	5 in.	10 in.	15 in.	20 in.	25 in.	30 in.	40 in.	50 in.
accuracy (% of f.s.):	0.2	5%		0.15%				0.10%	
potentiometer cycle life:	2,500,00	00 cycles	500,000 cycles					250,000 cycle	s
cable tension (20%):	12 oz.	5 oz.	12 oz.	9 oz.	6 oz.	5 oz.	9 oz.	6 oz.	5 oz.
max. cable acceleration:	11 g	3 g	11 g	5 g	4 g	3 g	5 g	4 g	3 g

Cable Exit:



Output Signals:


B <u>order code:</u>	500	1K	5K	10K	AB
	500 ohm*	1000 ohm*	5000 ohm*	10,000 ohm*	adjustable bridge
				$tolerance = \pm 10\%$	(030 mV/V)
	max. input voltage a	and power rating, options:	500, 1K, 5K, 10K		
		2-inch, 5-inch range	10-inch to 50-inch range		
	500-ohms:	20 V AC/DC (1 W)	30 V AC/DC (2 W)		
	1K to 10K-ohms:	30 V AC/DC (1 W)	30 V AC/DC (2 W)		
	circuit	options: 500, 1K, 5K, 10K		tion: AB (adjustable bridg	
	value by or	+in P I specified wercode		+in full scale out 1K zero adjust: +out -out -out zero 500	put: adjustable from 0 to 30mV/ to 50% of full stroke
	+0	put common	cable reinaction	1K ^H 976	

-in

Electrical Connection:

🕞 order code:	der code: MC4 4-pin micro-connector with 12 ft [3.5 M] cordset 1.2 in. [31 mm]				M6 6-pin plastic connector with mating plug 3.0 in. [78 mm]					C25				
										25-ft. instrumentation cable 24 AWG, shielded				
			1							1	<u>+</u>			
12 ft. x 5/16-in. dia. [3,5 M x 8 mm dia.] yellow PVC jacket shielded, 22 AWG [31 mm]			.30 – .39 in. [8 – 10mm] cable dia. 16 AWG max conductor size connector: MS3102E-145-6P mating plug: MS3106E-14S-6S						25 fL x 0.2-in. dia. [7,5 M x 5 mm dia.] 24 AWG, shielded					
4-pin mating plug and cord set:					6-pin mating plug:				25-ft. cable:					
		in color code 1 RED-BLK TR. 2 RED-WHT TR. 3 RED 4 GREEN	standard +IN COMMON +OUT -	bridge +IN -IN +OUT -OUT		(B) (F) (C) (C) (C) (C) (C) (C) (C) (C) (C) (C	pin A B C D	standard +IN COMMON +OUT -	bridge +IN -IN -OUT +OUT		color code RED BLACK GREEN WHITE	standard +IN COMMON +OUT -	bridge +IN -IN +OUT -OUT	

Cable Guide:



*note: start of full stroke range begins at full compression point (except 2-inch and 5-inch ranges).

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity company 20630 Plummer Street Chatsworth, CA 91311 Tel +1 800 423 5483 Tel +1 818 701 2750 Fax +1 818 701 2799 info@celesco.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

PT1A 12/01/2015