




# CDFP CAGES, CONNECTORS & CABLE ASSEMBLIES

## 400 GBPS PLUGGABLE I/O



CDFP Style 1 & 2 cages on representative PCIe card

### DESIGN FOR FASTER SPEEDS

- 400 Gbps per port, among the highest density ports in the input/ output (I/O) market today
- Transfers data at up to 28 Gbps per lane, supporting current and next generation Ethernet and PCIe networking protocols

### MAXIMIZE EFFICIENT USE OF SPACE

- 16 lanes of bi-directional data communication in one port and one cable assembly, the highest number of lanes per port of an I/O form factor on the market
- 0.75mm contact pitch

### SIMPLE, WORRY-FREE CONNECTIONS

- Pre-assembled, one-piece press-fit connector and cage design simplifies assembly with one-step placement on the board
- EMI springs provide plug to receptacle containment and shield from external interference

### FLEXIBILITY TO FIT YOUR DESIGN

- Connector and cage design allows you to choose the thermal management options that are best suited for your application
- Support both direct attach copper and active optical interfaces
- Double cable exit allows for increased flexibility for assembly routing
- Customized cabling options available

### APPLICATIONS

- Routers
- High Performance Computing
- Storage
- Controller Cards & Servers
- NIC Cards & GPUs

One of the highest port and bandwidth densities of any pluggable I/O on the market to support current and next generation proprietary or industry standard high speed designs.

## TWO STYLES OF CAGES

- **Style 1** (shorter cage body)
  - Supports direct attach copper
  - Includes EMI gasket
- **Style 2** (longer cage body)
  - Support direct attach copper and active optical modules
  - Includes EMI springs
  - TE offers a style 2 cage optimized for PCIe applications
- Styles 1 and 2 modules and cages are different mating depths and are not intermateable with each other
- Styles 1 and 2 have the same electrical pinout as defined in the CDFP MSA specification



Connector with Style 1 cage



Connector with Style 2 cage



Style 2 cable assembly

## STYLE 2 CABLE ASSEMBLIES

- Double cable exit allows for increased flexibility for assembly routing
- 30 AWG cable with 7.9mm OD
- Up to 2.0M cable reach
- Customized cabling options available - contact your TE representative

## STYLE 2 CABLE ASSEMBLIES

- Application spec: 114-32114
- Product spec: 108-32065

## ORDERING INFORMATION

Description	Part Number
CDFP Style 1 Receptacle & Cage Assembly	2291931-1
CDFP Style 2 Receptacle & Cage Assembly	2274233-1
CDFP Style 2 Receptacle & Cage Assembly Optimized for PCIe	2311882-1
CDFP Seating Tool Kit	2215034-1
CDFP Style 2 Cable Assembly, 0.5M	2327779-1
CDFP Style 2 Cable Assembly, 1.0M	2327779-2
CDFP Style 2 Cable Assembly, 1.5M	2327779-3
CDFP Style 2 Cable Assembly, 2.0M	2327779-4

Custom cable assemblies available. Contact your TE representative for more information.

## te.com

TE Connectivity, TE and TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. CDFP is part of the ZXP® family of connectors and uses ZXP technology. ZXP is a trademark of Molex, LLC. Other logos, products and company names mentioned herein may be trademarks of their respective owners.

© 2023 TE Connectivity. All Rights Reserved.

12/23

## KEY FEATURES

- CDFP compliant form factor connector, cage and cable assembly
- 16x25 Gbps electrical interface = 400 Gbps total port bandwidth
- 0.75mm pitch, 120 contact pins, dual row paddle card interface
- Connector and cage are provided as an integrated assembly
- Press-fit assembly of connector to host PCB; fasteners secure cage assembly
- Cage materials
  - Housing: nickel plated zinc alloy
  - EMI springs: copper alloy
  - EMI gasket: silver plated urethane
- Connector materials
  - Plastic housing: LCP, UL 94V rated
  - Contacts: phosphor bronze