



SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION





TERMINAL DATA:	DELPHI PACKAF	R D	TERMI	NALTE CR	IMP SP	ECIFIC	ATION			
TERMINAL NAME: 2.8 RECEPTACLE TERMINAL										
WIRE STRIP LI	ENGTH 📑	IV	NSULATION	DIAME	TER RAN	NGE				
3.33-4.09 mm [.131161 [N]	\emptyset 1	Ø1.50-2.40 mm [.059094 IN]							
TERMINAL APPLICATION	NONE			-		-				
SPECIFICATION	-			-		-				
TERMINALS APPLIED 12										
TE TERMINAL	DELPHI PACKARD TERM	INAL	T E	TERMINAL	DELPHI	PACKARD	TERMINAL			
2318371-1	33501244									

TYPE

WIRE SIZE 😸 🔭	CRIMP HEIGHT mm [INCH]	CRIMP HEIGHT 9 REFERENCE SETTING
1.00mm2	1.26+/-0.05 [.050+/002]	6.7
18 AWG	1.19+/-0.05 [.047+/002]	7.9
0.75mm2	1.12+/-0.05 [.044+/002]	8.7
20 AWG OR 0.50mm2	1.08+/-0.05 [.043+/002]	9.0
22 AWG OR 0.30mm2	0 98+/-0 05 [039+/- 002]	100

1 RECOMMENDED SPARE PARTS

APPLICATOR DATA

SIZE

WIRE 1.78 mm [.070]
INSUL 3.56 mm [.140]

APPL INSTRUCTIONS
408-10390

CRIMP

2 GREASE BEARING SURFACES LIGHTLY

3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

APPLICATOR SPECIFIC DATA TO BE ENTERED INTO BLANK MEMORY CHIP AT ASSEMBLY. SEE BELOW FOR PART NUMBER:

MECHANICAL FEED WITH "SMART APPLICATOR" CONVERSION: 8-2150837-4
PNEUMATIC FEED WITH "SMART APPLICATOR" CONVERSION: 8-2150837-4
SERVO FEED WITH "FINE CRIMP HEIGHT ADJUST": 8-2150837-5

5. ADJUSTMENT OF THE STRIPPER MAY BE REQUIRED WHEN MOVING THE APPLICATOR BETWEEN BENCH AND LEADMAKER APPLICATIONS.

APPLY PART NUMBER 1-23419-5 LOCTITE TO THREADS OF ITEMS 62 & 180. APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.

GREASE THREADS, GROOVE AND O-RING ON ITEMS 139 & 153.

MAGNET, ITEM 166 MUST BE ORIENTED CORRECTLY IN ORDER TO PROPERLY ACTUATE THE COUNTER.

CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.

SPARE FEED CAM STORAGE LOCATION REFER TO INSTRUCTION SHEET FOR ADDITIONAL INFORMATION.

THE RECOMMENDED SET-UP FOR END FEED APPLICATORS IS POST-FEED WITH ITEM 2119653-1. THE APPLICATOR CAN BE CONFIGURED FOR PRE-FEED WITH ITEM 2119652-1 BUT MAY ENCOUNTER PROBLEMS WITH SOME APPLICATIONS. FEED ISSUES OR TERMINAL JAMMING MAY OCCUR IN THE PRE-FEED CONFIGURATION.

TERMINAL LUBRICANT IS RECOMMENDED.

*WARNING
ON INSTALLATION, SET WIRE DISC, ITEM 40 TO
LARGEST WIRE SIZE SETTING. USE OF SETTINGS
BELOW MINIMUM REQUIRED CRIMP HEIGHT SETTING
WILL CAUSE DAMAGE TO CRIMP TOOLING.

_	1	1	1	1	2119782-1	FINE ADJUST HEAD ASM, PACIFIC STYLE	251
_	-	_	1	-	2119640-1	PUSH ROD, AIR FEED	250
_	_	_	1	-	1803259-1	BUSHING, FLANGED	249
_	1	1	1	1	1 - 22279 - 3	SPRING, COMPRESSION	246
_	1	1	1	1	2119082-7	CAM, SNAIL, INSULATION ADJUSTMENT	244
_	1	1	1	1	2079764-1	WASHER, WAVE SPRING, CREST-TO-CREST	243
- 77	- 27	- 25	- 22	- 21	PART NO	DESCRIPTION	I T E M N O

PACIFIC VERSION

Shown on sheets 3 of 4 & 4 of 4 (Atlantic version shown on sheets 1 of 4 & 2 of 4)

			211	9599	- 2		DESCRIPTION DATE	DWN APVD
						- 5	SEE SHEET 1 -	
6 -	-	1	1	1	1	2119083-1	RETAINER, INSULATION DIAL	242
_	-	-	2	_	_	2168400-7	SHCS, LOW HEAD, ROHS, M5 X 10	240
_	-	-	_	-	1	2119580-1	MECHANICAL FEED ASSEMBLY	239
_	_	_	_ 	_	_	2063440-1	AIR FEED MODULE TAG, IDENTIFICATION	238
_	-	4	4	4	4	2079383-9	SCR, BHSC, RoHS (M6 X 20)	186
_	-	- F	REF	_	_	1901697-1	FEED FINGER ASSEMBLY, EF	183
\	-	1	1	1	1	1752354-1	STANDOFF, HOLD-DOWN	180
_	-	1	1	1	1	6 - 9 9 3 1 1 1 - 6	PIN, SLOTTED SPRING 3.0 X 14.0	177
_	-	1	1	1	1	8-22280-7	SPRING, COMPRESSION	176
_		1	1	1	1	1752353-2	GUIDE PIN, HOLDDOWN	175
_		_		2	_	1901680-2	GUIDE PIN, HOLDDOWN RING, RETAIN, EXTERN, 3/16 CRESCENT	172
_	-	1	1	1	1	994969-1	MAGNET, RARE EARTH HIGH ENERGY	166
-	- R	EFF	REF	REF	REF	994970-2	COUNTER, MAGNETIC	164
_	-	-	-	1	_	240638-1	SPRING, FEED FINGER	163
_	-	1	1	1	1	8 - 2 1 0 8 4 - 1	O-RING, .801 ID, .070 DIA. MAT.	153
_	-	-		1	_	2119641-2	FEED CAM, AIR FEED	152
_	-	1	1	1	1	2119798-2	DETENT PIN	1 4 5
-	-	_	_	_	1	2079383-8	SCR, BHSC, ROHS (M4 X 16) FEED CAM, POST FEED	1 4 4
_	-	1	1	1	1	2119655-6	APPLICATOR BASIC ASSEMBLY, EF	1 4 1
-	-	1_	1	1	1	2119651-1	RAM, ASIAN STYLE, END FEED	1 4 0
_	-	1	1	1	1	2119092-2	BOLT, ADJUSTMENT	139
_		-	<u>-</u>	1	-	3-23627-7	PIN, RETAIN, GRVD, 3/16 X .854	137
_	_	-	<u> </u>	_	_	SEE NOTE 4 1633743-1	MEMORY CHIP, PROGRAMMED SERVO FEED LATCH ASM	135
<u>} </u>	-	1	1	1	1	2119955-2	ASSY, LUBRICATOR, END FEED	133
_	-	1	1	1	1	455888-5	SPACER, CRIMPER	82
_	-	1_	1_	1_	1_	2119956-2	DOCUMENTATION PACKAGE	7 1
-	-	2	2	2	2	2 - 18032 - 2	SCR, SET, FLT PNT, M3 X 10.0	70
_	-	1	-	1	1	2119740-1	TAG, IDENTIFICATION	6.7
_	-	2	2	2	2	2168078-1 1901681-5	SCREW, DRIVE, RH, ROHS, 2 x .188 HOLDDOWN, TERMINAL	66
_	-	2	2	2	2	2168400-5	SHCS, LOW HEAD, ROHS, M4 X 20	6 4
_	-	1	1	1	1	2119793-1	LIMITER, ADJUSTMENT BOLT	63
_	-	3	3	3	3	992763-5	SCR, SET, SOC, CONE PNT, M3 x 4.0	62
_	-	-	-	-	1	5-18022-5	SCR, HEX HD CAP, M4 X 6.0	59
_	-	-	-	-	7	2063961-1	FEED FINGER	58
_	-	3 2	3	3	3	2168400-4	SHCS, LOW HEAD, ROHS, M4 X 8 SCR, SKT HD CAP, ROHS, M4 X 8.0	57
_	-	2	2	2	2	5018030-1	NUT, HEX, REG, ROHS, M3	54
_	-	2	2	2	2	986965-8	NUT, LOCK, HEX, TORQUE (M4)	53
_	-	1	1	1	1	1 - 5018030 - 0	NUT, HEX, REG, RoHS, M3.5	52
_	-	-	-	1	-	2119792-2	PAWL, EF, AIR	51
	-	-	_	1	2	18023-9	SCR, SKT HD CAP M4 X 6.0	49
_	-	1	1	1	1	2119652-1 2079383-7	FEED CAM, PRE FEED SCR, BHSC, RoHS (M8 X 25)	48
_	-	1	1	1	1	2119645-1	DISC, NUMBERED FA WIRE ADJUSTMENT	40
-	-	1	1	1	1	2119957-1	APPLICATOR SHIM PACK	39
_	-	1	1	1	1	1 - 2 1 1 9 6 4 4 - 2	RAM WASHER, PRECISION	38
_	-	7	7	7	7	1-18028-2	WASHER, FLAT, REG M4	3 3
-	-	2	2	2	2	2168083-9	SCR, SKT HD CAP, ROHS, M4 X 20 SCR, SKT HD CAP, ROHS, M4 X 10	31
-	-	1	1	1	1	240639-1	STRIPPER (MACHINING)	27
-	-	2	2	2	2	1-2168083-5	SCR, SKT HD CAP, RoHS, M4 X 30	25
_	-	1	1_	1_	1_	1-1752371-8	PLATE, STRIP GUIDE	2 4
_	-	1	1	1	1	240825-1	PLATE, STRIP HOLD DOWN	23
_	-	2	2	2	2	2-22281-3	SPRING, COMPRESSION	22
-	-	7	<u>1</u> 2	2	2	1803292-4 1901259-5	DRAG GUIDE, LOWER STRIP	20
-	-	1	1	1	1	1752360-1	SPACER, HOLD-DOWN	1 3
_	-	1	1	1	1	240833-1	PLATE, REAR SHEAR	1 1
	-	_		-	_		-	10
	- [1	1	1	1	690482-1	PLATE, FRONT SHEAR	9
$\frac{1}{1}$		1	1	1	1	3-1803257-7	ANVIL, COMBINATION, END FEED	8 7
	-	_		_	_	2217206-2	BLADE, SLUG	6
-	-	1	1	1	1	240641-8	SPACER	5
_	-	1_	1	1	1	238009-1	BLOCK, FL CRIMPER SPACER	4
L		1	1	1	1	2-1633961-3	CRIMPER, INSULATION F PREMIUM	3
1	-	1	1	1	1	455888-3	SPACER, CRIMPER	2
1			1			3-456404-4	CRIMPER, WIRE PREMIUM	ITEM
1 -		_ [- 25	- 22		PART NO	DESCRIPTION	NO
					CTRONICS CO	REPORATION DWN 31AUG	TE Connectivity	
				LING ENGIN	VISION.	M. ZIIAO	20171	
1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	IS A CONT T TO CHAN SHOULD BE	TROLLED DO NGE AND TH E CONTACTE	OCUMENT FO HE CONTROL ID FOR THE			CHK 31AUG	The state of the s	
DRAWING IS IS SUBJECT SI	IS A CONT T TO CHAN SHOULD BE	TROLLED DO NGE AND TH E CONTACTE	OCUMENT FO HE CONTROL ID FOR THE	TOLERAI DTHER W IS		CHK 31AUG	2017 NAME Ocean End Feed	
DRAWING IS IS SUBJECT SI	IS A CONT T TO CHAN SHOULD BE	TROLLED DO NGE AND TH E CONTACTE	OCUMENT FOR CONTROL	TOLERAN DTHERWIS LC LC LC	NCES UNL SE SPECI ±- ±- ±-	CHK 31AUG K.ZHANG APVD 31AUG K.ZHANG PRODUCT SPEC	2017 NAME	
DRAWING IS IS SUBJECT SI	IS A CONT T TO CHAN SHOULD BE	TROLLED DO NGE AND TH E CONTACTE	OCUMENT FOR CONTROL	TOLERAI DTHERWIS LC LC LC LC LC LC LC	NCES UNL SE SPECI ±- ±-	CHK 31AUG K.ZHANG APVD 31AUG K.ZHANG	Ocean End Feed Applicator	ESTRICTED TO

REVISIONS

SET UP GAUGE A 66 P LTR

