




COIL:


RESISTANCE 2500 Ω ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 5.6 mADC
 MUST RELEASE _____

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 15 g's
 SHOCK 50 g's 11 ± 1 MS.DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES:

CUSTOMER DATA SHEET



CONTACT RATING: 2A 115VAC
5A 28VDC RESISTIVE 100,000
OPERATIONS

DR. R.B. 1-16-90 CK. V/16/90



Communications
 Instruments, Inc.

CUST. COMM. INSTR.
 CUST. NO. STANDARD

TYPE "SF5A" RELAY

SF5A5201J00