

Force Guided Relay SRL7

- Low profile relay with force guided contacts according to EN 50205
- 5 form A (NO) + 2 form B (NC) contacts
- Reinforced insulation between contact circuits

Typical applications

Emergency stop or two hand guard safety relays, expansion I/O modules, safety control circuits



SRL7



Approvals	
VDE O-+ N-	40000

VDE Cert. No. 40036240, UL E214025, TÜV 968/EL908

Technical data of approved types on request

Contact Data	
Contact arrangement	5 form A + 2 form B contacts,
	(5 NO + 2 NC)
Rated voltage	250VAC
Max. switching voltage	400VAC
Rated current	6A
Contact material	Ag alloy
Contact style	single contact, force guided
	type A according to EN 50205
Min. recommended contact load	5V/10mA
Initial contact resistance	≤100mΩ at 1A, 24VDC
	≤20Ω at 10mA, 5VDC
Frequency of operation, with/without lo	ad 6/300min ⁻¹
Mechanical endurance	10x10 ⁶ operations

Contact	ratings
Contoot	

Contact	Load	Cycles
UL61810-1 (forme	er UL508)	
NO/NC	6A, 250VAC, general purpose, 85°C	6.000
IEC61810		
NO/NC	6A, 250VAC, cosphi=1, 50% DF, 85°C	6.000
NO (1 form A)	5A, 24VDC, DC-13	6.050
NO (1 form A)	3A, 250VAC, AC-15	6.050

Coil Data		
Coil voltage range	5 to 110VDC	
Operative range, IEC 61810	2	
Max. coil power	700mW	

l versions.	130:-	ഹപ

Coll vers	sions, DC-cc	/II			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
005	5	3,8	0,5	36	694
006	6	4,5	0,6	51	706
009	9	6,8	0,9	116	698
012	12	9	1,2	206	699
015	15	11,3	1,5	319	705
018	18	13,5	1,8	463	700
021	21	16	2,1	630	700
024	24	18	2,4	820	702
036	36	27	3,6	1850	701
048	48	36	4,8	3290	700
060	60	45	6	5140	700
110	110	83	11	17280	700

All figures are given for coil without pre-energization, at ambient temperature +23°C.

Insulation Data	group A	group B		
Initial dielectric strength				
between open contacts	1000Vrms	1000Vrms		
between contact and coil	4000Vrms	2500Vrms		
between adjacent contacts	4000Vrms	2500Vrms		
between group A and group B	4000	Vrms		
Clearance/creepage				
between open contacts	microdisco	onnection		
between contact and coil	≥5.5/5.5mm	≥3/4mm		
between adjacent contacts	≥5.5/5.5mm	≥3/4mm		
between group A and group B	≥5.5/5	.5mm		
Insulation to EN 62477 (former EN 5	60178), type of insu	lation		
between contact and coil	reinforced	basic		
between adjacent contacts	reinforced	basic		
between group A and group B reinforced				

Other Data		
Ambient temperature	-40 to 85°C	
Category of environmental Protection		
IEC 61 810	RTII	
Packaging/unit	20 pcs. tray	
	100 pcs. box	

For more detailed information see product specification 2158004





54.45 ±0.1

Force Guided Relay SRL7 (Continued)

Dimensions 7 pole, 5 form A + 2 form B, 5NO + 2NC Low cover Normal cover 14.55 7.4 7.4 7.4 7.4 8.4 9.9 10.8 -01 2.8 -01 2.8 -01

PCB layout / terminal assignment Bottom view





For versions with different contact configuration or other number of poles please contact your nearest TE contact or partner.

Product code	Type	Cont. arrangement	Cont. material	Coil	Part Number
SRL7-523-D012-0010	7 pole relay	5 form A + 2 form B	AgSnO2	12VDC	2-2045880-4
SRL7-523-D018-0010	with force	contacts (5 NO + 2 NC)		18VDC	2-2045880-6
SRL7-523-D021-0010	guided			21VDC	2-2045880-7
SRL7-523-D024-0010	contacts			24VDC	2-2045880-8