

PART NUMBER	REVISION	DESCRIPTION
2400071-1	A	Mini Applicator-LP
7-2400071-1	A	Mini Applicator with Crimp Tooling Kit-LP
7-2400071-7	A	Crimp Tooling Kit-LP

CRIMP DATA			
CONNECTION DESCRIPTION: F-TYPE, MALE PLUG, AMPHENOL (FERRUL)			
DISC POSITION	CRIMP HEIGHT ±0.20mm [.007in]	CRIMP PROFILE	APPLICATION SPECIFICATION
C0	6.48 mm [.255 in]	HEX	2388685
COMPONENTS APPLIED			APPLICATOR GAUGE
CABLE	TE FERRUL	TE SUBASSEMBLY	AMPHENOL SUB ASSEMBLY
RG59	2401761-1	2388685-1	222119
-	-	-	-

NOTES:

- 1 RECOMMENDED SPARE PARTS
- 2 GREASE BEARING SURFACES LIGHTLY
- 3 MAGNET, ITEM 166, MUST BE ORIENTED CORRECTLY IN ORDER TO PROPERLY ACTUATE THE COUNTER.
4. UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.
5. APPLICATOR TO BE USED ON BENCH TERMINATORS ONLY.
6. RECOMMENDED TERMINATORS:
* GII TERMINATOR FOR LOOSE PIECE APPLICATORS PN 2374600-1 OR 2374600-2 (W/ COM).

* GII+ TERMINATOR FOR LOOSE PIECE APPLICATORS PN 2844810-1 OR 2844810-2 (W/ COM).
- 7 WHEN WORKING IN THE GII OR GII+ TERMINATOR THE INSTALLATION OF MICROSWITCH (ASSEMBLED IN APPLICATOR BASIC ASSY, ITEM #46) IN THE TERMINATOR IS NOT NEEDED. THE INSTALLATION OF THE MICROSWITCH IS MANDATORY ONLY FOR TERMINATORS THAT DO NOT FEATURE THE MAGNETIC ACTUATOR ITEM #53.

