



## MODEL 46037

### Super Stable Glass NTC Thermistor

- Unmatched Long Term Stability
- Glass Hermetic Seal
- Exposure up to 200°C
- 6000 ohm Resistance @ 25°C
- Interchangeable  $\pm 0.1^\circ\text{C}$ , 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- Thermally conductive epoxy coating
- 32 AWG, 3" (7.6 cm) long Gold Plated Dumet leads
- RoHS Compliant

Hermetically Sealed Glass Encapsulated Precision Interchangeable NTC Thermistor utilizing high stability pressed-disk ceramic sensor for high temperature and high stability applications.

#### FEATURES

- Glass Hermetic Seal
- 6000 ohm Resistance @ 25°C
- Interchangeability
- Excellent High Temperature Performance
- Drift Certified Unmatched Long Term Stability
- High Sensitivity
- Thermally Conductive Epoxy Coating
- RoHS Compliance

#### APPLICATIONS

- High Moisture Applications
- Low to Mid Range Temperature Applications
- Tight Tolerance Instrumentation
- Exposure up to 200°C
- Applications Requiring Outstanding Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments
- Allows use in Applications World-wide


## MODEL 46037

Super Stable Glass NTC Thermistor

### PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C	Ohms	6000
Tolerance 0°C to 70°C	°C	± 0.1
Beta Value 25/85	K	3978
Tolerance on Beta Value	%	0.4
Time response in stirred oil bath	Seconds	< 2.5
Dissipation Constant in stirred oil bath	mW/°C	10
Insulation Resistance (Min. of 100 Mohms for 1 sec.)	Volts	500

### MECHANICAL DETAILS



**TYPICAL PERFORMANCE CURVES (RESISTANCE OF INDIVIDUAL THERMISTORS)**

Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms
-55	578.400	-15	43.770	25	6.000	65	1.2500	105	0.3525
-54	537.400	-14	41.400	26	5.744	66	1.2070	106	0.3426
-53	499.300	-13	39.170	27	5.499	67	1.1650	107	0.3330
-52	464.400	-12	37.060	28	5.267	68	1.1260	108	0.3240
-51	432.100	-11	35.060	29	5.046	69	1.0880	109	0.3149
-50	402.300	-10	33.200	30	4.836	70	1.0510	110	0.3064
-49	374.600	-9	31.470	31	4.633	71	1.0160	111	0.2979
-48	349.000	-8	29.810	32	4.441	72	0.9818	112	0.2899
-47	325.300	-7	28.240	33	4.260	73	0.9490	113	0.2819
-46	303.500	-6	26.780	34	4.084	74	0.9179	114	0.2744
-45	283.200	-5	25.400	35	3.919	75	0.8875	115	0.2670
-44	264.500	-4	24.100	36	3.762	76	0.8587	116	0.2600
-43	247.000	-3	22.880	37	3.610	77	0.8307	117	0.2531
-42	230.900	-2	21.720	38	3.466	78	0.8038	118	0.2464
-41	215.900	-1	20.620	39	3.328	79	0.7780	119	0.2398
-40	201.900	0	19.600	40	3.197	80	0.7532	120	0.2337
-39	189.000	1	18.620	41	3.069	81	0.7292	121	0.2275
-38	176.900	2	17.700	42	2.949	82	0.7060	122	0.2217
-37	165.700	3	16.840	43	2.835	83	0.6839	123	0.2161
-36	155.300	4	16.020	44	2.726	84	0.6623	124	0.2105
-35	145.600	5	15.240	45	2.621	85	0.6418	125	0.2052
-34	136.600	6	14.500	46	2.521	86	0.6218	126	0.1998
-33	128.200	7	13.810	47	2.425	87	0.6027	127	0.1948
-32	120.300	8	13.150	48	2.333	88	0.5843	128	0.1900
-31	113.000	9	12.530	49	2.246	89	0.5664	129	0.1852
-30	106.200	10	11.940	50	2.162	90	0.5491	130	0.1806
-29	99.830	11	11.380	51	2.081	91	0.5326	131	0.1761
-28	93.890	12	10.850	52	2.004	92	0.5166	132	0.1716
-27	88.320	13	10.350	53	1.930	93	0.5012	133	0.1676
-26	83.130	14	9.879	54	1.859	94	0.4862	134	0.1633
-25	78.280	15	9.429	55	1.792	95	0.4718	135	0.1593
-24	73.720	16	9.000	56	1.727	96	0.4580	136	0.1556
-23	69.460	17	8.595	57	1.665	97	0.4447	137	0.1519
-22	65.490	18	8.209	58	1.605	98	0.4316	138	0.1481
-21	61.760	19	7.844	59	1.548	99	0.4191	139	0.1447
-20	58.270	20	7.497	60	1.493	100	0.4071	140	0.1412
-19	54.990	21	7.167	61	1.440	101	0.3954	141	0.1377
-18	51.900	22	6.853	62	1.389	102	0.3842	142	0.1345
-17	49.020	23	6.554	63	1.341	103	0.3733	143	0.1313
-16	46.330	24	6.272	64	1.294	104	0.3626	144	0.1284
								145	0.1252
								146	0.1223
								147	0.1196
								148	0.1167
								149	0.1140
								150	0.1115

## MODEL 46037

Super Stable Glass NTC Thermistor

### ORDERING INFORMATION

Part Number	Description	$\Omega$ @25°C
091690	46037 THERM,SUPER STABLE	6,000

#### NORTH AMERICA

Measurement Specialties, Inc.,  
a TE Connectivity Company  
Tel: 800-522-6752  
[customercare.ando@te.com](mailto:customercare.ando@te.com)

#### EUROPE

Measurement Specialties (Europe), Ltd.,  
a TE Connectivity Company  
Tel: 800-440-5100  
[customercare.tfse@te.com](mailto:customercare.tfse@te.com)

#### ASIA

Measurement Specialties (China), Ltd.,  
a TE Connectivity Company  
Tel: 0400-820-6015  
[customercare.chdu@te.com](mailto:customercare.chdu@te.com)

#### [te.com/sensorsolutions](http://te.com/sensorsolutions)

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.