

# TECHNICAL DATA SHEET

Document number: TTDS-178

Issue: 2

Date: JAN 2016

**EET-...PY9**

**DESCRIPTION** EET-...PY-9 self-adhesive Thermal transfer printable labels.

Label material	Low density polyethylene film, white	
Adhesive	Permanent pressure sensitive acrylic	
Liner	White Glassine	
Dimensions:		
• Label - thickness	0.095 mm $\pm$ 8mm	ASTM D374-88
• Adhesive - coating weight	22 $\pm$ 3 g/m <sup>2</sup>	FTM-12
• Liner - thickness	0.064mm $\pm$ 4mm	ISO 536
Peel Adhesion at 23°C	Stainless steel 750 N/m	FTM 1 (72 hour dwell) Average values
Service Temperature	-20°C to +80 °C	
Minimum application temperature	10 °C	
Print permanence	Dry rub Print legible after 70 rubs	SAE-AS-81531
Storage stability	2 years at 21°C and 50% RH	
Printability	Thermal transfer	

[www.te.com/rail](http://www.te.com/rail)

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.