


### **Double Micro Relay K (THT – THR)**

- Small power relay
- Limiting continuous current 20A at 85°C
- Minimal weight
- Low noise operation
- Wave (THT) and reflow (THR/pin-in-paste) solderable versions
- For single version refer to Single Micro Relay K



Door lock, heated front/rear screen, interior lights, seat control, sun roof, window lifter, wiper control.





Contact Data (continued)	
Contact material	silver alloy
Min. contact load <sup>2)</sup>	1A 5VDC
Initial voltage drop	
NO contact at 10A, typ./max.	30/300mV
NC contact at 10A, typ./max.	30/300mV
Operate time <sup>3)</sup>	typ. 3ms
Release time <sup>3)</sup>	typ. 1.5ms
Mechanical endurance	>5x10 <sup>6</sup> ops.

Electrical Endurance 12VDC Coil							
Load voltage/	Load type			Load current		On / off ratio	Electrical endurance <sup>4)</sup>
coil voltage				1 form C			
				NO	NC		endurance "
14VDC	resistive		make	20A		0.12s/4.88s	>1x10 <sup>5</sup> ops.
			break	20A		0.125/4.005	
	Motor reverse blocked	L=0.77mH	make	25A		0.12s/4.88s	>1x10 <sup>5</sup> ops.
			break	25A		0.125/4.005	
	Wiper	L=1mH	make	25A	20A	0.12s/4.88s	>1x10 <sup>5</sup> ops.
			break	5A	0A	0.125/4.005	

All tests performed with cyclic temperature -40 to 85°C

<sup>1)</sup> Measured on 70x70x1.5mm epoxy PCB FR4 with 25cm2 (double layer 105µm) copper area. Connecting cable cross section 6 mm2. Boundary conditions: 180°C coil temperature; 130°C

<sup>2)</sup> See Definitions for automotive relays https://relays.te.com/definitions/ and chapter Diagnostics of Relays in our Application Notes at https://relays.te.com/appnotes/

<sup>3)</sup> Measured at nominal voltage without coil suppression unit. A low resistive suppression device in parallel to the relay coil increases the release time and reduces the lifetime caused by increased erosion and/or higher risk of contact tack welding.

<sup>4)</sup> According Weibull




# Double Micro Relay K (THT - THR) (Continued)

Coil Data					
Coil	Rated	Must	Must	Coil	Rated
code	voltage	Operate	Release	resist.	coil
		voltage	voltage	±10%	power
	[VDC]	[VDC]	[VDC]	[Ω]	[W]
001	12	6.9	1.50	254	0.57
801	12	6.9	1.50	254	0.57
802	12	5.7	1.25	181	0.80


All figures are given for coil without pre-energization, at ambient temperature +23°C.

### Coil operating range coil 001/801



Does not take into account the temperature rise due to the contact current

### Coil operating range coil 802



Does not take into account the temperature rise due to the contact current

Insulation Data	
Initial dielectric strength	
between open contacts	500VAC <sub>rms</sub>
between contact and coil	500VAC <sub>rms</sub>

Other Data				
EU RoHS/ELV compliance	compliant			
Ambient temperature	-40 to +105°C			
Cold storage				
IEC 60068-2-1 (2007-03)	1000h; -40°C			
Dry heat				
IEC 60068-2-2 (2007-07)	1000h; +125°C			
Rapid change of temperature (therr	mal shock),			
IEC 60068-2-14 (2009-01)				
Na	100 cycles, -40°C /+125°C			
Damp heat cyclic,				
IEC 60068-2-30 (1985-08)				
Db, variant 1	6 cycles 25°C/55°C/93%RH			
Category of environmental protection	on			
IEC 61810 (2008-01)	THT: RT III			
	THR: RT II			
Sealing test				
IEC 60068-2-17 (1994-07)	THT: Qc, method 2, 1min, 70°C			
	THR: n.a vented			
Vibration resistance (functional)				
IEC 60068-2-6 (2007-12)	10 to 500Hz, 6g			
sine sweep	No change of switching state >10µs			
Shock resistance (functional) half si	ne			
IEC 60068-2-27 (2008-02)				
open NO contact will not close >	>10µs 6ms, up to 30g <sup>6)</sup>			
Solderability (aging 3: 4h/155°C)				
IEC 60068-2-20 (2008-07)	Ta, method 1, hot dip 5s, 215°C			
Resistance to soldering heat THT	Tb, method 1A, hot dip 10s,			
IEC 60068-2-20 (2008-07)	260°C with thermal screen			
Resistance to soldering heat THR	Tb, method 1A, hot dip 10s,			
IEC 60068-2-58 (2017-07)	260°C; preheating min 130°C			
Terminal type	PCB: THT, THR			
Weight	approx. 8g (0.28oz)			
Storage conditions <sup>7)</sup>	according IEC 60068-1 (2017-07)			
Packaging unit	990 pcs.			

<sup>6)</sup> Depending on mounting position: no change in switching state >10µs.


<sup>7)</sup> For general storage and processing recommendations please refer to our Application Notes and especially to Storage in the Definitions or at https://relays.te.com/appnotes/



# Double Micro Relay K (THT - THR) (Continued)

#### View of the Terminals

Bottom view on solder pins




#### Remark

Positional tolerances according to DIN EN ISO 5458

### **Terminal Assignment**


Bottom view on solder pins

#### 2 form C, 2 CO




#### **Dimensions**

Double Micro Relay THT




#### View of Stand-Offs

Bottom view on solder pins



#### **Dimensions**


Double Micro Relay THR





# Automotive Relays PCB Single Relays

# Double Micro Relay K (THT - THR) (Continued)



Product Code	Version	Design	Coil	Contact	Arrangement	Part Number
V23086-C2001-A403	PCB THT, cleanable	Double	Standard	Single	2 form C, 2 CO (standard)	1413009-9
V23086-R2801-A403	PCB THR, vented					6-1414920-1
V23086-R2802-A803			Sensitive		2 form C, 2 CO (wiper load)	8-1414964-5

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request