

108-10047

11 Mar 11 Rev C

Circular DIN Connector

- 1. SCOPE
- 1.1. Content

This specification covers the performance, tests and quality requirements for the AMP* circular DIN connectors.

- 1.2. Classification
 - A. Plugs
 - Class A: 2 piece, shield and grounded receptacle
 Class B: 1 piece, shield and shielded receptacle
 - B. Receptacles
 - (1) Class A: Contains grounding clip
 - (2) Class B: Contains shielding clip

Class A plugs may be mated with Class B receptacles and vice versa.

1.3. Qualification

When tests are performed on the subject product line, the procedures specified in AMP 109 series specifications shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

2. APPLICABLE DOCUMENTS

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

- 2.1. AMP Specifications
 - A. 109-1: General Requirements for Test Specifications



в.	109 Series:	Test Specifications as indicated in Figure 1. (Comply with MIL-STD-202, MIL-STD-1344 and EIA RS-364)	d
c.	Corporate B	ulletin 76: Cross reference between AMP Test Specifications and Military or Comm Documents	
D.	114	J O C L MONTE	
E.	501-15: Te	st Report	

E. 501-15: Test Rep

3. REQUIREMENTS

3.1. Design and Construction

Connector shall be of the design, construction and physical dimensions specified on the applicable product drawing.

3.2 Materials

- A. Contacts: Brass, tin or gold over nickel plated
- B. Shields: (1) Class A: Brass, nickel plated
 - (2) Class B: Brass, tin plated
- C. Housing: Polycarbonate, UL 94V-0
- D. Cord Guard: Polypropylene

3.3. Ratings

- A. Current/Voltage: 250 vac at 7.5 amperes maximum, see Para 3.5.(a)
- B. Operating Temperature: -55° to 105°C
- 3.4. Performance and Test Description

Connector shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1.

3.5. Test Requirements and Procedures Summary

Test Description	Requirements	Procedure
Examination of Product	Meets requirements of product drawing and AMP Spec 114	Visual, dimensional and functional per applicable inspection plan.

Figure 1 (cont)



Test Description	Requirement	Procedure
•	ELECTRICAL	
Termination Resistance,	Wire Test Resistance	Measure potential drop of
Specified Current	Size Current milliohm	mated contacts after
	AWG amperes maximum	stabilizing, see Figure 4;
	20 7.5 15	AMP Spec 109-25, calculate
	22 5.0 20 24 3.0 25	resistance.
	24 3.0 25 28 1.5 20	
Dielectric Withstanding	750 vac dielectric	Test between adjacent
Voltage	withstanding voltage,	contacts of mated
	one minute hold.	connector assemblies;
		AMP Spec 109-29-1.
Insulation Resistance	5 x 10 ³ megohms	Test between adjacent
	minimum.	contacts of mated
		connector assembly;
Tomponetune Dise Ve		AMP Spec 109-28-4.
Temperature Rise Vs. Current (a)	30°C maximum T-rise,	T-rise at rated current;
Current (a)	see Figure 2. MECHANICAL	AMP Spec 109-45-2.
Vibration (b)	No discontinuities	Subjected mated connectors
. ,	greater than	to 10-55-10 Hz
	1 microsecond	traversed in 1 minute
		at .06 inches total
		excursion; 2 hours in
		each of 3 mutually
		perpendicular planes;
Physical Shock (b)	No discontinuities	AMP Spec 109-21-1.
Thysical Shock (b)	greater than	Subject mated connector
	l microseconds.	to 50 G's half-size in 11 milliseconds; 3 shocks
	T microseconds.	in each direction applied
		along the 3 mutually
		perpendicular planes
		total 18 shocks; AMP
		Spec 109-26-1.
Mating Force	3 pounds maximum	Measure force necessary
	per contact.	to mate connector
		assembly from point of
		initial contact,
		incorporating free
		floating fixtures at a
		rate of 0.5 inch/minute;
		AMP Spec 109-42, cond A,
		calculate force per contact.

Figure 1 (cont)





Test Description	Requirement	Procedure
Unmating Force	1 pound minimum	Measure force necessary
	per contact	to unmate connector
		assembly with locking
		latches removed, at a
		rate of 0.5 inch/minute;
		AMP Spec 109-42, cond A,
Contact Retention	6 pounds minimum.	calculate force per contact.
Contact Retention	o pounds minimum.	Apply axial load of
		6 pounds to crimped
		contacts; AMP Spec 109-30
Durability	Maintain electrical	except grip wire. Mate and unmate
	continuity.	connector assemblies
	continuity.	for 100 cycles; AMP
		Spec 109-27.
	ENVIRONMENTAL	opec 107 21.
Thermal Shock (b)	Dielectric withstanding	Subject mated connectors
	voltage.	to 10 cycles between
		-55° and 105°C; AMP
		Spec 109-22.
Humidity, Steady State	Insulation resistance.	Subject mated connectors
		to steady state humidity
		at 40°C and 90-95% RH;
		AMP Spec 109-23, method
		II, cond A.
Corrosion, Salt Spray	No base metal	Subject mated connectors
	exposure.	to 5% salt concentration
		for 48 hours; AMP Spec
		109-24, cond B.

- (a) Maximum rated current that can be carried by this product is limited by maximum operating temperature of housings, which is 105°C, and temperature rise of contacts, which is 30°C. Variables which shall be considered for each application are: wire size, connector size, contact material, and ambient temperature.
- (b) Shall remain mated and show no evidence of damage, cracking or chipping.

-Figure 1 (end)





3, 4 and 5 Position Connectors With 20 AWG Wire



6, 7 and 8 Position Connectors With 20 AWG Wire

Figure 2



	Test Group (a)			
Test or Examination		2	3	4
	Test Sequence (b)			
Examination of Product	1,8	1,7	1,6	li
Termination Resistance, Specified Current	7		5	
Dielectric Withstanding Voltage	2	5		<u> </u>
Insulation Resistance	3	_	3	
Temperature Rise Vs. Current	1			2
Vibration	4			
Physical Shock	5			
Mating Force		2	· · · · ·	<u> </u>
Unmating Force	1	3		
Contact Retention		6		
Durability			4	
Thermal Shock		4		
Humidity, Steady State			2	
Corrosion, Salt Spray	6			

3.6. Connector Qualification and Requalification Tests and Sequences

- (a) See Para. 4.1.A.
- (b) Numbers indicate sequence in which tests are performed.

Figure 3

4. QUALITY ASSURANCE PROVISIONS

- 4.1. Qualification Testing
 - A. Sample Selection

Connector housings and contacts shall be prepared in accordance with applicable Instruction Sheets. They shall be selected at random from current production. All groups shall consist of 2 mated pair of Class A and 2 mated pair of Class B connectors. One mated pair of each class and size shall be terminated with the minimum wire size and the other with the maximum wire size. In addition Test Group 2 requires 2 mated pair of each class and size for the mate and unmate test only. These connectors need not be wired.

B. Test Sequence

Qualification inspection shall be verified by testing samples as specified in Figure 3.



- C. Acceptance
 - Requirements put on test samples, as indicated in the requirements portion of Figure 1, exist as either the upper or lower statistical tolerance limit (95% confidence, 99% reliability). All samples tested in accordance with this specification shall meet the stated tolerance limit.
 - (2) Failures attributed to equipment, test setup, or operator deficiencies shall not disqualify the product. When product failure occurs, corrective action shall be taken and samples resubmitted for qualification.
- 4.2. Requalification Testing

Requalification shall be established by the cognizant divisional engineering function and may consist of all or any part of the overall qualification program provided that it is conducted within the required time period.

4.3. Quality Conformance Inspection

The applicable AMP inspection plan will specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification.



Printed Circuit Board-

Note: Termination resistance equals millivolts divided by test current less resistance of 6 inches of wire.

Figure 4

Termination Resistance Measurement Points