



intercontec
products

923 Steckergehäuse

speedtec

6-polig
Schutzleitergehäuseanbindung gem. VDE 0627


TE Teile Nr.: 10-0360-002-P00
IC Ref. Nr.: 10.360.02

Technische Daten


Polzahl 6 (5+PE)
Temperaturbereich -20 °C bis 130 °C

Werkstoffe

Gehäuse Zinkdruckguss, vernickelt
Überwurfmutter Zinkdruckguss, vernickelt
Isolierkörper PA 6.6 mod., UL 94/ V0
Dichtungen FKM



Hauptabmessungen
Steckergehäuse



Polbild
Ansicht steckseitig

© 2018 TE Connectivity.

TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz





intercontec
products

923 Plug Housing

speedtec

6-pin
Earth-to-Housing Connection according to VDE 0627

TE part number: 10-0360-002-P00
IC reference number: 10.360.02

Technical Data



number of pins
temperature range

6 (5+PE)
-20 °C to 130 °C


Material

housing
coupling nut
insulation insert
seals

zinc diecast, nickel plated
zinc diecast, nickel plated
PA 6.6 mod., UL 94/ V0
FKM



Main Dimensions
plug housing



Contact Arrangement
mating view

Y6-F366-000-0EN issued: 04.03.2015/JA; modified: 17.10.2018/MK

© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz

