





DBLK POWER DISTRIBUTION BLOCKS

PI-Spring (Push-In & Spring) technology Unipolar 7, 15 & 16 connections, 10, 16 & 35 mm²

Unipolar 7, 15 & 16 connections, 10, 16 & 35 mm² up to 125 A, 1000VAC - 1500VDC

Compact, vibration proof and time saving power distribution in control panel.



EASY TO INSTALL

3 mounting options adapted to many panel configurations

- Horizontal & vertical Din rail mounting
- Panel mount with screws.

Clear identification

- Double marking area
- Flat "SNK" marking surface
- Ready to use marking kit (L1, L2, L3, N, PE, "+", "-", red, blue, green)
 delivered with each block
- Installation instruction on back.

Easy wiring

- Increased wiring visibility due to inline connection and front access
- Hands-free wiring, with or without screwdriver
- Screwdriver is locked during wiring process.

Flexibility

- · Compatible with BAM4 end stop
- Built-in voltage test point.



INCREASED PRODUCTIVITY

Reduced wiring, inventories, hardware and assembly costs

- Push-in connection save up to 50% installation time compared to screw technology
- Reduces assembly time by up to 90% compared to conventional systems
- Our modular and touch proof concept significantly reduces the needs for bus bars, isolators, fasteners, protection screens...

Time saving

- Allow flexible cables wiring without ferrules with screwdriver
- Easy and quick insertion for rigid and solid wires in push-in mode.

Fast & flexible wiring

PI-spring technology, pre-numbered connections, technical data on product cover.



FOR ALL YOUR NEEDS

Reduced inventory

Short range, no accessory, all mounting options provided on a single block: vertical or horizontal, Din rail mounting, panel mounting.

World-class certifications

Full standard package: IEC / UL / EAC.

Safety

Full IP20.

Main technical data Ordering details

Rated current		Rated voltage		Rated cross section						Туре	Part Number		Packing					
		IEC	UL							Rigid Solid/ Stranded								
				nb	mm²	mm²	AWG	mm²	AWG	mm²	AWG				pieces			
76 A	: :	1000 VAC 1500 VDC	1000 V	3	1.5 16	1.5 16	16 6	1.5 6	16 10	1.5 25	16 4	DBLK76-7	1SNL407610R0000	10 pcs				
00				4	1.5 10	1.5 10	16 8	1.5 4	16 12	1.5 16	16 6							
XIZ I	85 A 1000 VA	1000 VAC	:	3	1.5 16	1.5 16	16 6	1.5 6	16 10	1.5 25	16 4	DBLK76-15	1SNL407611R0000	5 pcs				
00000		1500 VDC		12	1.5 10	1.5 10	16 8	1.5 4	16 12	1.5 16	16 6							
125 A	1 1 1	130 A	130 A	1000 VAC	1000 VAC 6	1000 VAC	00 VAC 600 V	2*	10 35	10 35	8 1	N/A	N/A	10 35	8 1	DBLK125-16-2R 1S	1SNL412510R0000	1 pcs
		1000 VDC		2	1.5 16	1.51 6	16 6	1.5 6	16 10	1.5 16	16 6							
	:			12	1.5 10	1.5 10	16 8	1.5 4	16 12	1.5 16	16 6							

 $^{^{\}ast}$ The 2 x 10 ... 35 mm^2 connections are screw clamp technology

	100		:		
(ILC TRUE	RoHS	- 21	:	
• • •	market market	: nor to	: C TH	:	:
o= :	0.00			:	
CE :	CB	· ROHS	· USR CNR	•	

Flexible without ferrule	Flexible with insulated fer-	Rigid Solid	Rigid Stranded
IEC V-K (class 5/6)	rule IEC V-K (class 5/6)	IEC V-U (class 1), UL solid	IEC V-R (class 2), UL class B/C


Mounting instructions


Rail	꿉	TH 35-7.5 TH 35-15	
Wire stripping length	+		17 mm 0.67 in
			15 mm 0.591 in


Tool		
For screw connection		Allen key Ø 4 Ø 0.157
For PI-Spring connection (for flexible conductor without ferrule)	: V / 1	Flat screw- driver Ø 4 Ø 0.157

Torque	٥	Screw clamp			
		25 35 mm² 4 1 AWG	3.5 4 Nm 31 35.4 lb.in		
		:	3 3.5 Nm 26.5 35.4 lb.in		
		10 mm² 8 AWG	3 3.5 Nm 26.5 35.4 lb.in		


Dimensions







Mounting instructions



Panel mount:
Drilling instructions
at the back



Parallel to the mounting rail



Perpendicular to the mounting rail

te.com

© 2022 TE Connectivity Ltd. family of companies. All Rights Reserved.

ENTRELEC, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

INDUSTRIAL / DBLK POWER DISTRIBUTION BLOCKS / BROCHURE / EN

06/22

BROCHURE

TE Connectivity

3, rue Jean Perrin

69687 Chassieu cedex

France

Tel: +33 481923100

