



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Manufacturing Info/ Material Info	<b>Subsectionals</b>	D, A																									
<b>Supplier Information</b>																																		
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Chan, Nelson	<b>Contact Title</b>	Global Account Manager, HKG SELL DIR-EMS																											
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-03-30	<b>Contact Email</b>	nelson.chan@te.com																													
<b>Contact Phone Number</b>		+852-2738-8751																																
<b>Legal Statement</b>																																		
<b>Supplier Acceptance</b>	true																																	
<b>Legal Statement</b>																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
<b>Product</b>																																		
<b>Manufacturer Item number</b>	1-1624117-6	<b>Amount</b>	11.7	<b>Version</b>	-	<b>Identity</b>																												
<b>Manufacturer Item Name</b>	BMB-B 0805 600R	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>																												
<b>Date</b>		<b>UOM</b>	Each																															
<b>EURoHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions																																	
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed																																	
<b>Manufacturing Information</b>																																		
<b>J-STD-020 MSL Rating</b>		<b>Max Total a Wave Time</b>		<b>Ramp Rate</b>		<b>Wave Additional Info</b>																												
<b>Classification Temp</b>		<b>Max Wave Solder Time</b>	20.0	<b>Ramp Down Rate</b>		<b>Psl Rating Reflow</b>																												
<b>Max Time Within 5</b>		<b>Psl Rating Wave</b>		<b>Package Designator</b>		<b>Size</b>	0.0																											
<b>Time Above 217</b>		<b>Reflow Additional Info</b>		<b>Preheat Max Temp</b>		<b>Terminal Base Alloy</b>	Not Applicable																											
<b>Preheat Duration</b>		<b>bulk Solder Termination</b>	Not Applicable	<b>Nbr or Reflow Cycles</b>		<b>Terminal Plating</b>	Not Applicable																											
<b>Preheat Min Temp</b>		<b>Nbr of Instances</b>	0	<b>Component Temp Spike</b>		<b>Shape</b>	Not Applicable																											
<b>Product Disclosure</b>																																		
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>																									
Material	1	Ceramic body				1.0	10.179	mg																										
Substance	2	Nickel oxide (NiO)	Supplier	1313-99-1	7.0	1.0	0.71253	mg																										
Substance	2	Iron oxide (Fe2O3)	Supplier	1309-37-1	60.0	1.0	6.1074	mg																										
Substance	2	Zinc oxide (ZnO)	Supplier	1314-13-2	25.0	1.0	2.54475	mg																										
Substance	2	Copper oxide (CuO)	Supplier	1317-38-0	8.0	1.0	0.81432	mg																										
Material	1	Terminal(Paste )				1.0	1.034	mg																										
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	1.034	mg																										
Material	1	Sn Plating				1.0	0.266	mg																										
Substance	2	Tin	Supplier	7440-31-5	100.0	1.0	0.266	mg																										
Material	1	Ni Plating				1.0	0.089	mg																										
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	0.089	mg																										
Material	1	Cu Plating				1.0	0.132	mg																										
Substance	2	Copper	Supplier	7440-50-8	100.0	1.0	0.132	mg																										