

## **1.0 SCOPE**

### **1.1. Content:**

This specification covers performance, tests and quality requirements for 2 Pin Wire to Wire connectors. Applicable product descriptions and part numbers are as shown on product drawing.

### **1.2. Qualification:**

When tests are performed on the subject product line, procedures specified shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

## **2.0 APPLICABLE DOCUMENTS**

The following documents form a part of this specification to the extent specified herein. Unless otherwise specified, the latest edition of the document applies. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

### **2.1 TE Connectivity Documents:**

501-137159: Test Report.

C-2834048: Customer drawing for plug

C-2834049: Customer drawing for receptacle

C-2834050: Customer drawing for mated connector

## **3.0 REQUIREMENTS**

### **3.1 Design and Construction**

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

### **3.2 Materials**

Materials used in the construction of this product shall be as specified on the applicable product drawing.

### **3.4 Ratings**

A. Voltage: 600 V AC Max.

B. Current: 9A Max.

C. Operating Temperature: -40 to 105°C

D. Storage Environment:

Temperature: - 25°C to 40°C      Relative humidity: 15%-70%

### **3.5 Performance and Test Description**

Product is designed to meet the electrical, mechanical and environmental performance requirements. Unless otherwise specified, all tests shall be performed in the room temperature (5~35°C), relative humidity (45~85%), air pressure (86~106kPa), and special case temperature (18~22°C), relative humidity (60~70%), unless otherwise specified.

### 3.6 Test Requirements and Procedures Summary

#### 3.6.1 Examination:

Test Description	Requirement	Procedure
Examination of the product	Meets visual requirements.	Visual inspection per product drawing. Per EIA-364-18

#### 3.6.2 ELECTRICAL

Test Description	Requirement	Procedure
Contact Resistance	20 mΩ Max	Subject the specimen to maximum allowed rating current (9A) and measure the contact resistance. Per EIA-364-06
Insulation resistance.	1000 MΩ Min.initial, 100 MΩ Min,Final.	Mated connector with 500 V DC between adjacent contacts for 1 min. Per EIA-364-21
Withstanding Voltage	No breakdown.	Unmated connector with 2200 V AC between adjacent contacts for 1 min. Per EIA-364-20
Current rating	The temperature rise should be 30°C Max.	Mated connector measured at max rated current with series all contacts (8A with 16&18AWG,3A with 20&22AWG). Per EIA-364-70

#### 3.6.3 MECHANICAL

Test Description	Requirement	Procedure
Durability	No mechanical damage No change to performance Contact resistance: 20mΩ Max.	Mating and unmating specimens for 10 cycles at a max rate of 500 cycles per hour. Per EIA-364-09.
Random Vibration	No discontinuities of 1 microsecond or longer duration.	Subject mated specimens to 3.10G's rms between 20~500HZ. Fifteen minutes in each of 3 mutually perpendicular planes. Per EIA-364-28, Test Condition VII, Condition D.
Mechanical shock	No discontinuities of 1 microsecond or longer duration.	Subject mated specimens to 30 G's half-sine shock pulses of 11 milliseconds duration. Three shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks. Per EIA-364-27, Condition H.
Wire insertion force	20N Max for 18-22AWG Solid Wire 30N Max for Tin Dipped 16AWG stranded wire(26 strands Max.),18AWG stranded wire(16 strands Max.) and 20AWG stranded wire(7 strands Max.).	Measuring max force during wire insertion operation. Operating speed : 10mm/minute Per EIA-364-13
Wire retention force	44.5N Min : 18-20 AWG solid wire or Tin dipped stranded wire (18AWG with16 strands Max. ,20AWG with 7 strands). 35.6N Min.: 22AWG solid wire. 66.7N Min.:16AWG with 26 strands Max.).	Measuring max force during wire pull out operation. Operating speed : 10mm/minute Per EIA-364-13
Mating force	40N Max.	Measure force necessary to mate specimens at a max rate of 12.7mm per minute. Per EIA-364-13
Unmating force	30N Min(with latch)	Measure force necessary to unmate specimens at a max rate of 12.7mm per minute. Per EIA-364-13

### 3.6.4 Environmental

Test Description	Requirement	Procedure
Thermal shock	No physical damage, and meet requirements of additional tests specified in Product Qualification Test Sequence (Item 3.6.7)	Subject specimens to 25 cycles between -40 and 105 °C with 30 minute dwells at temperature extremes and 1 minute transition between temperatures. Per EIA-364-32, Test Condition VII.
Humidity (cycling Temperature)	No physical damage, and meet requirements of additional tests specified in Product Qualification Test Sequence (Item 3.6.7)	Subject specimens to 10 cycles (10 days) between 25 and 65 °C at 80 to 100% RH. Per EIA-364-31, Method III.
Temperature life	No physical damage, and meet requirements of additional tests specified in Product Qualification Test Sequence (Item 3.6.7)	Subject mated specimens to 105 °C for 250 hours. Per EIA-364-17, Method B, Test Condition 4.

*Remark:*

1. The text “**No mechanical damage**” means *No structure is damaged/No connection becomes loose/The specimen still is fully functional in electricity after testing.*
2. *Current rating test with 18AWG and 22AWG, wire insertion force& retention force with 16AWG to 22AWG, other test items with default 18AWG.*

### 3.6.5 Product Qualification and Requalification Test Sequence

Test group	a	b	c	d	e	f
Examination of product	1, 6	1, 8	1, 8	1, 6	1, 4	1,6
Contact resistance	2, 5	2, 4, 7		2, 5	2	
Insulation resistance			3, 6			
Withstanding Voltage			2, 7			
Current rating					3	
Random vibration	4					
Mechanical shock	3					
Durability		3		3		
Mating force						4
Unmating force						5
Thermal shock		5	4			
Wire insertion force						2
Wire retention force						3
Humidity -temperature cycling		6	5			
Temperature life				4		
Sample size	5pcs	5pcs	5pcs	5pcs	5pcs	5pcs

**4.0 Quality Assurance Provisions**

**4.1 Qualification Testing**

**A. Specimen Selection**

Specimens shall be prepared in accordance with applicable Instruction Sheets and shall be selected at random from current production.

**B. Test Sequence**

Qualification inspection shall be verified by testing specimens as specified.

**4.2. Requalification Testing**

If changes significantly affecting form, fit or function are made to the product or manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality and reliability engineering.

**4.3. Acceptance**

Acceptance is based on verification that the product meets the requirements. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify the product. If product failure occurs, corrective action shall be taken and specimens resubmitted for qualification. Testing to confirm corrective action is required before resubmitted.

**4.4. Quality Conformance Inspection**

The applicable quality inspection plan shall specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification

Product Part No.	Description
2834048-*	2Pin latched wire to wire poke in connector,Plug assembly
*-2834049-*	2Pin latched wire to wire poke in connector,Receptacle assembly
2834050-*	2Pin latched wire to wire poke in connector,Mated assembly