

11-May-2020 Rev C

### **HDP Series Connector System**

#### 1. SCOPE

#### 1.1. Content

This specification covers performance, tests and quality requirements for the TE Connectivity (TE) HDP Series Connector System.

#### 1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 2 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

1.3. Successful qualification testing on the subject product line was completed in 1992. The Qualification Test Report number for this testing is 501-151033. This document is on file at and available from Product Engineering, Industrial Commercial Transportation (ICT).

#### 2. APPLICABLE DOCUMENTS AND FORMS

The following documents and forms constitute a part of this specification to the extent specified herein. Unless otherwise indicated, the latest edition of the document applies.

### 2.1. TE Connectivity (TE) Documents

•	109-1:	General Requirements for Testing
•	114-151000:	Application Specification for DEUTSCH Size 16 S&F Pin & Socket
•	114-151001:	Application Specification for DEUTSCH Size 16 S&F Pin & Socket
•	114-151002:	Application Specification for DEUTSCH Size 12 S&F Pin & Socket
•	114-151003:	Application Specification for DEUTSCH Size 20 S&F Pin & Socket
•	114-151004:	Application Specification for DEUTSCH Size 4-20 Solid Pin & Socket
•	114-151006:	Application Specification for DEUTSCH Size 12 S&F Pin & Socket
•	114-151015:	Application Specification for DEUTSCH HDP Series Connector System
•	408-151007:	Instruction Guide DEUTSCH Extraction Tools

**HDP Qualification Test Report** 

#### Product Drawings

501-151033:

```
HDP24-18-XXP/SX – Size 18 Receptacles
HDP24-24-XXP/SX – Size 24 Receptacles
HDP26-18-XXP/SX – Size 18 Plugs
HDP26-24-XXP/SX – Size 24 Plugs
```



### Products

 $\boldsymbol{X}$  refers to N, T, E seal type. XXXX refers to special modification.

HDP24-18-6SX-XXXX       6 so         HDP24-18-8PX-XXXX       8 pir         HDP24-18-8SX-XXXX       8 so	receptacle cket receptacle	HDP26-18-6PX-XXXX HDP26-18-6SX-XXXX	6 pin plug 6 socket plug
HDP24-18-8PX-XXXX         8 pir           HDP24-18-8SX-XXXX         8 so		HDP26-18-6SX-XXXX	6 socket plug
HDP24-18-8SX-XXXX 8 so			o socket plug
	ı receptacle	HDP26-18-8PX-XXXX	8 pin plug
	cket receptacle	HDP26-18-8SX-XXXX	8 socket plug
HDP24-18-14PX-XXXX   14 p	in receptacle	HDP26-18-14PX-XXXX	14 pin plug
HDP24-18-14SX-XXXX 14 s	ocket receptacle	HDP26-18-14SX-XXXX	14 socket plug
HDP24-18-20PX-XXXX 20 p	in receptacle	HDP26-18-20PX-XXXX	20 pin plug
HDP24-18-20SX-XXXX 20 s	ocket receptacle	HDP26-18-20SX-XXXX	20 socket plug
HDP24-18-21PX-XXXX 21 p	in receptacle	HDP26-18-21PX-XXXX	21 pin plug
HDP24-18-21SX-XXXX 21 s	ocket receptacle	HDP26-18-21SX-XXXX	21 socket plug
HDP24-24-7PX-XXXX 7 pir	receptacle	HDP26-24-7PX-XXXX	7 pin plug
HDP24-24-7SX-XXXX 7 so	cket receptacle	HDP26-24-7SX-XXXX	7 socket plug
HDP24-24-9PX-XXXX 9 pir	receptacle	HDP26-24-9PX-XXXX	9 pin plug
HDP24-24-9SX-XXXX 9 so	cket receptacle	HDP26-24-9SX-XXXX	9 socket plug
HDP24-24-14PX-XXXX 14 p	in receptacle	HDP26-24-14PX-XXXX	14 pin plug
HDP24-24-14SX-XXXX 14 s	ocket receptacle	HDP26-24-14SX-XXXX	14 socket plug
HDP24-24-16PX-XXXX 16 p	in receptacle	HDP26-24-16PX-XXXX	16 pin plug
HDP24-24-16SX-XXXX 16 s	ocket receptacle	HDP26-24-16SX-XXXX	16 socket plug
	in receptacle	HDP26-24-18PX-XXXX	18 pin plug
HDP24-24-18SX-XXXX 18 s	ocket receptacle	HDP26-24-18SX-XXXX	18 socket plug
	in receptacle	HDP26-24-19PX-XXXX	19 pin plug
HDP24-24-19SX-XXXX 19 s	ocket receptacle	HDP26-24-19SX-XXXX	19 socket plug
	in receptacle	HDP26-24-21PX-XXXX	21 pin plug
	ocket receptacle	HDP26-24-21SX-XXXX	21 socket plug
	in receptacle	HDP26-24-23PX-XXXX	23 pin plug
HDP24-24-23SX-XXXX 23 s	ocket receptacle	HDP26-24-23SX-XXXX	23 socket plug
	in receptacle	HDP26-24-29PX-XXXX	29 pin plug
HDP24-24-29SX-XXXX 29 s	ocket receptacle	HDP26-24-29SX-XXXX	29 socket plug
	in receptacle	HDP26-24-31PX-XXXX	31 pin plug
HDP24-24-31SX-XXXX 31 s	ocket receptacle	HDP26-24-31SX-XXXX	31 socket plug
HDP24-24-33PX-XXXX 33 p	in receptacle	HDP26-24-33PX-XXXX	33 pin plug
HDP24-24-33SX-XXXX 33 s	ocket receptacle	HDP26-24-33SX-XXXX	33 socket plug
HDP24-24-35PX-XXXX 35 p	in receptacle	HDP26-24-35PX-XXXX	35 pin plug
HDP24-24-35SX-XXXX 35 s	ocket receptacle	HDP26-24-35SX-XXXX	35 socket plug
	in receptacle	HDP26-24-47PX-XXXX	47 pin plug
	ocket receptacle	HDP26-24-47SX-XXXX	47 socket plug
	receptacle	HDP26-24-91PX-XXXX	9 pin plug
HDP24-24-91SX-XXXX 9 so	cket receptacle	HDP26-24-91SX-XXXX	9 socket plug

Rev C 2 of 10



#### 2.2. Industry Documents

- DIN 40050-9: Road Vehicles Degrees of Protection (IP Code)
   DIN 72551-6: Road Vehicles—Low-Tension Cables—Part 6: Single-Core, Unscreened with Thin Insulation Wall; Dimensions, Materials, Marking
- EIA-364: Electrical Connector/Socket Test Procedures Including Environmental Classifications
- IEC-60512: Electronic Equipment Tests and Measurements
- IEC-60529: Degrees of Protection Provided by Enclosures (IP Code)
   ISO 6722: Road Vehicles—60 V and 600 V Single-Core Cables—Dimensions, Test Methods and Requirements
- SAE J1128: Low Voltage Primary Cable

#### 3. REQUIREMENTS

#### 3.1. Design and Construction

Product shall be of the design, construction, materials and physical dimensions specified on the applicable product drawing.

#### 3.2. Ratings

Voltage: 250 V AC/DC, except 24-29, 24-31, 24-47 arrangements are 200 V AC/DC

Current (Amp): See Figure 1

	I	T.	
Contact	Wire Size	All Circuits	
Size	AWG [mm²]	Energized (A)	
4	4 [25.0-21.0]	100	
4	6 [16.0-13.0]	100	
8	8 [10.0-8.0]	60	
O	10 [6.0-5.0]	40	
	10 [6.0-5.0]	25	
12	12 [4.0-2.5]	25	
	14 [2.0]	18	
	12 [2.5]		
	14 [2.0]	13	
16	16 [1.5-1.0]		
	18 [0.8-0.75]	10	
	20 [0.5]	7.5	
	16 [1.5-1.0]		
20	18 [0.8-0.75]	7.5	
20	20 [0.5]		
	22 [0.35]	5	
	l	l	

Figure 1

Temperature: -55°C to +125°C
Ingress Protection (IP) Level: IP67

• Flammability: UL Recognized. Parts are made out of V-0 material and have been successfully tested to the 20 mm Flame Test per Standard UL-94.

Rev C 3 of 10



## 3.3. Test Requirements and Procedures Summary

Unless otherwise specified, all tests shall be performed at ambient environmental conditions.

See Appendix A for additional test requirements

See Appendix B for Test Procedure Comparison Chart

Test Description	Requirement	Procedure
Examination of Product	The connectors shall be correctly constructed, marked and shall show good quality and workmanship and match the customer drawing.	EIA-364-18 Visually inspected for use of materials, proper construction, correct part number and insert markings and over-all quality of workmanship. Poor molding fabrication, loose materials, damaged or improperly manufactured contacts, galling of metal parts, nicks and burrs of metal parts, torn seals or cracked plastic were considered adequate basis for rejection.
	ELECTRICA	AL
Insulation Resistance	1000 MΩ minimum at 25°C	MIL-STD-1344, Method 3003.1 Using a 500 VDC megohmeter check each contact to all other contacts and the shell electrically connected together.
Dielectric Withstanding Voltage	No evidence of breakdown or flashover or current leakage in excess of 2.0 milliamps.	MIL-STD-1344, Method 3001.1 Check each contact to all other contacts and the shell electrically connected together for breakdown / flashover when subjected to a 1500 VAC test potential for a period of 1 minute.
Contact Resistance	Calculated resistance across mated contact pairs shall not exceed 7.5 mOhms using 100 mA current	MIL-STD-1344, Method 3004.1 The resistance of an equal length of wire will be subtracted from measured reading to determine the increase in resistance due to the terminal. Test current: 10A for size 16 (18AWG)
Low Voltage Resistance	Maximum voltage drop for wire/contact assembly shall be 60 mV for solid and 100 mV for S&F terminals	MIL-STD-1344 method 3002.1 The resistance of an equal length of wire shall be subtracted from all readings to determine the added resistance of the terminal. Test voltage: 20 mV max open circuit. Test current: 100 mA

Figure 2 Cont.

Rev C 4 of 10



Test	Requirement	Procedure
Description	MECHANICA	 
Maintenance Aging	Failure shall consist of the inability to complete 10 cycles or breakage of any of the contact retention mechanism	MIL-STD-1344, Method 2002.1 Subject 10% of the cavities to 10 cycles of inserting and removing its respective contact pin and socket. Insert by hand, remove using removal tool.
Contact Retention	The contact shall remain in place.	MIL-STD-1344, Method 2007.1 Subject each wired contact to an applied load of 25 lbf (size 16) for a period of 15 seconds in a direction tending to push the contact or of the rear of the connector.
Durability	No evidence of damage to the contacts, contacting plating, connector housing or seals detrimental to reliable connector performance. Coupling torque must not increase as a result of cycling past the point where it can reasonably be done by hand.	MIL-STD-1344, Method 2016 The connector shall be mated and unmated for a total of 100 complete cycles at room temperature
Tool Abuse	Test up to five cavities from each sample. Test three times on each cavity. Pin and socket. There shall be no damage to the locking fingers or rear wire seals.	The applicable removal tool shall be inserted into the connector. With an axial load of 5 pounds applied, the tool shall be rotated 180° and then removed, also removing the terminal.
Vibration	No discontinuity in excess of 1.0 µs at 20 mV and 100 mA during the last hour of each axis. Shall meet visual requirements, show no physical damage and meet requirements of additional tests as needed.	MIL-STD-1344, Method 2005.1 Sine Sweep: 10 to 2000 Hz Sweep Cycle: 20 minutes Initial Displacement: .07 inch DA Maximum Max Acceleration: 20G's Test Duration: 12 hours Time Per Axis X, Y, Z: 4 hours Test Current first 3 hours each axis: 18AWG = 8A
Impact	No There shall be no cracking, uncoupling, or part breakage as a result of impact testing.	Wired mated connectors to be dropped from a height of 4 feet on to a concrete floor a total of 5 times.
Insert Retention	There shall be no damage as a result of the pull test. Connector halves to remain mated.	Apply a pulling force to the wire bundle that exist the rear of the connector for a period of 1 minute. The amount of load is to be 25 lbf times the number of cavities up to maximum of 100 lbf
	ENVIRONMEN	ITAL
Temperature Life	There shall be no evidence of torn seals, cracking, distortion or detrimental damage to the connector following the test.	MIL-STD-1344, Method 1005.1 The wired mated connectors shall be subjected to 1000 hours at 125°C.
Salt Spray	There should be no evidence of corrosion on the connector or terminals after the connector is removed from the test and cleaned with tap water.	MIL-STD-1344, Method 1001.1 Connector shall be fully mated, then submerged in a fine mist of 5% by weight of salt solution for 96 hour.

Figure 2 Cont.

Rev C 5 of 10



Test Description	Requirement	Procedure			
Fluid Immersion	There shall be no evidence of cracking, distortion or detrimental damage to the connector following the test.	MIL-STD-1344, Method 1016 Subject each connector to one fluid only. The wired mated connectors shall be submerged in the fluids below at listed temperature. Each connector shall be submerged for 5 minutes, then removed from the fluid to air dry for 24 hours. This cycle is to be completed a total of 5 cycles.			
		Fluid   Temperature (°C)			
Thermal Cycling	There shall be no evidence of cracking, distortion or detrimental damage to the connector following the test.	Cycle mated connectors for 1 hour minimum at –55°C followed by 1 hour minimum at +125°C at a rate of 3°C per minute. Repeat for 20 cycles.			
Water Immersion	All samples must pass insulation resistance. Then un-mate and check for water intrusion.	Heat mated connectors to 125° C for 2 hours. Immediately submerge mated connectors in water to a depth of 3 feet free ends (service connectors) remain out of water. Samples to remain in water 4 hours minimum. Then check insulation resistance.			

Figure 2 end

# 3.4. Product Qualification and Requalification Test Sequence

		Test Group No. (a)						
Test	1	2	3	4	5	6		
			Test Sequ	ience (b)				
Examination of Product	1	1	1	1	1	1		
Insulation Resistance	2	2	2	2	2	2		
Dielectric Withstanding Voltage	3	3	3	3	3	3		
Maintenance Aging	4		4					
Temperature Life		4		4		4		
Contact Retention	5		5					
Durability		5	6		4			
Tool Abuse				5	5			
Salt Spray		6	7			5		
Fluid Immersion	6	7	8	6	6	6		
Thermal Cycling	7	8				7		
Vibration	8			7	7			
Impact Test	9			8	8			
Insert Retention	10		9		9			
Water Immersion	11	9	10	9	10	8		
Low Voltage Resistance		10	11					
Contact Resistance	12	11	12	10	11	9		
Final Examination	13	12	13	11	12	10		

Rev C 6 of 10





#### NOTE

- (a) Specimens shall be prepared in accordance with applicable product drawings and shall be selected at random from current production.
- (b) All cavities use wire gauge per SAE J1128 suitable for the terminal size and with sufficient length to accommodate testing. The wire insulation shall be within the connector wire sealing range. Crimp characteristics (i.e. crimp height, crimp width, etc.) shall be checked prior to testing.
- (c) Specimen shall consist of 24-23 arrangement connectors with DEUTSCH Solid Terminal System size 16 nickel plated pins and sockets on 18 AWG SXL and DEUTSCH Stamped & Formed Terminal System size 16 nickel plated pins and sockets on 18 AWG SXL.
- (d) All unsealed cavities shall be secured with sealing Plugs. To prevent capillary action on the sealed connector, all free wire ends and test points (i.e. millivolt test connection) shall be sealed with alcohol-based RTV silicone or equivalent and covered with heat shrink tubing
- (e) Numbers indicate sequence in which tests are performed.

### 3.5 Appendix A Additional Test Requirements

Test Description		Requir	rement			Procedure
			ELECTI	RICAL	_	
Low Level Contact Resistance	Wire Size AWG [mm²] 16 [1.0] 18 [0.80] 20 [0.50] 22 [0.35]		Resistance (mΩ max) 6.0 7.5 11.0 17.0			EIA-364-23 Test with applied voltage not to exceed 20 mV open circuit and the test current shall be limited to 100 mA. The resistance of an equal length of wire (reference wire) shall be subtracted from the same reel as used for the connector wiring.
Contact Resistance	Contact Size	Wire Size AWG [mm²] 4 [25.0-21.0] 6 [16.0-13.0] 8 [10.0-8.0]	Test Currrent Amp 100	(mV	age op max) S&F	EIA-364-06 Using test currents as defined. The resistance of an equal length wire (reference wire) shall be subtracted from the actual readings to determine the added resistance of the terminal. The reference wire
	12	10 [6.0-5.0] 10 [6.0-5.0] 12 [4.0-2.5] 14 [2.0]	40 25 18			shall be from the same reel as used for the connector wiring.
	16	12 [2.5] 14 [2.0] 16 [1.5-1.0] 18 [0.8-0.75]	13 10 7.5	60	100	
	20	20 [0.50] 16 [1.5-1.0] 18 [0.8-0.75] 20 [0.50] 22 [0.35]	7.5			

Rev C 7 of 10



Test Description	Requirement		Procedure	
<u> </u>	MECHANICAL			
Vibration	There shall be no discontinuity in excess of one (1) µs at 20mV and 100 mA during the last hour of each axis. Shall meet visual requirements, show no physical damage and meet requirements of additional tests as needed.	Maximun Test Dura Time Per	78 mm DA : 20 G's s	
		Contact Size	Wire Size	Test Currrent
			AWG [mm²]	Amp
		4	4 [25.0-21.0] 6 [16.0-13.0]	46
			8 [10.0-8.0]	33
		8	10 [6.0-5.0]	23
			10 [6.0-5.0]	47
		12	12 [4.0-2.5]	17
			14 [2.0]	14
		16	12 [2.5]	
			14 [2.0]	10
			16 [1.5-1.0]	
			18 [0.8-0.75]	8
			20 [0.50]	5
		20	16 [1.5-1.0]	
			18 [0.8-0.75]	5
			20 [0.50]	_
			22 [0.35]	3
			22 [0.55]	3
Contact Retention	The contact shall remain in place.	maintena direct loa seconds push the the conn Testing N weights r Contac Size 4 8 12	me cavities from the cavities from the caying, such as specified in a direction contact out of ector. Either a Machine or equal to the caying be used.	bject to a I below for 15 tending to f the rear of Tension uivalent  orce
		20		

Rev C 8 of 10



# 3.6 Appendix B Test Procedure Comparison Chart

Test	MIL-STD- 1344 Method	EIA-364 Dash No.	Similar to SAE J2030 Paragraph	Similar to ISO 8092-2 Paragraph
Examination of Product	-	18	6.1	4.2
Insulation Resistance	3003.1	21	6.3	4.12
Dielectric Withstanding Voltage	3001.1	20	-	4.13
Low Level Contact Resistance	3002.1	23	6.2	4.8
Contact Resistance	3004.1	06	6.4	4.8
Maintenance Aging	2002.1	24	6.6	-
Contact Retention	2007.1	29	6.18	4.7
Durability	2016	09	6.11	4.3
Vibration	2005.1	28	6.15	-
Shock	2004.1	27	6.16	-
Impact	-	42	6.17	4.20
Connector Retention	-	-	6.20	-
Temperature Life	1005.1	17	6.7	4.18
Salt Spray	1001.1	26	6.12	4.16
Fluid Immersion	1016	10	6.14	4.23
Thermal Cycle	-	-	-	-
Thermal Shock	1003.1	32	6.13	4.22
Moisture	-	-	-	-
Water Immersion	-	-	6.19	4.9

Rev C 9 of 10



## 4. REVISION HISTORY

Rev Ltr	Brief Description of Change	Date	Dwn	Apvd
Α	Initial Release	5-Mar-2017	PV	DM
В	General Specification clarification to reflect actual product specification, updated Figure 1 to include 4AWG and other missing wire gage specs, added missing MIL-STD-1344 test procedures as needed, updated notes on Page 7, added Appendix A. Additional test requirements and Appendix B Test Procedure Comparison Chart	19-Dec-2017	VNB	DM
С	<ul> <li>Page 1, Sec 2.1. Deleted 0425-013-1800, 0425-014-2400, 0425-021-0000.</li> <li>Page 1, Sec 2.1. Added 114-151001, 114-151002, 114-151003, 114-151004, 114-151006, 114-151015.</li> <li>Page 3, sec 3.2 Flammability. Changed per UL test report (is) UL Recognized. Parts are made out of V-0 material and have been successfully tested to the 20 mm Flame Test per Standard UL-94. (was) UL94 V-1. Parts have been successfully tested to the 20 mm Flame Test per Standard UL-94.</li> </ul>	11-May-2020	DM	DM

Rev C 10 of 10