

DESIGN OBJECTIVES

JUL 29 1994

The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore AMP Incorporated makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, AMP Incorporated may change these requirements based on the results of additional testing and evaluation. Contact AMP Engineering for further details.

1. SCOPE

1.1. Content

This specification covers performance, tests and quality requirements for AMP-LATCH* DIP plug connector. These connectors are pin contacts in housings crimped to .050 inch centerline ribbon cable with 30, 28, or 26 AWG solid or 28 or 26 AWG stranded conductors. Complete assemblies can be plugged into .100 X .300 or .100 X .600 inch centerline DIP sockets or soldered to printed circuit boards.

1.2. Qualification

When tests are performed on subject product line, procedures specified in AMP 109 series specifications shall be used. All inspections shall be performed using applicable inspection plan and product drawing.

2. APPLICABLE DOCUMENTS

The following documents form a part of this specification to the extent specified herein. Unless otherwise specified, latest edition of the document applies. In the event of conflict between requirements of this specification and product drawing, product drawing shall take precedence. In the event of conflict between requirements of this specification and referenced documents, this specification shall take precedence.

2.1. AMP Documents

- A. 109-1: General Requirements for Test Specifications
- B. 109 Series: Test Specifications as indicated in Figure 1. (Comply with MIL-STD-202, MIL-STD-1344 and EIA RS-364)
- C. Corporate Bulletin 401-76: Cross-reference between AMP Test Specifications and Military or Commercial Documents
- D. 114- : Application Specification
- E. 501- : Test Report

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of design, construction and physical dimensions specified on applicable product drawing.

* Trademark

Product Code:

CONTROLLED DOCUMENT This specification is a controlled document per AMP Specification 102-21. It is subject to change and Corporate Standards should be contacted for latest revision.				DR		AMP AMP Incorporated Harrisburg, PA 17105-3608		
				CHK				
APP				NO		REV		LOC
				108-1538		0		B
				PAGE		TITLE		
				1 OF 6		CONNECTOR, AMP-LATCH, DIP PLUG		
LTR	REVISION RECORD	APP	DATE					

COPYRIGHT 1984 BY AMP INCORPORATED ALL RIGHTS RESERVED.

3.2. Materials

- A. Contact: Phosphor bronze, full tin-lead or duplex gold/tin-lead over nickel underplating
- B. Cover: Thermoplastic, black, UL94V-0
- C. Housing: Thermoplastic, black, UL94V-0

3.3. Ratings

- A. Voltage: 250 volts UL, 150 volts CSA
- B. Current: Signal application only
- C. Temperature: -65 to 105°C

3.4. Performance and Test Description

Product is designed to meet electrical, mechanical and environmental performance requirements specified in Figure 1. Unless otherwise specified, all tests shall be performed at ambient environmental conditions per AMP Specification 109-1.

3.5. Test Requirements and Procedures Summary

Test Description	Requirement	Procedure
Examination of product.	Meets requirements of product drawing and AMP Spec 114-_____.	Visual, dimensional and functional per applicable quality inspection plan.
ELECTRICAL		
Termination resistance.	15 milliohms maximum.	AMP 109-6-1. Subject mated contacts assembled in housing to 50 mv maximum open circuit at 100 ma maximum. See Figure 3.
Insulation resistance.	5000 megohms minimum.	AMP Spec 109-28-4. Test between adjacent contacts of mated connector assemblies.
Dielectric withstanding voltage.	500 vac at sea level.	AMP Spec 109-29-1. Test between adjacent contacts of mated connector assemblies.
MECHANICAL		
Solderability.	Solderable area shall have minimum of 95% solder coverage.	AMP Spec 109-11-2. Subject contacts to solderability.

Figure 1 (cont)

Test Description	Requirement	Procedure
Vibration, random.	No discontinuities greater than 1 microsecond. See Note (a).	AMP Spec 109-21-7. Subject mated connectors to 3.14 G's rms. 1 hour in each of 3 mutually perpendicular planes. See Figure 4.
Physical shock.	No discontinuities greater than 1 microsecond. See Note (a).	AMP Spec 109-26-1. Subject mated connectors to 30 G's half-sine shock pulses of 11 milliseconds duration. 3 shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks. See Figure 4.
ENVIRONMENTAL		
Thermal shock.	See Note (a).	AMP Spec 109-22. Subject mated connectors to 5 cycles between -65 and 105°C.
Humidity-temperature cycling.	See Note (a).	AMP Spec 109-23-3, Condition B. Subject mated connectors to 10 cycles between 25 and 65°C at 95% RH.
Temperature life.	See Note (a).	AMP Spec 109-43. Subject mated connectors to temperature life at 105°C for 1000 hours.

(a) Shall meet visual requirements, show no physical damage and shall meet requirements of additional tests as specified in Test Sequence in Figure 2.

Figure 1 (end)

3.6. Product Qualification and Requalification Test Sequence

Test or Examination	Test Group (a)				
	1	2	3	4	5
	Test Sequence (b)				
Examination of product	1,6	1,5	1,5	1,8	1,3
Termination resistance	2,5	2,4	2,4		
Insulation resistance				2,6	
Dielectric withstanding voltage				3,7	
Solderability					2
Vibration	3				
Physical shock	4				
Thermal shock				4	
Humidity-temperature cycling			3	5	
Temperature life		3			

- (a) See Para 4.1.A.
 (b) Numbers indicate sequence in which tests are performed.

Figure 2

4. QUALITY ASSURANCE PROVISIONS

4.1. Qualification Testing

A. Sample Selection

Samples shall be prepared in accordance with applicable Instruction Sheets and shall be selected at random from current production. All test groups shall each consist of minimum of 5 connectors.

B. Test Sequence

Qualification inspection shall be verified by testing samples as specified in Figure 2.

4.2. Requalification Testing

If changes significantly affecting form, fit or function are made to product or manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of original testing sequence as determined by development/product, quality and reliability engineering.

4.3. Acceptance

Acceptance is based on verification that product meets requirements of Figure 1. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify product. When product failure occurs, corrective action shall be taken and samples resubmitted for qualification. Testing to confirm corrective action is required before resubmittal.

4.4. Quality Conformance Inspection

Applicable AMP quality inspection plan will specify sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with applicable product drawing and this specification.

Figure 3
Termination Resistance Measurement Points

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

PAGE NO
5

108-1538

REV LOC
0 B

Figure 4
Vibration & Physical Shock Mounting Fixture

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

PAGE NO
6

108-1538

REV LOC
0 B