
Surface Mount .100 Inch Centerline Standard Pitch DIP Switch

1. SCOPE

1.1. Content

This specification covers performance, tests and quality requirements for AMP* surface mountable Dual-Inline Packaging (DIP) switches.

1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 1 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

1.3. Qualification Test Results

Successful qualification testing on the subject product line was completed in Jun98. The Qualification Test Report number for this testing is 501-443. This documentation is on file at and available from Engineering Practices and Standards (EPS).

2. APPLICABLE DOCUMENTS

The following AMP documents form a part of this specification to the extent specified herein. Unless otherwise specified, the latest edition of the document applies. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

- A. 109-1: General Requirements for Test Specifications
- B. 109 Series: Test Specifications as indicated in Figure 1
- C. Corporate Bulletin 401-76: Cross-reference between AMP Test Specifications and Government or Commercial Documents
- D. 501-443: Qualification Test Report

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

3.2. Materials

Materials used in the construction of this product shall be as specified on the applicable product drawing.

3.3. Ratings

- A. Current:
 - 1. Non-switching: 100 milliamperes at 50 vdc maximum
 - 2. Switching: 100 milliamperes at 20 vdc maximum
- B. Temperature:
 - 1. Operating: -20 to 85°C
 - 2. Storage: -40 to 85°C

3.4. Performance and Test Description

Product is designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1. Unless otherwise specified, all tests shall be performed at ambient environmental conditions per AMP Specification 109-1.

3.5. Test Requirements and Procedures Summary

Test Description	Requirement	Procedure
Examination of product.	Meets requirements of product drawing.	Visual, dimensional and functional per applicable quality inspection plan.
ELECTRICAL		
Dry circuit resistance.	25 milliohms maximum initial. 50 milliohms maximum final.	AMP Spec 109-6-6. Subject switches to 20 mv maximum open circuit at 100 ma maximum. See Figure 3.
Insulation resistance.	1000 megohms minimum final.	AMP Spec 109-28-4. Test between adjacent switch contacts with switches in the ON position and between opposite switch contacts with the switches in the OFF position.
Dielectric withstanding voltage.	500 vac at sea level. 1 minute hold with no breakdown or flashover. 1.3 milliamperes maximum leakage current.	AMP Spec 109-29-1. Test between adjacent switch contacts with switches in the ON position and between opposite switch contacts with the switches in the OFF position.
Capacitance.	5 picofarads maximum.	AMP Spec 109-47. Test between a minimum of 10 adjacent switch contacts in the ON position at a frequency of 1 MHz.
MECHANICAL		
Vibration, random.	No discontinuities of 1 microsecond or longer duration. See Note.	AMP Spec 109-21-7. Subject mounted switches in the ON position to 3.13 G's rms between 5-500 Hz. 15 minutes in each of 3 mutually perpendicular planes.

Figure 1 (cont)

Test Description	Requirement	Procedure
Mechanical shock, specified pulse.	No discontinuities of 1 microsecond or longer duration. See Note.	AMP Spec 109-26-1, except 30 G's. Subject mounted switches in the ON position to 30 G's half-sine shock pulses of 11 milliseconds duration. 3 shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks.
Durability.	No open circuits in the ON position. No short circuits in the OFF position. See Note.	AMP Spec 109-27. Subject mounted switches to 2000 actuation cycles with an applied resistive load of 100 milliamperes maximum at 20 vdc.
Resistance to soldering heat.	See Note.	AMP Spec 109-63-6. Subject switches in the OFF position to 255 ± 5°C for 55 ± 5 seconds.
Actuation force.	100 to 700 grams initial. 60 grams minimum final. See Note.	Measure force necessary to move the actuator from the OFF to the ON and return to the OFF position. Repeat for a minimum of 10 positions. See Figure 4.

ENVIRONMENTAL

Thermal shock.	See Note.	AMP Spec 109-22. Subject unmounted switches in the OFF position to 5 cycles between -20 and 85°C.
Humidity-temperature cycling.	See Note.	AMP Spec 109-23-3, Condition B. Subject unmounted switches in the OFF position to 10, 24 hour cycles between 25 and 65°C at 95% RH.
Temperature life.	See Note.	AMP Spec 109-43. Subject mounted switches in the ON position to temperature life at 85°C for 1000 hours.
Mixed flowing gas.	See Note.	AMP Spec 109-85-2. Subject mounted switches in the ON position to environmental class II for 14 days.

NOTE

Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in the Product Qualification and Requalification Test Sequence shown in Figure 2.

Figure 1 (end)

3.6. Product Qualification and Requalification Test Sequence

Test or Examination	Test Group (a)				
	1	2	3	4	5
	Test Sequence (b)				
Examination of product	1,9	1,5	1,5	1,8	1,4
Dry circuit resistance	3,7	2,4	2,4		
Insulation resistance				2,6	
Dielectric withstanding voltage				3,7	
Capacitance					3
Vibration	5				
Mechanical shock	6				
Durability	4				
Resistance to soldering heat					2
Actuation force	2,8				
Thermal shock				4	
Humidity-temperature cycling				5	
Temperature life		3			
Mixed flowing gas			3		

NOTE (a) See Para 4.1.A.
 (b) Numbers indicate sequence in which tests are performed.

Figure 2

4. QUALITY ASSURANCE PROVISIONS

4.1. Qualification Testing

A. Sample Selection

Samples shall be prepared in accordance with applicable Instruction Sheets and shall be selected at random from current production. All test groups shall each consist of 6 switches with 3 switches of the largest position and 3 switches of the smallest position. Prior to testing and after soldering to printed circuit boards, sealed samples for test groups 2, 3 and 4 shall be conditioned as follows: Immerse samples in distilled water at 70 +0 -5°C for 5 minutes. Dry samples in oven at 125 ± 3°C for 5 minutes. Remove seal from samples. Activate each position ON and OFF 5 times.

B. Test Sequence

Qualification inspection shall be verified by testing samples as specified in Figure 2.

4.2. Requalification Testing

If changes significantly affecting form, fit or function are made to the product or manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality and reliability engineering.

4.3. Acceptance

Acceptance is based on verification that the product meets the requirements of Figure 1. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify the product. If product failure occurs, corrective action shall be taken and samples resubmitted for qualification. Testing to confirm corrective action is required before resubmittal.

4.4. Quality Conformance Inspection

The applicable AMP quality inspection plan shall specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification.






Figure 3
Dry Circuit Resistance Measurement Points



Standard Slider



Recessed Slider

Figure 4
Actuation Force