


SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION



| | MIKE SIKIP LI | | INSULATION L | DIAMETER RANGE | |
|---|-------------------------|-----------------|---------------------------------------|-----------------|--|
| | 4.35-5.11 mm [.171 | 201 IN] | \emptyset 1.42-2.03 mm [.056080 [N] | | |
| | TERMINAL APPLICATION | NONE | - | - | |
| | SPECIFICATION | - | - | - | |
| 0 | TERMINALS APPLIED 25 27 | | | | |
| | TE TERMINAL | WATLOW TERMINAL | TE TERMINAL | WATLOW TERMINAL | |
| | 2303683-1 | 716055 | 2303683-2 | 716056 | |
| | | | | | |

| INSUL | | - | _ | | | | |
|----------|--------------------------------|-----------------|---------|------|---------------|----------|--------|
| | OR INS ⁷ 08-3504 | TRUCTIONS 42 | | | | | |
| | | | | | | | |
| TERMINAL | DATA: | WATLOW TE | ERMINAL | | TE CRIMP | SPECIFIC | CATION |
| TERMINAL | NAME: | FORMED | PIN S | TRIP | TERMINAL | - | |
| WIRE S | TRIPIE | - NGTH | | INS | III ATION DIA | METER RA | NGE |

| | PPLICATOR DATA | |
|--------------|------------------|------|
| A | ١ | |
| CRIMP | SIZE | TYPE |
| WIRE | 2.29 mm [.090] | F |
| INSUL | - | ı |
| I Applica | TOR INSTRUCTIONS | |

| THIS DRAWING IS UNPUBLIE | | RELEASED FOR PUBLICATION | 20 | | |
|--|----------|--------------------------|------------|--|--|
| C COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED. | | | | | |
| P A R T N U M B E R | REVISION | DESCRIPTION | FEED TYPE | | |
| 2-2836480-1 | В | FINE CRIMP HEIGHT ADJUST | MECHANICAL | | |
| 2-2836480-2 | В | FINE CRIMP HEIGHT ADJUST | PNEUMATIC | | |
| 7-2836480-7 | А | CRIMP TOOLING KIT | - | | |

7 - 18023 - 7 SCR, SKT HD CAP M3 X 4.0

REVISIONS DESCRIPTION SEE SHEET 1

PACIFIC VERSION TERMINATOR INTERFACE ADAPTER

A 66

