





Α	PPLICATOR DATA	١
CRIMP	SIZE	TYPE
WIRE	1.83 mm [.072]	F
INSUL	2.40 mm [.094]	F
APPLICA	TOR INSTRUCTIONS 408-10389	

TERMINAL DATA:	SUMITOMO TERMINA	AL SUMITOMO CRIM	MP SPECIFICATION
TERMINAL NAME:	2.8 MALE TER	RMINAL	
WIRE STRIP LE	NGTH	INSULATION D	IAMETER RANGE
4.61-5.37 mm [.181-	.211 IN]	Ø1.90-2.20 mm l	[.075087 [N]
	82305257 Rev 2014	/10/15 -	-
APPLICATION SPECIFICATION	-	-	-
TERMINALS AP	PLIED /		
TE TERMINAL ·	SUMITOMO TERMINAL :	TE TERMINAL	SUMITOMO TERMINAL
2318319-1	8230-5257		

WIRE SIZE 🛞 T	CRIMP HEIGHT mm [INCH]	CRIMP HEIGHT 9 REFERENCE SETTING
1.00mm2	1.30+/-0.05 [.051+/002]	4.5
0.75mm2	1.25+/-0.05 [.049+/002]	5.3
0.50mm2	1.20+/-0.05 [.047+/002]	5.8



1 RECOMMENDED SPARE PARTS

2 GREASE BEARING SURFACES LIGHTLY

3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

APPLICATOR SPECIFIC DATA TO BE ENTERED INTO BLANK MEMORY CHIP AT ASSEMBLY. SEE BELOW FOR PART NUMBER:
MECHANICAL FEED WITH "SMART APPLICATOR" CONVERSION: 8-2836822-4
PNEUMATIC FEED WITH "SMART APPLICATOR" CONVERSION: 8-2836822-4
SERVO FEED WITH "FINE CRIMP HEIGHT ADJUST": 8-2836822-5

5. ADJUSTMENT OF THE STRIPPER MAY BE REQUIRED WHEN MOVING THE APPLICATIONS.

APPLY PART NUMBER 1-23419-5 LOCTITE TO THREADS OF ITEM 62.
APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.

GREASE THREADS, GROOVE AND O-RING ON ITEMS 139 & 152.

MAGNET MUST BE ORIENTED CORRECTLY IN ORDER TO PROPERLY ACTUATE THE COUNTER.

ORIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.

SPARE FEED CAM STORAGE LOCATION REFER TO INSTRUCTION SHEET FOR ADDITIONAL INFORMATION.

TO CONVERT THE APPLICATOR TO A NON-CARRIER CUTTING STYLE, REMOVE ITEM 13 AND ATTACH TO THE LOCATION ON BACK SIDE OF THE HOUSING. REFER TO INSTRUCTION SHEET FOR ADDITIONAL INFORMATION.

12 TERMINAL LUBRICANT IS RECOMMENDED.

\*WARNING

ON INSTALLATION, SET WIRE DISC, ITEM 40 TO LARGEST WIRE SIZE SETTING. USE OF SETTINGS BELOW MINIMUM REQUIRED CRIMP HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.

-	1	1	1	1	2119782-1	FINE ADJUST HEAD ASM, PACIFIC STYLE	251
- 77	- 27	- 25	- 22	- 21	PART NO	DESCRIPTION	I T E M NO

## PACIFIC VERSION

Shown on sheets 3 of 4 & 4 of 4 (Atlantic version shown on sheets 1 of 4 & 2 of 4)

				<u> </u>		- SEE S	HEET 1	-
_					T			
	-	-	-	1	-	2119640-1	PUSH ROD, AIR FEED BUSHING, FLANGED	250
	-	1	1	1	1	1 - 22279 - 3	SPRING, COMPRESSION	246
	-	1	1	1	1	2119082-5	CAM, SNAIL, INSULATION ADJUSTMENT WASHER, WAVE SPRING, CREST-TO-CREST	2 4 4 2 4 3
6	-	1	1	1	1	2119083-1	RETAINER, INSULATION DIAL	242
	-	1	1	1	1	7-18023-7	SCR, SKT HD CAP M3 X 4.0	241
	-	-	2	_	1	2168400-6 2119580-1	SHCS, LOW HEAD, ROHS, M5 X 16  MECHANICAL FEED ASSEMBLY	240
	-	-	-	1	-	2063440-1	AIR FEED MODULE	238
	-	-	1	_	-		TAG, IDENTIFICATION  SPACER, FEEDER	213
	-	-	-	2	-		RING, RETAIN, EXTERN, 3/16 CRESCENT	172
	-	1 REF	1 REF	1 REF	1 REF		MAGNET, RARE EARTH HIGH ENERGY COUNTER, MAGNETIC	166
	-	-	-	1	-		SPRING, FEED FINGER	163
7	-	1	1	1	1		O-RING, .801 ID, .070 DIA. MAT.	152
	-	1	1	1	1		FEED CAM, AIR FEED  DETENT PIN	151
	-	1	1	1	1		SCR, BHSC, RoHS (M4 X 16)	1 4 4
	-	4	4 -	4	1		SHCS, LOW HEAD, ROHS, M4 X 20 FEED CAM, POST FEED	1 4 3
	-	1	1	1	1	1-2119656-0	APPLICATOR BASIC ASSEMBLY, SF	1 4 1
<u> </u>	-	1	1	1	1 1		RAM, ASIAN STYLE, SIDE FEED  BOLT, ADJUSTMENT	1 4 0
1	-	-	-	1	_	3-23627-7	PIN, RETAIN, GRVD, 3/16 X .854	137
	-	-	- REF	1 -	-		HOLDER, FEED FINGER, AF MEMORY CHIP, PROGRAMMED	136
		_	1	_	-		SERVO FEED LATCH ASM	133
	-	- 1	REF 1	- 1	_ 1	2119944-1 2119955-1	FEED FINGER ASSEMBLY, SF ASSY, LUBRICATOR, SIDE FEED	1 1 7
12	-	1	1	1	1	455888-5	SPACER, CRIMPER	82
	-	1	1	1	1	2119956-1	DOCUMENTATION PACKAGE	7 1
	-	2	2	2	2		TAG, IDENTIFICATION  SCREW, DRIVE, RH, ROHS, 2 x .188	67
	-	1	1	1	1	2119793-1	LIMITER, ADJUSTMENT BOLT	63
6	-	3	3	3	3	992763-5 5-18022-5	SCR, SET, SOC, CONE POINT, M3 x 4.0° SCR, HEX HD CAP, M4 X 6.0	62 59
	-	-	-	1	1	1338685-1	PAWL, FEED	56
	-	2	2	2	2		SCR, SKT HD CAP, RoHS, M4 X 10  NUT, HEX, REG, RoHS, M3	53
	-	1	1	1	1		BUMPER, HOLD DOWN	51
	-	1	1	1	1 2	690753-2 18023-9	SPACER, TONKER	50
	-	_		-	1		SCR, SKT HD CAP M4 X 6.0  FEED CAM, PRE FEED	49
	-	1	1	1	1		SCR, BHSC, RoHS (M8 X 25)	41
	-	1	1	1	1		DISC, NUMBERED FA WIRE ADJUSTMENT APPLICATOR SHIM PACK	40
	-	1	1	1	1		RAM WASHER, PRECISION	38
	-	2	2	2	2		SUPPORT, TERMINAL SCR, BHSC, RoHS (M4 X 20)	34
	-	1	1	1	1	2161328-1	HEX HEAD, FLANGED, M5 x 8mm LONG	32
	-	1	1	1	1		SPACER, STRIP GUIDE  ASSEMBLY, STRIP GUIDE	30
	-	1	1	1	1	455888-4	SPACER, CRIMPER	28
	-	1	1	1	1	240792-5	DRAG, TERMINAL STRIP GUIDE	25
	-	1	1	1	1		SCR, SKT HD CAP, RoHS, M4 X 8.0	21
	-	2	2	2	2		WASHER, FLAT, REG M4	20
	_	1	1	1	1	2119533-1 2119806-1	STRIPPER, SIDE FEED INSERT, SHEAR	1 9
	_	1	1	1	1	3-22280-3	SPRING, COMPRESSION	12
	-	1	1	1	1		STOP, SHEAR SHEAR HOLDER, FRONT	11
	-	1	1	1	1	1803095-1	FLOATING SHEAR, FRONT -	9
1	1	1 -	<u> </u>	1 -	1 –	1803554-4	ANVIL, COMBINATION	8 7
	-	-	_	-	_	-	-	6
	-	1	1	1	1		DEPRESSOR, SHEAR BLOCK, CRIMPER SPACER	5 4
	1	1	1	1	1	2-1803016-3	CRIMPER, INSULATION F	3
$\bigwedge$	-	1	1	1	1	455888-3 6-568176-4	SPACER, CRIMPER CRIMPER, WIRE	2
1 \	_ 7 7	- 27	- 25	- 22	- 21		DESCRIPTION	ITEM
G IS A ECT TO SHOW	CONTROLLED CHANGE AND D BE CONTAC			TRONICS CORF ERING ORGANI		DWN 14JUN2017	TE Connectivity	NO
SHOUL ENSIO						K.HUANG  CHK L.ZHANG  14JUN2017	Harrisburg, PA 17105-3608	
mm mm		0 PL		CES UNLE E SPECIF <del>L</del> -		APVD 14JUN2017 L.ZHANG PRODUCT SPEC	Ocean Side Feed	
_		I PL 2 PL 3 PL	.C <u>=</u> .C <u>=</u>	±- ±- ±-		- APPLICATION SPEC	Applicator 	
$\bigoplus$				±-			SIZE   CAGE CODE   DRAWING NO   REST	RICTED TO
( <del>)</del>		4 PL ANGL FINI	.ES	<u>±</u>	-	- WEIGHT	A   00779 C=2836822	_

REVISIONS

DESCRIPTION

SET UP GAUGE

2119599-1

66

