LTR

REVISION RECORD

# **Product Specification**

# 108-5294

# .187 Series, Sealed Connector

# 1. Scope:

## 1.1 Contents

This specification covers the requirements for product performance, test methods and quality assurance provisions of .187 Series, Sealed Connector.

The applicable product descriptions and part number are as shown in Fig. 1:

Product Part No.	Descriptions				
175087	Tab Contact (M Size), Waterproof Type				
175088	Tab Contact (L Size), Waterproof Type				
175090	Receptacle Contact (M Size), Waterproof Type				
175091	Receptacle Contact (L Size), Waterproof Type				
176143	2-Position, Cap Housing Assembly				
176146 2-Position, Plug Housing Assembly					

Fig. 1




Fig. 2

						DR.	5/13 '91					
						Y. Kind	oshita	SHEET OF			AMP (Japan), Ltd. Kawasaki, Japan	
						СНК.	5/13 '91	1			nanosom, copon	
			1		<u> </u>	1		13	LOC	FOC	NO.	REV.
DIST.	С	REVISED FJ00-0277-94	77	577/	1/18	K. Oda	1	1.5	J	Α	108-5294	C
ä	В	REVISED RFA-1935	Y.K	K.O	1/28'92	APP.	5/14 '91	NAME			~	
PRINT	A	Released RFA-1779	Y,K	к.о	5/1/191			.18	7 Se	ries,	, Sealed Connecto	r
£		DELEGION DEGODO	100	0	5.75	S. Isoh	ata	1				

DR CHK DATE

# 2. Applicable Documents:

The following documents from a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

# 2.1 AMP Specifications:

A. 109-5000

Test Specification, General Requirements for Test Methods

B. 114-5126

Application Specification, Crimping of 187 Series, Water-proof Contact

C. 501-5021:

Test Report.

D. CM-488J:

Customer Manual, 187 Series, Sealed Connector

# 2.2 Military Standard and Specifications:

MIL-STD-202

Test Methods for Electronic and Electrical Component Parts.

## 2.3 Commercial Standard and Specification:

A. JASO D605

**Multi-Connectors for Automotives** 

B. JASO D7101

Testing Method of Molded Plastics Parts for Automobile

C. JIS C 3406

Low-Voltage Cables for Automobile

D. JIS D 0203

Method of Moisture, Rain and Spray Test for Automobile Parts

E. JIS D 0204

Method of High and Low Temperature Test for Automobile Parts

F. JIS D 1601

Vibration Testing Method for Automobile Parts

G. JIS K 6301

Physical Testing Methods for Vulcanized Rubber


H. JIS K 2202

Motor Gasoline

#### Requirements:

## 3.1 Design and Construction:

Product shall be of the design, construction and physical dimensions specified in the applicable product drawing.



3.2 Materials:

A. Contact:

Tab and Receptacle:

Brass

Housing:

Cap and Plug Housing Molded Polybuthylene Terephthalate (PBT)

Keying and Plate

Molded Polybuthylene Terephthalate (PBT)

Accessories and Hardware:

Seal Ring

Silicon Rubber

3.3 Ratings:

Voltage Rating:

13.2 V DC

Current Rating: В.

25 A

C. Temperature Rating: -30 °C to 105 °C


3.4 Performance and Test Descriptions:

> The product is designed to meet the electrical, mechanical and environmental performance requirements specified in Fig. 3. All tests are performed at ambient temperature unless otherwise specified.

3.5 Test Requirements and Procedures Summary:

Para	Test Items	Requirements				Procedures
3.5.0	Confirmation of Product	Product shall be conforming to the requirements of applicable product drawing and Application specification 114-5126				Visually, dimensionally and functionally inspected per applicable inspection plan.
		· <u>·</u>	Ele	ctrical Perfo	ormance	
	Termination Resistance		re Size (AWG)	Test (A) Current	Resistance (mΩ) (max.)	
3.5.1	(Specified Current)	0.5	# 20	8.25	3.0 (Initial)	contact test circuit in mated
		0.85 # 18 11.25		3.0 (111101817	connectors. by probing between Y-Y'.	
		1.25	# 16	14.25	10.0 (Final)	See Fig. 4. Calculate Termination
		2	# 14	18.75	_	resistance after deducting resistance of
		3	# 12	25.5		150 mm long wire used for wiring.

Fig. 3 (To be cont'd)



Para	Test Items	Requirements	Procedures
3.5.2	Termination Resistance (Low Level)	3 m $\Omega$ max. (Initial) 10 m $\Omega$ max. (Final)	Subject mated contacts assembled in housing to closed circuit current of $10\pm0.5$ mA. at open circuit voltage of $20\pm1$ mV Fig. 4.
3.5.3	Insulation Resistance	100 MΩ min. (Final)	Measure by applying test potential (500V DC) between the adjacent contacts, and between the contacts and ground in the unmated connector.  See Fig. 5
3.5.4	Dielectric Strength	No abnormalities such as corona and flashover shall be present.	Measure by applying test potential of 1000 V AC between the adjacent contacts, and between the contacts and ground in the mated connector for 1 minute. See Fig. 5.  MIL-STD-202, Method 301
3.5.5	Current Cycling	Termination resistance (low level) $10~\text{m}\Omega$ max. (Final)	Subject mated contacts to 300 cycles of intermitent current application of the specified intensity in Para. 3.5.1, 45 minuted ON, and 15 minutes OFF.
3.5.6	Temperature Rise vs. Current	60°C max. under loaded specified current. Fig. 4.	Measure temperature rise by energized current, probing at wire crimp of receptacle contact. Obtain temperature rise by subtracting room temperature.  AMP Spec. 109-5310
3.5.7	Current Leakage	3.5 mA max.	After exposing connector in test chamber (60±5°C, 90-95 % R. H.) for I hour, measure by applying DC 12 V to the circuit.  See Fig. 5.

Fig. 3 (To be cont'd)

SHEET	Æ	71	/IF	<b>&gt;</b>	AMP (Japar Kawasaki, .	
4 OF 13	roc	1.0C	NO.	10	8-5294	REV.
NAME .18'	7 Se	ries	, Sea	aled	Connect	or

		(Rev. MAR 91)				
_	Para.	Test Items	<u></u>	Requir	rements	Procedures
294				Physica	al Performance	
108-5	3.5.8	Vibration Sinusoidal High Frequency		than 1 n	scontinuity microsecond (s)	Subject mated connectors to 20-200 Hz vibration traversed in 1 minute with 4.5 G (44 m/s²) accelerated velocity: for 4 hours in up-down, 2 hours in back-forth, and 2 hours in right-left directions.
NUN	3.5.9	Connector Mating Force	No. of	Pos.	Mating Force N <sub>MAX</sub> (kgf max.)	Using autograph measure the force required to mate connector without
ome r a s e	0.0.0	İ	2		49 (5.0)	locking latch by operating at 100 mm a minute.
Customer Release	3.5.10	Connector Unmating Force	No. of	Pos.	Unmating Force N <sub>MAX</sub> (kgf max.)	Using autograph measure the force required to unmate connector without
	0,0.10	I VICE	2		29 (3.0)	locking latch, by operating at 100 mm a minute.
SECURITY CLASSIFICATION :	3.5.11	Handling Ergonomics	sharp ed	lges tha issembl	l be free from at can injure or lers' hands during mating.	Manually repeat mating and unmating to confirm the absence of sharp edges.
	3.5.12 (a)	Contact Retention Force (a)	78 N (8 k	(gf) min	1.	Apply axial load to contact by operating without double lock plate at a rate of 100 mm a minute. Use contact lead crimped on 0.85 mm <sup>2</sup> wire or greater.
	3.5.12 (b)	Contact Retention Force (b)	98 N (10	kgf) mi	in.	Measure in the same manner as (a), with double lock plate set in effect.
	3.5.13	Contact Disengaging Force	2 N (200 kgf) min. per contact.			Apply an axial pull-off load to mated contacts on the tester at a rate of 100 mm a minute.
	3.5.14	Crimp Tensile Strength	Wire Size         Crimp Tensile (min.)           mm²         (AWG)         N (kgf)           0.5         #20         88 (9)           0.85         #18         128 (13)           1.25         #16         177 (18)           2         #14         265 (27)           3         #12         294 (30)			Apply an axial pull-off load to crimped wire of contact secured on the tester, at a rate of 100 mm a minute.

Fig. 3 (To be cont'd)

SHEET	#	//	ЛF	AMP (Japar Kawasaki,	
5 OF 13	roc j	L0C	NO.	108-5294	REV.
NAME .18	7 Se	ries	, Sea	led Connect	or

Para.	Test Items	Requirements	Procedures						
3.5.15	Durability (Repeated Mate/Unmating)	Termination Resistance (Low Level) (Final) 10 mΩ max.	Mate and unmate connectors for 30 cycles at a rate of 100 mm a minute.  Determine strength of housing locking mechanism by applying an axial pull-off load to engaged housings, until the housings are separated with or without breakage of locking device.  Securely fasten one of the mated connectors on a sturdy bench, and apply prying and twisting motions of 196 N (20 kgf·cm (T)) to free end connector in back forth direction at every 1 mm depth graduation until separation. Making this a cycle, repeat for 30 cycles. After completion, repeat in the right-left direction in the same manner for another 30 cycles.  See Fig. 6.						
3.5.16	Housing Lock Strength	98 N (10 kgf) min.							
3.5.17	Resistance to "Kojiri"	After testing, the requirements per Test Sequence specified in Para. 3.6 shall be met.							
Environmental Requirements									
3.5.18	Thermal Shock	Termination Resistance (Low Level) (Final) 10 mΩ max.	Subject mated connectors to 5 cycles between $-30\pm5$ °C and $85\pm5$ °C, each cycle consisting of 2 hours holding at each extreme with temperature transition within 5 minutes.						
3.5.19	Humidity, Steady State	Termination Resistance (Low Level) (Final) 10 mΩ max.	Subject mated connectors to steady state humidity at 60 °C and 90-95% R.H. by applying test potential of 12 °DC. Measure after reconditioning to room temperature.						
3.5.20	Salt Spray	Termination Resistance (Low Level) (Final) 10 mΩ max.	Subject mated connectors to 5 % salt concentration for 96 hours for 2 cycle with one hour interval taken between them. After completion, rinse with ta water, and have them dried for 1 hour before measurement						

Fig.3 (To be cont'd)

SHEET	_	/1/	ΛF	AMP (Japan) Kawasaki, Ja	
6 OF 13	LOC	LOC A	ND.	108-5294	REV.
NAME .18	7 Se	ries	, Sea	led Connecto	r

		(REV. MAR 91)	* .				
	Para.	Test Items	Requirements		Procedures	-	
108-5294	3.5.21	Resistance to Heat:	Termination Resistance (Final) $10 \ m\Omega$ max	of 120° 30 min	t mated connectors to ex C for 120 hours. Recondutes at room temperatu measurement.	lition for	
NUMBER:	3.5.22	Resistance to Cold	Termination Resistance (Low Level) $10\ m\Omega\ max.$	of -50 Recond	t mated connectors to ex °C±5°C for 120 hours. lition at room temperate utes before measureme	ure for	
ON: Customer Release	3.5.23 (1)		Termination Resistance (Low Level) $10 \ m\Omega$ max.	(Low Level) Portland			
SECURITY CLASSIFICATION:	3.5.24	leing	Termination Resistance (Low Level) $10\ m\Omega$ max.	- I	t mated connector to im ng water for 1 hour.	mersion	
	3.5.25	Resistance to to Sulfurous Acid Gas	Termination Resistance (Low Level) 10 mΩ max.	under s	t mated connectors to ex sulfurous acid gas of 10 tration in the room tem )% R.H. minimum for 2	p.p.m. perature	
	3.5.26	Resistance to Oil	Termination Resistance (Low Level) $10~\text{m}\Omega$ max.	immer 50±5° the spe	t mated connectors to sion in the oil shown be 'C for the specified dura cified sequence. Rinse ine for 5 minutes between to foil immersion.	tion, in n	
			·	Step	Names of Oils	Dura- tion	
ļ				1	Torque Converter Oil	1 Hour	
j				2	Transmission Oil	1 Hour	
				3	Engine Oil	1 Hour	
				4	Clutch Oil	1 Hour	
				5	Brake Oil	1 Hour	

Fig.3 (To be cont'd)

SHEET	_	<b>/</b>	/IF	AMP (Japan Kawasaki, J	
7 OF 13	LOC J	LOC <b>A</b>	NO.	108-5294	REV.
NAME					

.187 Series, Sealed Connector

	Para.	Test Items	Requirements	Procedures
+670-00!	3.5.27	Resistance to Coolant	Termination Resistance (Low Level) 10 m $\Omega$ max.	Subject mated connectors to immersion in commercial coolant at $50\pm2$ °C for 2 hours. After this duration, rinse in tap water for 5 minutes, and have them dried at room temperature before measurement.
Release	3.5.28	Resistance to Frontshield Washer Agent	Termination Resistance (Low Level) 10 mΩ max.	Subject mated connectors to immersion in commercial front shield washer agent at 50 ± 2 °C for 2 hours. After this duration, rinse in tap water for 5 minutes, and have them dried at room temperature before measurement.
	3.5.29	Resistance to Ozon	Termination Resistance (Low Level) 10 mΩ max. No abnormalities shall be present, when evaluated per Class C, Para. 9 of JIS D 0205, and Para. 6.6 of JIS K 6301 for aged cracking of rubber.	Subject mated connectors to ozon test atmosphere in the closed test chamber at $40\pm2^{\circ}\text{C}$ by hanging for 24 hours.  The concentration of ozon shall be $50\pm5\text{p.p.m.}$ per Para. 16 of JIS K 6301.
	3.5.30	Water Sprinkle	Termination Resistance (Low Level) 10 mΩ max. Current Leakage: 100 μA max.	Subject mated connectors to water sprinkle test in the closed test chamber where the samples are heated at 120 °C±3 °C for 40 minutes and sprinkle water of normal temperature for 20 minutes. Making this a cycle, repeat for 48 cycles per Test Class S1 of JIS D 0203. During test, apply test potential of 12 V DC by using lead wires of 2 meters.


Fig.3 (To be cont'd)

SHEET	<b>#</b>	/1/	Æ F	AMP (Japan), Kawasaki, Jap	
8 OF 13	roc <b>j</b>	toc <b>A</b>	NO.	108-5294	REV.
NAME .18	7 Se	ries	, Sea	aled Connector	

	Para.	Test Items	Require	ements	Procedures		
4 4		Watertight Sealing	Initial	Final	Subject one of mated connectors to be		
7 -			49 KPa	29.4 KPa	drilled in order to make a hole,		
8			(0.5 kgf/cm <sup>2</sup> )	(0.3 kgf/cm <sup>2</sup> )	through which compressed air of 0.1		
-	3.5.31		min.	min.	kg/cm² (9.8 KPa) is blown in inside		
1				<u> </u>	them while the wire ends are solder-		
l					sealed with insulation ends masked		
					with adhesives. Immerse		
					in water in 30 cm max. deep for 30		
┙					seconds. Monitor for air leakage and		
					increase pressure by 9.8 kPa (0.1 kgf/		
a					cm <sup>2</sup> ) graduation, until leakage takes		
ase					place.		

Fig.3 (end)

SHEET	4	<b>7</b> IV	Æ	AMP (Japar Kawasaki, J	
9 OF 13	roc <b>J</b>	LOC A	NO.	108-5294	REV.
NAME .18	7 Se	ries	, Sea	aled Connecto	or




To obtain termination resistance, deduct resistance of wire from the measured reading. For measuring millivolt drop value, apply test current of 1 A at 12 V DC to the mated connectors.

Fig. 4 Measurement of Termination Resistance

Wrap the connector with the metallic foil.

Between the Adjacent Contacts and Housing

Fig. 5 Measurement of Insulation Resistance and Dielectric Strength







Fig. 7 "Kojiri" Resistance Test Method



# $3.6 \qquad \hbox{Product Qualification and Requalification Tests}.$

	Test Group (a)											
Test or Examination	1	2	3	4	5	6	7	8	9	10	11	12
	Test Sequence (b)											
Confirmation of Product	1	1	1	1	1	1	1	1	1,4	1, 4	1	1
Termination Resistance, Specified Current							3,6,8					
Termination Resistance, Dry Circuit				3,6,8 10,12		2, 6 8,10	7	2, 4	2,5,7	2, 5	2,6	2, 4
Dielection Withstanding Volage		<del>-</del> -			3							
Insulation Resistance						3,11						
Temperature Rise vs Current			į		2							
Current Cycling		•										3
Vibration											3	
Mating Force				2								
Unmating Force				4								
Contact Retention Force (a)			2		,				<u></u>			
Contact Retention Force (b)			_							<u> </u>		5
Contact Unmating Force	3											_
Crimp Tensile Strength		2									<u></u>	
Durability											5	
Housing Lock Strength					5							
Thermal Shock				11								
Humidity, Steady State				9					<u> </u>	ļ		
Corrosion, Salt Spray									3			
Handling Ergonomics							4					
Current Leakage					4					<u> </u>	<u> </u>	
Resistance to "Kojiri"							5		<u> </u>			
Heat Aging				5								
Resistance to Cold				7								
Dust Bombardment						9					<u> </u>	<u> </u>

Fig. 8 (To be cont'd)

SHEET	<b>/</b>	71	ΛF	AMP (Japar Kawasaki,					
12 OF 13	roc	Lac	NO.	108-5294	REV.				
.187 Series, Sealed Connector									

3.6 Product Qualification and Requalification Tests.

	Test Group (a)											
Test or Examination	1	2	3	4	5	6	7	8	9	10	11	12
	Test Sequence (b)											
Icing							7					
Sulfurous Acid Gas									3			
Resistance to Oil						7						
Resistance to Coolant						4						
Resistance to Frontshield Washer Agent						5						
Resistance to Ozon	1								6			
Water Sprinkling	<b>†</b>							3				
Watertight Sealing	<u>                                     </u>			13			9	5	8			

- (a) See Para 4.1.A.
- (b) Numbers indicate sequence in which tests are performed.
- (c) Discontinuties shall not take place in this test group, during tests.

Fig. 8 (end)

SHEET	<b>A</b>	<b>7</b> L	/I F		AMP (Japan), Ltd. Kawasaki, Japan			
13 OF 13	ΓΟC	LOC A	NO.	108-5294	REV.			
NAME	7 Se	ries	. Sea	aled Connecte	or			