Product Specification 108-5300

250 Series, 4-Position, Housing Lance Connector for PCB

Scope: 1.

Contents 1.1

This specification covers the requirements for product performance, test methods and quality assurance provisions of 250 Series, 4-Position, Housing Lance Connector for PCB. The applicable product descriptions and part number are as shown in Fig. 1:

Product Part No.	Descriptions
175763	4-Position, Cap Housing Assembly
172134	4-Position, Plug Housing Assembly
170258	Receptacle Contact #12-#14, 3.0-2.0 mm ²
170032-2/-5	Receptacle Contact #14-#20, 2.0-0.5 mm ²
170384	Receptacle Contact #20-#22, 0.5-0.3 mm ²

Fig. 1

1.2 Product Features:

250 Series, 4-Position, Housing Lance Connector has the following product features.

- (1) Housing has been provided with built-in plastic contact locking device to retain loaded contacts in housing.
- (2) Cap housing has the design suitable to PCB termination.

						DR. 357'91 Minoshita CHK.	SHEET 1 OF		<u> </u>	AMP (Japan), Ltd. Kawasaki, Japan	
Drst.						K, ada 3/27.91	9	roc	LOC A	108-5300	REV.
Š,	C	Revised RFA-1965	K.7	37	3/13	APP. 20 91	NAME				
FININ	В	Revised RFA-1773	YK	Ko	1991	2 Portata	250 Series, 4-Position, Housin Lance Connector for PCB				
ã.	LTR	REVISION RECORD	DR	СНК	DATE	00000		Lan	ice C	onnector for PCB	

2. Applicable Documents:

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1 AMP Specifications:

A. 109-5000

Test Specification, General Requirements for Test Methods

B. 114-5052

Application Specification, Crimping of 250 Series, Tab and Receptacle Contacts

2.2 Military Standard and Specifications:

MIL-STD-202 Test Methods for Electronic and Electrical Component Parts

2.3 Commercial Standards and Specifications:

A. JIS C 3406 Low Voltage Cables for Autmobiles.

3. Requirements:

3.1 Design and Construction:

Product shall be of the design, construction and physical dimensions specified in the applicable product drawing.

3.2 Materials:

A. Contact

Brass, conforming to Alloy No. 260 of ASTM B36

B. Housing:

Cap Housing

6/6 Nylon, Glass-filled,

Plug Housing

6/6 Nylon, Glass-filled, Heat Resistible Grade

3.3 Ratings:

A. Voltage Rating

100 VAC

B. Current Rating

:

C. Temperature Rating

-30 °C to 105 °C

3.3.1 Applicable PCB Thickness

 $1.6 \pm 0.15 \, \text{mm}$

Wire	e Size	R ated
mm ²	(AWG)	Current (A)
0.3	(#22)	5
0.5	(#20)	8
0.85	(#18)	11
1.25	(#16)	15
2.0	(#14)	20
3.0	(#12)	25

SHEET	4	71	ЛF	•	AMP (Japan), Ltd. Kawasaki, Japan				
2 OF 9	roc	toc A	NO.	^{NO.} 108-5300					

250 Series, 4-Position, Housing Lance Connector for PCB

3.4 Performance and Test Descriptions:

The product is designed to meet the electrical, mechanical and environmental performance requirements specified in Fig. 2. All tests are performed at ambient temperature, unless otherwise specified.

3.5 Test Requirements and Procedures Summary:

Para.	Test Items	Req	uirements	-	Procedures
3.5.1	Confirmation of Product	Product shall the requirem product draw Application S 114-5052.	ents of appl ing and	icable	Visually, dimensionally and functionally inspected per applicable inspection plan.
		Electrical Pe	rformance	Requirem	ents
3.5.1	Termination Resistance (Specified Current)	Wire Size mm² (AWG) (422) 0.5 (#20) 0.85 (#18) 1.25 (#16) 2.0 (#14) 3.0 (#12)	Test (A) Current 2 4 7 10 15	Millivolt Drop (mV) 6 12 21 30 45	Measure initial millivolt drop of contact test circuit in mated connectors, Fig. 4. AMP Spec. 109-5305
3.5.1 (2)	Termination Resistance (Low Level)	10 mΩ max. (Final).		Subject contact-loaded and mated connector to open circuit voltage of 50 mA max. closed circuit current of 50 mA DC max. AMP Spec. 109-5306
3.5.1	Dielectric Strength	Connector m potential of 1 minute. No a as corona or t place.	kVAC for i	l es such	Measure by applying test potential between the adjacent contacts, and between the contacts and ground in the mated connectors. MIL-STD-202, Method 301
3.5.1 (4)	Insulation Resistance	100 MΩ min.	(Initial).		Measure by applying test potential between the adjacent contacts, and between the contacts and ground in the unmated connector. MIL-STD-202, Method 302, Condition B

Fig. 2 (to be continued)

SHEET

AMP (Japan), Ltd. Kawasaki, Japan

3 OF 9

LOC LOC NO. 108-5300

NAME

250 Series, 4-Position, Housing

Lance Connector for PCB

2	Para.	Test Items		Req	uirements		Procedures		
108-5300	3.5.1 (5)	Temperature Rising vs. Current	mm² 0.3 0.5 0.85 1.25 2.0 3.0 Phy	(#WG) (#22) (#20) (#18) (#16) (#14) (#12)	Test Current (A) 2 4 7 10 15 20 formance R	sile (min.)	Apply an axial pull-off load to crimpe		
9	3.5.2	Crimp Tensile Strength	mm2 0.3 0.5 0.85 1.25 2.0 3.0	(AWG) (#22) (#20) (#18) (#16) (#14) (#12)	59 88 127 177 265	(kgf) (6) (9) (13) (18) (27) (35)	wire of contact second on the tester at a rate of 100 mm (4.0") a minute. AMP Spec. 109-5205		
Release	3.5.2 (2)	Contact Mating Force		34.3N(0	.5-3.5 kgf)		Measure the force required to mate the contact by operating at 100 mm a minute. AMP Spec. 109-5206		
	3.5.2	Contact Unmating Force	1	34.3N(0	.5-3.5 kgf)		Measure the force to unmate the contacts by operating at 100 mm a minute. AMP Spec. 109-5206		
	3.5.2 (4)	Contact Retention Force	59	N (6kg	f) min.		Apply an axial load to contact by operating at a rate of 100 mm a minute. AMP Spec. 109-30		

Fig. 2 (to be continued)

SHEET	4.	/ IV	1P	AMP (Japai Kawasaki,	
4 OF 9	roc	10C	NO 1	08-5300	REV.
NAME 25				on, Housing r for PCB	


ŀ	Para.	Test Items	Requirements	Procedures
	3.5.2 (5)	Connector Mating Force	147(15kgf) max. (initial) (4-Position connector)	Measure the force required to mate connector by operating at 100 mm a minute. Record by using autograph. AMP Spec. 109-5206
ease	3.5.2 (6)	Connector Unmating Force	29.4N(3kgf) min. (initial) (4-Position connector)	Measure the force required to unmate connector without locking latch by operating at 100 mm (4 in.) a minute. Record by using autograph.
Rele	3.5.2	Vibration Sinusoidal Low Frequency	No abnormalities such as breakage of connector shall not take place. Termination Resistance: 10mV/A max.	Subject mated connectors to 33 Hz, 44 m/s ² (4.5G) accelerated velocity; 200 hours changing the axes in every 50 hours of duration. See. Fig. 5.
	3.5.2 (8)	Solderability	Tested area shall have solder coverage of 95% minimum, excepting sheared surfaces.	Subject contacts to solderability testing. After pretreating by immersion into non-active flux (Alpha-100 or equivalent), immerse in soldering tub at 230 ± 5 °C for 3 ± 0.5 seconds.
Ī		E	nvironmental Performance Requir	ements
	3.5.3 (1)	Humidity, Steady State	Insulation Resistance (Final) $100~M\Omega$ min. Termination Resistance (Low Level) (Final) $10~m\Omega$ min. Dielectric requirements shall be met.	Subject mated connectors to steady state humidity at 60 ± 5 °C and $90\text{-}95\%$ R. H. for 96 hours. Connecter shall be free from dripping affection. MIL-STD-202, Method 103, Condition B

Fig.2 (to be continued)

SHEET		/ IV	/IF	AMP (Japan), Kawasaki, Jap	
5 OF 9	FOC	LOC 0	NO.	108-5300	REV.
NAME 25				sition, Housing etor for PCB	•

Ì	Para.	Test Items	Requirements	Procedures
	3.5.3 (2)	Temperature Life	Termination Resistance (Low Level) (Final) : $10 \ m\Omega$ max.	Subject mated connectors to exposure at 120 ± 3 °C for 120 hours, and recondition in the room temperature for 1 hour before subsequent measurement.
ease	3.5.3	Resistance to Cold	Termination-Resistance (Low Level): $10 \ m\Omega$ max.	Subject mated connector to exposure under cold atmosphere at $-50^{\circ}\mathrm{C}$ for 120 hours. Recondition in the room temperature for 1 hour before subsequent measurement.

Fig.2 (end)



SECURITY CLASSIFICATION:

3.6 Product Qualification and Requalification Tests

					Te	st Gro	р				
Test of Examination	1	2	3	4	5	6	7	8	9	10	11
		Test Sequence (a)									
Examination of Product	1,4	1,4	1,3	1	1	1	1	1,4	1,6	1,5	1,4
Termination Resistance , Specified Current	2			-				3			
Termination Resistance, Dry Circuit				_					5	2,4	3
Dielectric Withstanding Voltage		3							4	ļ	
Insulation Resistance		2							3		
Temperature Rise vs Current	3							<u> </u>			
Vibration								2			
Mating Force		<u> </u>					2	ļ	<u> </u>	ļ <u>.</u>	
Unmaking Force						ļ	3				ļ
Contact Retention						2					
Contact Engaging Force					2					<u> </u>	
Contact Separating Force					3			ļ <u>.</u>			ļ
Crimp Tensile				2							
Solderability			2								
Humidity, Steady State									2		
Temperature Life										3	
Resistance to Cold											2

(a) Numbers indicate the sequence in which tests are performed.

Fig. 3

- 4. Quality Assurance Frovisions
- 4.1 Qualification Testing
 - A. Sample Selection

Connector housings and contacts shall be prepared in accordance with applicable Instruction Sheets and Application Specification, 114-5052. They shall be selected at random from current production. Unless otherwise specified, no sample shall be reused for testing.

B. Test Conditions:

Unless otherwise specified, all the test shall be performed under any combination of the following test conditions.

Temperature:


15 - 35 °C

Relative Humidity:

45 - 75 %

Atmospheric Pressure:

86.7 - 107 kPa (650 - 800 mmHg)



108-5300

Customer Release

SECURITY CLASSIFICATION:




Fig. 3
Termination Resistance (Specified Current and Low Level) and Temperature Rising Measuring Method




Fig. 4 Vibration Testing Method

SHEET		/1/	ΛF	AMP (Japa Kawasaki,	
9 OF 9	roc	roc	NO.	108-5300	REV.
NAME 25				sition, Housing ctor for PCB	