

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST



REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	M1	ECR-14-003330	11MAR2014	GK	HMR

REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2266067-1

FOR REPLACEMENT PARTS FOR APPLICATOR 466502
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
466502

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV		 TE Connectivity	
DIMENSIONS:		CHK RAGHAVENDRA			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RAGHAVENDRA	
		0 PLC ±		NAME SIDE FEED HDM APPLICATOR	
		1 PLC ±		PRODUCT SPEC	
MATERIAL		2 PLC ±		APPLICATION SPEC	
		3 PLC ±		SIZE A3	
FINISH		4 PLC ±		CAGE CODE	
		ANGLES ±		DRAWING NO C= 466502	
		WEIGHT		RESTRICTED TO	
		CUSTOMER ACCESSIBLE PRODUCTION DRAWING		SCALE	
				SHEET 1 OF 2	
				REV M1	

466502-3
OBS

5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.

466502

9-1	PIN, WIRE DISC (.3045)D	129
3-5	PIN, WIRE DISC (.2970)C	128
3-5	PIN, WIRE DISC (.2920)B	127
3-7	PIN, WIRE DISC (.2880)A	126
1	WASHER, FLAT PRECISION	125
	RING,RET "C"(Ø.187)FD FING PIN	124
		123
-1	PIN,SLT SPR(Ø.125x.50)ADJ ROD	122
-0	PIN,SLT SPR(Ø.093x.75)ST GDE PL	121
-1	PIN,DOWEL(Ø.187x.50)LEVER	120
-6	PIN,DOWEL(Ø.187x1.25)HOUSING	119
		118
	WASHER, LOCK(#10)ADJ BLOCK	117
	WASHER,LOCK(#10)ADJ PLATE	116
	WASHER,LOCK(#10)FEED GDE ROD	115
	WASHER,LOCK(#4)FRONT STP GUIDE	114
		113
		112
	WASHER,LOCK(#8)STRIPPER	111
	WASHER,FLAT(Ø5/16)SCREW ADJ	110
		109
	NUT,HEX(NO.6)HOLDDOWN	108
	NUT,HEX(6-32)FEED ADJ	107
		106
	SCR,SHLD(Ø.187x.25)DRAG LEVER	105
		104
	SCR,SKT SET(1/4-20x.25 LW)RAM	103
	SCR,DRIVE(3-20x.19)ID PLATE	102
-5	SCR,PAN HD(6-32x1.50)FEED ADJ	101
-1	PLATE, IDENTIFICATION	100
-6	SCR,SKT(10-32x.75)DRAG	99
	SCR,BHC(8-32x.38 LW)ANVIL	98
-9	SCR,BHC(10-32x.75)CAP	97
-8	SCR,BHC(1/4-20x.62)HOUSING	96
-7	SCR,BHC(10-32x.50)SG ADJ BLOCK	95
-2	SCR,BHC(8-32x.50)SHEAR	94
		93
		92
-7	SCR,BHC(6-32x.38)CAM	91
		90
		89
		88
-7	SCR,SHC(8-32x.46)DEP-HOLD	87
-0	SCR,HEX HD(8-32x.31)FEED FINGER	86
-3	SCR,SHC(4-40x.25)F ST GUIDE	85
-7	SCR,SHC(8-32x.50)STRIPPER	84
-7	SCR,SHC(10-32x.75)FEED ROD GD	83
-6	SCR,SHC(10-32x.62)FD ADJ BLK	82
-4	SCR,SHC(10-32x.38)SG ADJ BL	81
-4	SCR,SHC(10-32x.38)PIVOT BLK	80
3	GUARD ASSY	79
1	INSERT, GUARD	78
		77
		76
		75
1	SPRING, ASSIST	74
	SCR,SHC(6-32x.25 SL)INS DISC	73
1	WASHER, SPECIAL	72
1	SPACER	71
0	DESCRIPTION	ITEM NO
EACH ASSY NO (WHEN BLANK, USE DWG REVISION)		
PARTS LIST		

166600